

Econoseal J Series [Mark II+] (Continued)

Dimensional Data




Figure #1
CAP HOUSING
Single Row Configuration






Figure #2
PLUG HOUSING
Single Row Configuration




Figure #3
CAP HOUSING
Double Row Configuration






Figure #4
PLUG HOUSING
Double Row Configuration

Position Housing Type	Part Number	Figure	Rows Single/ Double	Dim. "A"		Dim. "B"		Dim. "C"		Dim. "D"		Dim. "E"		Dim. "F"	
				mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
1 / Cap	174879-2	1	1	32.5	[1.28]	15.7	[.618]	14.2	[.559]	—	—	13.5	[.531]	—	—
1 / Plug	174877-2	2	1	27.6	[1.09]	17.5	[.689]	22.0	[.866]	—	—	15.8	[.622]	—	—
2 / Cap	174354-2	1	1	32.5	[1.28]	15.7	[.618]	14.05	[.553]	4.8	[.189]	18.3	[.720]	—	—
2 / Plug	174352-2	2	1	27.6	[1.09]	17.5	[.689]	22.8	[.898]	4.8	[.189]	20.6	[.811]	—	—
3 / Cap	174359-2	1	1	32.5	[1.28]	15.7	[.618]	13.9	[.547]	4.8	[.189]	23.1	[.909]	—	—
3 / Plug	174357-2	2	1	27.6	[1.09]	17.5	[.689]	22.8	[.898]	4.8	[.189]	25.4	[1.00]	—	—
4 / Cap	174259-2	3	2	35.5	[1.40]	18.2	[.717]	20.6	[.811]	4.8	[.189]	18.3	[.720]	5.6	[.220]
4 / Plug	174257-2	4	2	27.6	[1.09]	21.5	[.846]	29.3	[1.15]	4.8	[.189]	20.6	[.811]	5.6	[.220]
6 / Cap	174264-2	3	2	35.5	[1.40]	18.2	[.717]	20.6	[.811]	4.8	[.189]	23.1	[.909]	5.6	[.220]
6 / Plug	174262-2	4	2	27.6	[1.09]	21.5	[.846]	29.3	[1.15]	4.8	[.189]	25.4	[1.00]	5.6	[.220]
8 / Cap	174984-2	3	2	36.5	[1.44]	19.7	[.776]	30.7	[1.21]	4.8	[.189]	27.9	[1.10]	5.6	[.220]
8 / Plug	174982-2	4	2	27.6	[1.09]	21.5	[.846]	33.2	[1.31]	4.8	[.189]	31.0	[1.22]	5.6	[.220]
10 / Cap	174657-2	3	2	36.5	[1.44]	19.7	[.776]	30.7	[1.21]	4.8	[.189]	32.7	[1.29]	5.6	[.220]
10 / Plug	174655-2	4	2	27.6	[1.09]	21.5	[.846]	33.2	[1.31]	4.8	[.189]	35.8	[1.41]	5.6	[.220]
12 / Cap	174663-2	3	2	36.5	[1.44]	19.7	[.776]	26.85	[1.06]	4.8	[.189]	37.5	[1.48]	5.6	[.220]
12 / Plug	174661-2	4	2	27.6	[1.09]	21.5	[.846]	33.2	[1.31]	4.8	[.189]	40.6	[1.60]	5.6	[.220]