


PCMCIA COMPONENTS: SINGLE DECK ASSEMBLY



- REFER TO HEADER DRAWING 94898 AND EJECT MECHANISM 92192 FOR ADDITIONAL DIMENSIONS, MATERIAL, AND PLATING INFORMATION.
- REFER TO TA-946 FOR PCB LAYOUT AND PCB KEEP-OUT AREA.
- RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).


mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X±.3			projection	title	product family	code
A	V71608	RHG	12/1/97		.XX±.13			⊕	68 POS. 3.3V EJECT HEADER ASSEMBLY	MCS	—
B	V10948	TFG	2/28/01		.XXX±.051			⊕		size	dwg no
C	V03-0452	LP	4/23/03	angles	0° ±2°			⊕			sheet
D	V03-0517	WL	05/07/03	dr	R.GRAPE	12/1/97		MM			1 of 3
E	T03-0207	WL	05/30/03	enr	D.BRANN	12/1/97		scale			
F	N05-0045	WB	02/18/05	chr	D.BRANN	12/1/97		1:1	A4	74362	
				appd	D.BRANN	12/1/97					
sheet index	revision sheet	F	E	F						cage code	
		1	2	3							

PCMCIA COMPONENTS: SINGLE DECK ASSEMBLY

PCB SIDE ①	PUSH ROD LOCATION ①	SOLDER TAIL ②	STANDOFF (MM)	Ⓐ EJECT HEADER	Ⓑ EJECT MECHANISM	TO MAKE FINAL ASSY PART NUMBER
ABOVE	RIGHT	R/A	NONE	94898-000	92192-00CA	74362 -000CA
ABOVE	RIGHT	R/A	NONE	94898-000	92192-00DA	74362 -000DA
ABOVE	LEFT	R/A	NONE	94898-000	92192-10CA	74362 -100CA
ABOVE	RIGHT	R/A	2	94898-040	92192-02CA	74362 -020CA
ABOVE	LEFT	R/A	2	94898-040	92192-12CA	74362 -120CA
ABOVE	RIGHT	R/A	4	94898-010	92192-04CA	74362 -040CA
ABOVE	LEFT	R/A	4	94898-010	92192-14CA	74362 -140CA
ABOVE	RIGHT	R/A	5	94898-020	92192-05CA	74362 -050CA
ABOVE	LEFT	R/A	5	94898-020	92192-15CA	74362 -150CA
ABOVE	RIGHT	SMT-IL	NONE	94898-002	92192-00CA	74362 -002CA
ABOVE	LEFT	SMT-IL	NONE	94898-002	92192-10CA	74362 -102CA
ABOVE	LEFT	SMT-IL	NONE	94898-002H	92192-10CAH	74362 -102CAH
ABOVE	RIGHT	SMT-STG	NONE	94898-001	92192-00CA	74362 -001CA
ABOVE	LEFT	SMT-STG	NONE	94898-001	92192-10CA	74362 -101CA
ABOVE	LEFT	SMT-STG	NONE	94898-001H	92192-10CAH	74362 -101CAH
BELOW	RIGHT	R/A	NONE	94898-500	92192-10CA	74362 -500CA
BELOW	LEFT	R/A	NONE	94898-500	92192-00CA	74362 -600CA
BELOW	RIGHT	R/A	2	94898-540	92192-12CA	74362 -520CA
BELOW	LEFT	R/A	2	94898-540	92192-02CA	74362 -620CA
BELOW	RIGHT	R/A	4	94898-510	92192-14CA	74362 -540CA
BELOW	LEFT	R/A	4	94898-510	92192-04CA	74362 -640CA
BELOW	RIGHT	R/A	5	94898-520	92192-15CA	74362 -550CA
BELOW	LEFT	R/A	5	94898-520	92192-05CA	74362 -650CA
BELOW	RIGHT	SMT-IL	NONE	94898-502	92192-10CA	74362 -502CA
BELOW	LEFT	SMT-IL	NONE	94898-502	92192-00CA	74362 -602CA
BELOW	RIGHT	SMT-STG	NONE	94898-501	92192-10CA	74362 -501CA
BELOW	LEFT	SMT-STG	NONE	94898-501	92192-00CA	74362 -601CA

NOTES:

- ① PCB SIDE AND PUSHROD LOCATION ARE AS APPEARS INSTALLED.
- ② SOLDER TAIL KEY:
R/A = RIGHT ANGLE PIN-THROUGH-HOLE
SMT-STG = STAGGERED SURFACE MOUNT
SMT-IL = SURFACE MOUNT IN-LINE (SINGLE ROW)
- 3 ADD "H" TO PART NUMBER FOR
OPTIONAL HOLD DOWN (4 PER ASSEMBLY)
- | mat'l. code | |
|-------------|--------|
| ltr | ecn no |
| E | |



[illegible]

PCMCIA COMPONENTS: SINGLE DECK ASSEMBLY

PCB SIDE ①	PUSH ROD LOCATION ①	SOLDER TAIL ②	STANDOFF (MM)	Ⓐ EJECT HEADER	Ⓑ EJECT MECHANISM	TO MAKE FINAL ASSY PART NUMBER
ABOVE	RIGHT	R/A	NONE	94898-000LF	92192-00CA	74362-000CALF
ABOVE	RIGHT	R/A	NONE	94898-000LF	92192-00DA	74362-000DALF
ABOVE	LEFT	R/A	NONE	94898-000LF	92192-10CA	74362-100CALF
ABOVE	RIGHT	R/A	2	94898-040LF	92192-02CA	74362-020CALF
ABOVE	LEFT	R/A	2	94898-040LF	92192-12CA	74362-120CALF
ABOVE	RIGHT	R/A	4	94898-010LF	92192-04CA	74362-040CALF
ABOVE	LEFT	R/A	4	94898-010LF	92192-14CA	74362-140CALF
ABOVE	RIGHT	R/A	5	94898-020LF	92192-05CA	74362-050CALF
ABOVE	LEFT	R/A	5	94898-020LF	92192-15CA	74362-150CALF
ABOVE	RIGHT	SMT-IL	NONE	94898-002LF	92192-00CA	74362-002CALF
ABOVE	LEFT	SMT-IL	NONE	94898-002LF	92192-10CA	74362-102CALF
ABOVE	LEFT	SMT-IL	NONE	94898-002HLF	92192-10CAH	74362-102CAHLF
ABOVE	RIGHT	SMT-STG	NONE	94898-001LF	92192-00CA	74362-001CALF
ABOVE	LEFT	SMT-STG	NONE	94898-001LF	92192-10CA	74362-101CALF
ABOVE	LEFT	SMT-STG	NONE	94898-001HLF	92192-10CAH	74362-101CAHLF
BELOW	RIGHT	R/A	NONE	94898-500LF	92192-10CA	74362-500CALF
BELOW	LEFT	R/A	NONE	94898-500LF	92192-00CA	74362-600CALF
BELOW	RIGHT	R/A	2	94898-540LF	92192-12CA	74362-520CALF
BELOW	LEFT	R/A	2	94898-540LF	92192-02CA	74362-620CALF
BELOW	RIGHT	R/A	4	94898-510LF	92192-14CA	74362-540CALF
BELOW	LEFT	R/A	4	94898-510LF	92192-04CA	74362-640CALF
BELOW	RIGHT	R/A	5	94898-520LF	92192-15CA	74362-550CALF
BELOW	LEFT	R/A	5	94898-520LF	92192-05CA	74362-650CALF
BELOW	RIGHT	SMT-IL	NONE	94898-502LF	92192-10CA	74362-502CALF
BELOW	LEFT	SMT-IL	NONE	94898-502LF	92192-00CA	74362-602CALF
BELOW	RIGHT	SMT-STG	NONE	94898-501LF	92192-10CA	74362-501CALF
BELOW	LEFT	SMT-STG	NONE	94898-501LF	92192-00CA	74362-601CALF

NOTES:

- IF LEAD FREE P/N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
SOLDER TAIL : SMT-IL, SMT-STG CAN RESIST 40 SECONDS IN A CONVECTION,
INFRA-RED OR VAPOR PHASE REFLOW OVEN.
SOLDER TAIL : R/A CAN RESIST 10 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- PCB SIDE AND PUSHROD LOCATION ARE AS APPEARS INSTALLED.
- SOLDER TAIL KEY:
R/A = RIGHT ANGLE PIN-THROUGH-HOLE
SMT-STG = STAGGERED SURFACE MOUNT
SMT-IL = SURFACE MOUNT IN-LINE (SINGLE ROW)
- ADD "H" TO PART NUMBER FOR
OPTIONAL HOLD DOWN (4 PER ASSEMBLY)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X±.3	projection 	title 68 POS. 3.3V EJECT HEADER ASSEMBLY	product family MCS	code -
F					.XX±.13				
					.XXX±.051				
				angles	0° ±2°	MM 	scale 1:1	size A4	dwg no 74362
				dr	R.GRAPE 12/1/97				
				enrg	D.BRANN 12/1/97				
				chr	D.BRANN 12/1/97	sheet index	revision sheet		
				appd	D.BRANN 12/1/97				