





REV.	DATE	DESCRIPTION
NC	03/25/02	INITIAL RELEASE
A	09/03/07	REVISE BARREL, FERRULE DIMENSIONS, UPDATE DRAWING FORMAT



CRIMP NOTES:

1. CRIMPED FERRULE HEX CRIMP .178"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS DATE	Amphenol Connex F R/A CRIMP PLUG (FOR RG-179/U, 187A/U)							
8						DRAWN G.R.S.						09/03/07		
7						CHECKED								
6						ISSUED								
5						SHEET 1 OF 1		PART DESCRIPTION						
4	FERRULE	BRASS	NICKEL	1				PART NO.	222179					
3	CONTACT PIN	BRASS	GOLD	1				CAD FILE	C:/222/222179.DWG					
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO.	222179.DWG			REV. A	SIZE A	SCALE NA
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY										