






1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. WILL ACCEPT SEVEN (7) TYPE XII SOCKET CONTACTS.
3. #4 FASTENER RECOMMENDED FOR MOUNTING.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	4-40 THREADED INSERTS	NO	A	206227-6		
	3.81±0.08 [.150±.003]	YES	A	206227-5		
	3.81±0.08 [.150±.003]	NO	B	206227-2		
	3.81±0.08 [.150±.003]	NO	A	206227-1		
C		PERIPHERAL SEAL	SEE DETAIL	PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG D.HARDY 05/31/94	 TE Connectivity			
DIMENSIONS: INCHES		CHK W.G.LENKER 06/08/94				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.FRANTUM 07/13/94	NAME			
		PRODUCT SPEC	RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC			
		108-10024				
		APPLICATION SPEC				
		—				
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
NYLON, BLACK	—	—	A1	00779	C=206227	—
CUSTOMER DRAWING			SCALE	2:1	SHEET 1 of 1	REV M2