




19 L

SOCKET 1/2" hexagon UD profile, long pattern

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated



12.5

1/2



mm

Code	No.	Ø mm	L	d ₁	d ₂	t	mm	mm	£
1718738	19 L 10	10	77.0	15.5	22.5	12.0	117	10	
1718746	19 L 11	11	77.0	16.7	22.5	13.0	121	10	
1718754	19 L 12	12	77.0	18.0	22.5	14.0	127	10	
1718762	19 L 13	13	77.0	19.2	22.5	16.0	98	10	
1718770	19 L 14	14	77.0	20.5	22.5	16.5	109	10	
1718789	19 L 15	15	77.0	21.7	22.5	16.5	117	10	
1718800	19 L 16	16	77.0	23.0	24.0	16.5	130	10	
1718819	19 L 17	17	77.0	24.0	24.0	16.5	132	10	
1718827	19 L 18	18	82.0	25.5	25.0	20.0	147	10	
1718835	19 L 19	19	82.0	26.7	26.0	22.0	174	10	

Code	No.	Ø mm	L	d ₁	d ₂	t	mm	mm	£
2300559	19 L 21	21	82.0	29.2	28.5	24.0	211	1	
2300567	19 L 22	22	82.0	30.5	28.5	24.0	219	1	
2300575	19 L 24	24	82.0	33.0	29.0	26.0	257	1	
2300583	19 L 27	27	82.0	36.7	30.0	30.0	290	1	
2300591	19 L 30	30	82.0	40.5	32.5	33.0	351	1	
2300605	19 L 32	32	82.0	43.0	34.5	36.0	387	1	
2300613	19 L 34	34	82.0	45.5	36.5	37.0	432	1	


D 19 L

SOCKET 1/2" bi-hexagon UD profile, long pattern

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- Sizes 16, 18, 21 mm with hole drilled for tommy bar Ø 8 mm

12.5

1/2



mm

Code	No.	Ø mm	L	d ₁	d ₂	t	mm	mm	£
6141140	D 19 L 10	10	77.0	15.5	22.5	12.0	117	10	
6141220	D 19 L 12	12	77.0	18.0	22.5	14.0	127	10	
6140170	D 19 L 13	13	77.0	19.2	22.5	16.0	101	10	
6140250	D 19 L 14	14	77.0	20.5	22.5	16.5	109	10	
6142460	D 19 L 15	15	77.0	21.7	22.5	16.5	119	10	
6142540	D 19 L 16	16	77.0	23.0	24.0	16.5	128	10	
6140330	D 19 L 17	17	77.0	24.0	24.0	16.5	133	10	
6142380	D 19 L 18	18	82.0	25.5	25.0	20.0	147	10	
6140410	D 19 L 19	19	82.0	26.7	26.0	22.0	175	10	
6140680	D 19 L 21	21	82.0	29.2	28.5	24.0	211	10	
6145050	D 19 L 22	22	82.0	30.5	28.5	24.0	219	10	
6140760	D 19 L 24	24	82.0	33.0	29.0	26.0	257	10	
6141060	D 19 L 27	27	82.0	36.7	30.0	30.0	290	10	
6145640	D 19 L 30	30	82.0	40.5	32.5	33.0	351	10	
6191320	D 19 L 32	32	82.0	43.0	34.5	36.0	387	10	
6147500	D 19 L 34	34	82.0	45.5	36.5	37.0	432	5	

mm AF

Code	No.	Ø AF	L	d ₁	d ₂	t	mm	mm	£
6141300	D 19 L 1/2AF	1/2	77.0	18.7	22.5	16.0	95	10	
6141490	D 19 L 9/16AF	9/16	77.0	20.7	22.5	16.5	105	10	
6141570	D 19 L 5/8AF	5/8	77.0	22.5	24.0	16.5	120	10	
6141650	D 19 L 11/16AF	11/16	77.0	24.7	24.8	16.5	143	10	
6141730	D 19 L 3/4AF	3/4	82.0	26.7	26.0	22.0	164	10	
6141810	D 19 L 13/16AF	13/16	82.0	28.5	28.5	22.0	197	10	
6142030	D 19 L 7/8AF	7/8	82.0	30.6	28.5	24.0	208	10	
6142110	D 19 L 15/16AF	15/16	82.0	32.6	29.0	26.0	234	10	


TX 19

SOCKET 1/2" for protruding TORX® head screws

- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2



Code	No.	Ø	mm	L	d ₁	d ₂	t	mm	mm	£
6145720	TX 19 E10	E10	M8	9.42	38.0	13.5	22.5	15.5	56	10
6194180	TX 19 E11	E11	-	10.08	38.0	14.0	22.5	15.5	55	5
6147340	TX 19 E12	E12	M10	11.17	38.0	15.5	22.5	15.5	59	10
6147420	TX 19 E14	E14	M12	12.90	38.0	17.0	22.5	13.0	59	10
6194420	TX 19 E16	E16	M12	14.76	38.0	19.0	22.5	13.0	62	10
6194500	TX 19 E18	E18	M14	16.70	40.0	21.0	24.5	14.0	78	10
6194690	TX 19 E20	E20	M16	18.45	40.0	23.5	24.5	14.0	85	10
6195070	TX 19 E24	E24	M18 - M20	22.16	41.5	28.5	26.0	16.0	116	5


ITX 19

SCREWDRIVER BIT SOCKET 1/2" for recessed TORX® head screws

- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2



Code	No.	Ø	mm	L ₁	L ₂	d	mm	mm	mm	£
6152930	ITX 19 T20	T20	M4 - M5	3.86	55	17	22.5	76	10	
6154200	ITX 19 T25	T25	M4.5 - M5	4.43	55	17	22.5	75	10	
6154630	ITX 19 T27	T27	M4.5 - M6	4.99	55	17	22.5	76	10	
6156170	ITX 19 T30	T30	M6 - M7	5.52	55	17	22.5	75	10	
6156330	ITX 19 T40	T40	M7 - M8	6.65	55	17	22.5	76	10	
6157060	ITX 19 T45	T45	M8 - M10	7.82	55	17	22.5	77	10	
6158030	ITX 19 T50	T50	M10	8.83	55	17	22.5	92	10	
6158380	ITX 19 T55	T55	M12	11.22	55	17	23.0	107	10	
6158540	ITX 19 T60	T60	M14	13.25	55	15	24.7	137	10	