




PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	J	K	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT
	MIN. in (mm)	MAX. in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	lbs (N)		100 pcs lbs (g)
PLWP30SC	.12 (3)	1.18 (30)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	5.8 (147.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.32 (145)
PLWP40SC	.12 (3)	1.58 (40)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	7.0 (178)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.37 (168)
PLWP50SC	.12 (3)	1.97 (50)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	8.2 (208.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.42 (191)

NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

CAD FILENAME/LAYERS										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS									
										PANDUIT CORP. TINLEY PARK, ILLINOIS									
										WINGED PUSH MOUNT CABLE TIE PLWP30, 40, 50SC									
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.1(2.5) (.XXX) ±.020(1.51) (.XX) ±.02(1.5) ANGLES ±----					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.				
										DRAWN BY SO		MAT'L: HEAT STABILIZED NYLON 6.6 BLACK (-30)			SCALE NONE				
10	10/28/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS			26267	10			DATE 12/14/90				DRAWING NO. SS-26267			DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP		CHK'D HVP						