








|                               |  |                |  |      |                                       |      |      |      |      |                                                                                       |      |      |             |  |                                                                                                     |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
|-------------------------------|--|----------------|--|------|---------------------------------------|------|------|------|------|---------------------------------------------------------------------------------------|------|------|-------------|--|-----------------------------------------------------------------------------------------------------|--|--|--|--|---------------------------|--|--|--|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|-------|--|--|--|--|--|--|--|--|--|
| mat'l. code                   |  |                |  |      | surface<br>ISO 1302 ✓                 |      |      |      |      | tolerance<br>ISO 406<br>ISO 1101                                                      |      |      |             |  | projection<br> |  |  |  |  | product family<br>QUICKIE |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| ltr ecn no dr date            |  |                |  |      | tolerances unless otherwise specified |      |      |      |      |                                                                                       |      |      |             |  |                                                                                                     |  |  |  |  |                           |  |  |  |  | <br><br>scale 1:1<br><br> |  |  |  |  | title |  |  |  |  |  |  |  |  |  |
| BA N08-007 Bobby S 4/28/08    |  |                |  |      | angles                                |      |      |      |      | linear                                                                                |      |      |             |  | HEADER, QUICKIE                                                                                     |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| BB N09-0007 R.B 2009/01/12    |  |                |  |      |                                       |      |      |      |      |                                                                                       |      |      |             |  | SEA-HORSE, VERTICAL                                                                                 |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| BC EL-N-012087 J.Z 2012-07-04 |  |                |  |      | 0°±2°                                 |      |      |      |      |                                                                                       |      |      |             |  |                                                                                                     |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| BD EL-N-13354 DCS 2012-11-02  |  |                |  |      | dr M. CORNMAN 8/21/90                 |      |      |      |      |  |      |      |             |  | dwg no                                                                                              |  |  |  |  | sheet 1 of 23             |  |  |  |  | size                                                                                                                                                                                                |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| BE EL-N-17979 TIM 2014-06-17  |  |                |  |      | enr M. SMYK 8/21/90                   |      |      |      |      |                                                                                       |      |      |             |  | 65863                                                                                               |  |  |  |  | A3                        |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
|                               |  |                |  |      | chr M. SMYK 8/21/90                   |      |      |      |      |                                                                                       |      |      |             |  |                                                                                                     |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
|                               |  |                |  |      | appd M. SMYK 8/21/90                  |      |      |      |      |                                                                                       |      |      |             |  | type                                                                                                |  |  |  |  | Product Customer Drawing  |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |
| sheet index                   |  | revision sheet |  | BE 1 | BE 2                                  | BE 3 | BE 4 | BE 5 | BE 6 | BE 7                                                                                  | BE 8 | BE 9 | . . . BE 23 |  |                                                                                                     |  |  |  |  |                           |  |  |  |  |                                                                                                                                                                                                     |  |  |  |  |       |  |  |  |  |  |  |  |  |  |

NOTES:

- HOUSING MAT'L: HIGH TEMPERTURE THERMOPLASTIC. UL94V-0.  
COLOR : BLACK
- PIN MATERIAL: PHOSPHOR-BRONZE
- 3 LBS/1.36 KG MIN. RETENTION.
- TO DETERMINE DIMENSION:  
N = NUMBER OF POSITIONS.  
EXAMPLE: 10 POS., (N-1) x .100[2.54]=.900[22.87]
- RETENTIVE LEG:  
RETENTION FEATURE AVAILABLE ON CONNECTORS WITH .105/2.67, .120/3.05  
OR .150/3.81 TAIL LENGTH. RETENTION P/N INCLUDES THE LETTER "R"  
AFTER THE EXISTING P/N.  
EXAMPLE : 65863-XXX FOR EXISTING P/N  
65863-XXXR FOR RETENTION P/N  
RETENTION FEATURE LOCATION IS MANUFACTURERS OPTION.  
5LB/2.3KG MAX INSERTION FORCE AND .25LB./1KG MIN RETENTION FORCE  
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED  
HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER.  
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES UNLESS OTHERWISE SPECIFIED.
- PLATING ON LEAD-IN PORTION OF PIN IS MANUFACTURING OPTION.
- L.P. LATCHES TO BE USED WITH FEMALE CONNECTOR WITHOUT STRAIN RELIEF, ,  
STANDARD LATCHES TO BE USED WITH FEMALE CONNECTOR WITH STRAIN RELIEF.
- RECOMMENDED MOUNTING SCREW SIZE : #2-56 FILLISTER HEAD MACHINE SCREW,  
1/4" LONG FOR 1/16" AND 3/32" BOARD, 5/16" LONG FOR 1/8" BOARD.
- DASH -7XX IS POLARIZED (PIN MISSING).
- UNDERPLATING: 50μ"/1.27μm Ni.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER  
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- FOR POLARIZATION, SPECIFY POSITION NUMBER (i.e.. 03= PIN 3) TO OMIT PIN.  
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE  
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm  
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES  
IF THEY ARE AVAILABLE.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND  
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT  
ENVIRONMENTS."
- PLATING OPTIONS:  
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL,  
OPTIONALLY TIN ON TAIL.
- THE PART NUMBER IN THE DASH NUMBER WITH A LETTER "S" WILL HAVE A  
SPECIAL SEA HORSE USED.
- LEAD FREE PLATING: 100u"~160u"/2.54u~4.06u PURE Sn.
- 65863-XXXP, P-DESIGNATE ORIENTATION POST.(SEE PAGE 23)
- 65863-XXXF, F-PLATING FOUR SIDES ON CONTACT AREA.(SEE PAGE 23)



|             |          |    |    |                       |                                       |                       |                                                 |  |  |  |
|-------------|----------|----|----|-----------------------|---------------------------------------|-----------------------|-------------------------------------------------|--|--|--|
| mat'l. code |          |    |    | surface<br>ISO 1302 ✓ | tolerance<br>ISO 406<br>ISO 1101      | projection<br>INCH/MM | product family<br>QUICKIE                       |  |  |  |
| ltr         | ecn      | no | dr | date                  | tolerances unless otherwise specified | scale 1:1<br>FCI      | title<br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |  |  |
| BE          |          |    |    |                       | angles linear                         |                       |                                                 |  |  |  |
|             |          |    |    |                       | 0°±2°                                 |                       |                                                 |  |  |  |
|             |          |    |    |                       | dr                                    |                       | dwg no                                          |  |  |  |
|             |          |    |    |                       | enr                                   |                       | sheet 2 of 23                                   |  |  |  |
|             |          |    |    |                       | chr                                   |                       | 65863                                           |  |  |  |
|             |          |    |    |                       | appd                                  |                       | type Product Customer Drawing                   |  |  |  |
| sheet       | revision |    |    |                       |                                       |                       |                                                 |  |  |  |
| index       | sheet    |    |    |                       |                                       |                       |                                                 |  |  |  |

|                          |      |                 |              |            |                                             |   |  |  |       |            |  |  |   |  |  |   |            |
|--------------------------|------|-----------------|--------------|------------|---------------------------------------------|---|--|--|-------|------------|--|--|---|--|--|---|------------|
| 1                        |      |                 | 2            |            |                                             | 3 |  |  |       | 4          |  |  | 5 |  |  | 6 |            |
| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D      | TERMINAL PLATING                            |   |  |  | STYLE | NOTE 16,19 |  |  |   |  |  |   |            |
| 65863-001                | 2x5  | NO              | .400/10,160  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | A     |            |  |  |   |  |  |   |            |
| ↑ -002                   | ↑    | ↑               | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | ↑     |            |  |  |   |  |  |   |            |
| -003                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -004                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -005                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | ↓     |            |  |  |   |  |  |   | NOTE 16,19 |
| -006                     | 2x5  |                 | .400/10,160  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | A     |            |  |  |   |  |  |   | NOTE 16,19 |
| -007                     | 2x7  |                 | .600/15,240  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | C     |            |  |  |   |  |  |   | NOTE 16,19 |
| -008                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | ↑     |            |  |  |   |  |  |   | NOTE 16,19 |
| -009                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -010                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -011                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | ↓     |            |  |  |   |  |  |   | NOTE 16,19 |
| -012                     | 2x7  |                 | .600/15,240  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | C     |            |  |  |   |  |  |   | NOTE 16,19 |
| -013                     | 2x8  |                 | .700/17,780  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | D     |            |  |  |   |  |  |   | NOTE 16,19 |
| -014                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | ↑     |            |  |  |   |  |  |   | NOTE 16,19 |
| -015                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -016                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -017                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -018                     | 2x8  |                 | .700/17,780  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -019                     | 2x10 |                 | .900/22,860  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -020                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -021                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -022                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -023                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -024                     | 2x10 |                 | .900/22,860  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -025                     | 2x13 |                 | 1.200/30,480 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -026                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -027                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -028                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -029                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -030                     | 2x13 |                 | 1.200/30,480 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
|                          | 2x17 |                 | 1.600/40,640 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -032                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -033                     |      |                 |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| -034                     |      |                 |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |       |            |  |  |   |  |  |   | NOTE 16,19 |
| ↓ -035                   | ↓    | ↓               | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  | ↓     |            |  |  |   |  |  |   | NOTE 16,19 |
| 65863-036                | 2x17 | NO              | 1.600/40,640 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  | D     | NOTE 16,19 |  |  |   |  |  |   |            |

|             |  |                |  |                       |  |                                  |  |                                                                                                     |  |                           |  |                                                            |  |                                                                                       |  |                     |  |                          |  |
|-------------|--|----------------|--|-----------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------|--|------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|---------------------|--|--------------------------|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE |  |                                                            |  |                                                                                       |  |                     |  |                          |  |
| ltr         |  | ecn no         |  | dr                    |  | date                             |  | tolerances unless otherwise specified                                                               |  |                           |  |                                                            |  | title                                                                                 |  |                     |  |                          |  |
| BE          |  |                |  |                       |  |                                  |  | angles                                                                                              |  | linear                    |  | XXX±.01/XXX±.3<br>XXX±.005/XXX±0.13<br>XXX±.0020/XXX±0.051 |  | INCH/MM                                                                               |  | HEADER, QUICKIE     |  |                          |  |
|             |  |                |  |                       |  |                                  |  | 0°±2°                                                                                               |  |                           |  |                                                            |  | scale 1:1                                                                             |  | SEA-HORSE, VERTICAL |  |                          |  |
|             |  |                |  |                       |  |                                  |  | dr                                                                                                  |  | M. CORNMAN                |  | 8/21/90                                                    |  |  |  | dwg no              |  | sheet3 of23size          |  |
|             |  |                |  |                       |  |                                  |  | engr                                                                                                |  | M. SMYK                   |  | 8/21/90                                                    |  |                                                                                       |  | 65863               |  | A3                       |  |
|             |  |                |  |                       |  |                                  |  | chr                                                                                                 |  | M. SMYK                   |  | 8/21/90                                                    |  |                                                                                       |  | type                |  | Product Customer Drawing |  |
| sheet index |  | revision sheet |  |                       |  |                                  |  |                                                                                                     |  |                           |  |                                                            |  |                                                                                       |  |                     |  |                          |  |

|             |  |                |  |                       |  |                                  |  |                                                                                                     |  |                           |  |         |  |
|-------------|--|----------------|--|-----------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------|--|---------|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE |  |         |  |
| ltr         |  | ecn no         |  | dr                    |  | date                             |  | tolerances unless otherwise specified                                                               |  | title                     |  |         |  |
| BE          |  |                |  |                       |  |                                  |  | linear                                                                                              |  | INCH/MM                   |  |         |  |
|             |  |                |  |                       |  |                                  |  | .XXX±.01/.XXX.3                                                                                     |  |                           |  |         |  |
|             |  |                |  |                       |  |                                  |  | .XXX±.005/.XXX.0.13                                                                                 |  |                           |  |         |  |
|             |  |                |  |                       |  |                                  |  | .XXX±.0020/.XXX±0.051                                                                               |  |                           |  |         |  |
|             |  |                |  |                       |  |                                  |  | dr                                                                                                  |  | M. CORNMAN                |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | enr                                                                                                 |  | M. SMYK                   |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | chr                                                                                                 |  | M. SMYK                   |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | appd                                                                                                |  | M. SMYK                   |  | 8/21/90 |  |
| sheet index |  | revision sheet |  |                       |  |                                  |  |                                                                                                     |  |                           |  |         |  |

|           |  |                                                                                       |  |        |  |                          |  |      |  |
|-----------|--|---------------------------------------------------------------------------------------|--|--------|--|--------------------------|--|------|--|
| scale 1:1 |  |  |  | dwg no |  | sheet3 of 23             |  | size |  |
|           |  |                                                                                       |  | 65863  |  |                          |  | A3   |  |
|           |  |                                                                                       |  | type   |  | Product Customer Drawing |  |      |  |



FCIconnect.com

Copyright FCI

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-037                | 2x20 | NO                 | 1.900/48,260 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -038                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -039                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -040                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -041                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -042                     | 2x20 |                    | 1.900/48,260 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -043                     | 2x25 |                    | 2.400/60,960 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -044                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -045                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -046                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -047                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -048                     | 2x25 | NO                 | 2.400/60,960 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | D     |
| -049                     | 2x5  | STD                | .400/10,160  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |
| -050                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -051                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -052                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -053                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -054                     | 2x5  |                    | .400/10,160  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | A     |
| -055                     | 2x7  |                    | .600/15,240  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     |
| -056                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -057                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -058                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -059                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -060                     | 2x7  |                    | .600/15,240  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | C     |
| -061                     | 2x8  |                    | .700/17,780  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -062                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -063                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -064                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -065                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -066                     | 2x8  |                    | .700/17,780  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -067                     | 2x10 |                    | .900/22,860  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -068                     |      |                    |              | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -069                     |      |                    |              | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -070                     |      |                    |              | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -071                     |      |                    |              | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-072                | 2x10 | STD                | .900/22,860  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | D     |

|             |  |                |  |                       |  |                                  |  |                                       |  |                           |  |         |  |
|-------------|--|----------------|--|-----------------------|--|----------------------------------|--|---------------------------------------|--|---------------------------|--|---------|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br>                        |  | product family<br>QUICKIE |  |         |  |
| ltr         |  | ecn no         |  | dr                    |  | date                             |  | tolerances unless otherwise specified |  | title                     |  |         |  |
| BE          |  |                |  |                       |  |                                  |  | linear                                |  | HEADER, QUICKIE           |  |         |  |
|             |  |                |  |                       |  |                                  |  | 0°±2'                                 |  | SEA-HORSE, VERTICAL       |  |         |  |
|             |  |                |  |                       |  |                                  |  | dr                                    |  | M. CORNMAN                |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | enr                                   |  | M. SMYK                   |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | chr                                   |  | M. SMYK                   |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | appd                                  |  | M. SMYK                   |  | 8/21/90 |  |
| sheet index |  | revision sheet |  |                       |  |                                  |  |                                       |  |                           |  |         |  |

|           |  |  |  |        |  |                          |  |
|-----------|--|--|--|--------|--|--------------------------|--|
| scale 1:1 |  |  |  | dwg no |  | sheet4 of23size          |  |
|           |  |  |  | 65863  |  | A3                       |  |
|           |  |  |  | type   |  | Product Customer Drawing |  |

|   |      |                           |      |                    |              |                                             |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|---|------|---------------------------|------|--------------------|--------------|---------------------------------------------|---------------------------------------------|---|--|--|--|-------|------------|------------|--|---|--|--|---|--|---|
|   |      | 1                         |      |                    |              | 2                                           |                                             | 3 |  |  |  |       |            |            |  | 4 |  |  | 5 |  | 6 |
|   |      | PRODUCT NO<br>NOTES 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D                                       | TERMINAL PLATING                            |   |  |  |  | STYLE |            |            |  |   |  |  |   |  |   |
| A |      | 65863-073                 | 2x13 | STD                | 1.200/30,480 | .105/ 2,67                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  | D     |            |            |  |   |  |  |   |  |   |
|   | ↑    | -074                      | ↑    | ↑                  | ↑            | .105/ 2,67                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -075                      |      |                    |              | .150/ 3,81                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -076                      |      |                    |              | .150/ 3,81                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -077                      | ↓    |                    |              | .675/17,15                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -078                      | 2x13 |                    | 1.200/30,480 | .675/17,15                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -079                      | 2x17 |                    | 1.600/40,640 | .105/ 2,67                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -080                      | ↑    |                    | ↑            | .105/ 2,67                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -081                      |      |                    |              | .150/ 3,81                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -082                      | ↓    |                    |              | .150/ 3,81                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -083                      | ↓    |                    | ↓            | .675/17,15                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -084                      | 2x17 |                    | 1.600/40,640 | .675/17,15                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -085                      | 2x20 |                    | 1.900/48,260 | .105/ 2,67                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -086                      | ↑    |                    | ↑            | .105/ 2,67                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -087                      | ↑    |                    |              | .150/ 3,81                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -088                      | ↓    |                    |              | .150/ 3,81                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -089                      | ↓    |                    | ↓            | .675/17,15                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -090                      | 2x20 |                    | 1.900/48,260 | .675/17,15                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   |      | -091                      | 2x25 |                    | 2.400/60,960 | .105/ 2,67                                  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | -092                      | ↑    |                    | ↑            | .105/ 2,67                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  |       |            | NOTE 16,19 |  |   |  |  |   |  |   |
|   | -093 | ↑                         |      |                    | .150/ 3,81   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -094 | ↓                         |      | ↓                  | .150/ 3,81   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -095 | ↓                         |      | ↓                  | .675/17,15   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -096 | 2x25                      | STD  | 2.400/60,960       | .675/17,15   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -097 | 2x30                      | NO   | 2.900/73,660       | .105/ 2,67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -098 | ↑                         | ↑    | ↑                  | .105/ 2,67   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -099 |                           |      |                    | .150/ 3,81   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -100 |                           |      |                    | .150/ 3,81   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -101 |                           | ↓    |                    | .675/17,15   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -102 |                           | NO   |                    | .675/17,15   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -103 |                           | STD  |                    | .105/ 2,67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -104 |                           | ↑    |                    | .105/ 2,67   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -105 |                           |      |                    | .150/ 3,81   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   | -106 |                           |      |                    | .150/ 3,81   | 120u"~200u"/3.04um~5.08umTIN/LEAD           |                                             |   |  |  |  |       | NOTE 16,19 |            |  |   |  |  |   |  |   |
|   | -107 | ↓                         | ↓    | ↓                  | .675/17,15   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |                                             |   |  |  |  |       |            |            |  |   |  |  |   |  |   |
|   |      | 65863-108                 | 2x30 | STD                | 2.900/73,660 | .675/17,15                                  | 120u"~200u"/3.04um~5.08umTIN/LEAD           |   |  |  |  | D     |            | NOTE 16,19 |  |   |  |  |   |  |   |

FCI

FCIconnect.com

Copyright FCI

|             |  |                |  |                       |  |                                  |  |                                                                                                     |  |                                        |  |         |  |
|-------------|--|----------------|--|-----------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|----------------------------------------|--|---------|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE              |  |         |  |
| ltr         |  | ecn no         |  | dr                    |  | date                             |  | tolerances unless otherwise specified                                                               |  | title                                  |  |         |  |
| BE          |  |                |  |                       |  |                                  |  | angles linear                                                                                       |  | HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |         |  |
|             |  |                |  |                       |  |                                  |  | 0°±2'                                                                                               |  | INCH/MM                                |  |         |  |
|             |  |                |  |                       |  |                                  |  |                                                                                                     |  | scale 1:1                              |  |         |  |
|             |  |                |  |                       |  |                                  |  | dr                                                                                                  |  | M. CORNMAN                             |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | enr                                                                                                 |  | M. SMYK                                |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | chr                                                                                                 |  | M. SMYK                                |  | 8/21/90 |  |
|             |  |                |  |                       |  |                                  |  | appd                                                                                                |  | M. SMYK                                |  | 8/21/90 |  |
| sheet index |  | revision sheet |  |                       |  |                                  |  |                                                                                                     |  |                                        |  |         |  |

form: A3

1

2

3

4

5

6

PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014

D

|             |        |                |      |                                       |            |                                  |                  |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
|-------------|--------|----------------|------|---------------------------------------|------------|----------------------------------|------------------|-----------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-------------------------------------------------|-----------------|---------|--|
| mat'l. code |        |                |      | surface<br>ISO 1302 ✓                 |            | tolerance<br>ISO 406<br>ISO 1101 |                  | projection<br> |  | product family<br>QUICKIE                                                             |                                                 |                 |         |  |
| ltr         | ecn no | dr             | date | tolerances unless otherwise specified |            |                                  |                  |                                                                                                     |  |  | title<br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |                 |         |  |
| BE          |        |                |      | angles                                | linear     |                                  |                  |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
|             |        |                |      |                                       |            |                                  | XXX±.01 / XXX±.3 |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
|             |        |                |      |                                       |            | XXX±.005 / XXX±.013              |                  |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
|             |        |                |      | 0°±2'                                 |            | XXX±.0020 / XXX±.0051            |                  | scale 1:1                                                                                           |  |                                                                                       |                                                 |                 |         |  |
|             |        |                |      | dr                                    | M. CORNMAN | 8/21/90                          |                  |                |  | dwg no                                                                                |                                                 | sheet6 of23size |         |  |
|             |        |                |      | enr                                   | M. SMYK    | 8/21/90                          |                  |                                                                                                     |  | 65863                                                                                 |                                                 | A3              |         |  |
|             |        |                |      | chr                                   | M. SMYK    | 8/21/90                          |                  |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
|             |        |                |      | appd                                  | M. SMYK    | 8/21/90                          |                  |                                                                                                     |  |                                                                                       |                                                 |                 |         |  |
| sheet index |        | revision sheet |      |                                       |            |                                  |                  |                                                                                                     |  | type                                                                                  | Product                                         | Customer        | Drawing |  |



D



4 | PDS: Rev :BE STATUS: Released Printed: Jun 19, 201









1

2

3

4

5

6

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-396                | 2x5  | LP                 | .400/10.160  | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u NI | A     |
| -397                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -398                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -399                     |      | LP                 |              | .150/ 3,81 |                                             | A     |
| -400                     |      | NO                 |              | .105/ 2,67 |                                             | B     |
| -401                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -402                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -403                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -404                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -405                     | 2x5  | LP                 | .400/10.160  | .150/ 3,81 |                                             | B     |
| -406                     | 2x7  | NO                 | .600/15.240  | .105/ 2,67 |                                             | C     |
| -407                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -408                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -409                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -410                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -411                     | 2x7  | LP                 | .600/15.240  | .150/ 3,81 |                                             | C     |
| -412                     | 2x8  | NO                 | .700/17.780  | .105/ 2,67 |                                             | D     |
| -413                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -414                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -415                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -416                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -417                     | 2x8  | LP                 | .700/17.780  | .150/ 3,81 |                                             |       |
| -418                     | 2x10 | NO                 | .900/22.860  | .105/ 2,67 |                                             |       |
| -419                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -420                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -421                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -422                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -423                     | 2x10 | LP                 | .900/22.860  | .150/ 3,81 |                                             |       |
| -424                     | 2x13 | NO                 | 1.200/30.480 | .105/ 2,67 |                                             |       |
| -425                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -426                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -427                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -428                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -429                     | 2x13 | LP                 | 1.200/30.480 | .150/ 3,81 |                                             |       |
| 65863-430                | 2x17 | NO                 | 1.600/40.640 | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u NI | D     |

FCIconnect.com

Copyright FCI

| mat'l. code |                | surface    |      | tolerance                             |            | projection |  | product family                |  |
|-------------|----------------|------------|------|---------------------------------------|------------|------------|--|-------------------------------|--|
|             |                | ISO 1302 ✓ |      | ISO 406<br>ISO 1101                   |            |            |  | QUICKIE                       |  |
| ltr         | ecn no         | dr         | date | tolerances unless otherwise specified |            | INCH/MM    |  | title                         |  |
| BE          |                |            |      | angles                                | linear     | linear     |  | HEADER, QUICKIE               |  |
|             |                |            |      | 0°±2°                                 |            | scale 1:1  |  | SEA-HORSE, VERTICAL           |  |
|             |                |            |      | dr                                    | M. CORNMAN | 8/21/90    |  | dwg no sheet 14 of 23 size    |  |
|             |                |            |      | enrg                                  | M. SMYK    | 8/21/90    |  | 65863 A3                      |  |
|             |                |            |      | chr                                   | M. SMYK    | 8/21/90    |  | type Product Customer Drawing |  |
|             |                |            |      | appd                                  | M. SMYK    | 8/21/90    |  |                               |  |
| sheet index | revision sheet |            |      |                                       |            |            |  |                               |  |

form: A3

1

2

3

4

5

6

PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014

| PRODUCT NO<br>NOTES 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | PIN<br>STYLE | MISSING |
|---------------------------|------|--------------------|--------------|------------|---------------------------------------------|--------------|---------|
| 65863-431                 | 2x17 | STD                | 1.600/40.640 | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D            | NONE    |
| -432                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -433                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -434                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -435                      | 2x17 | LP                 | 1.600/40.640 | .150/ 3,81 |                                             |              |         |
| -436                      | 2x20 | NO                 | 1.900/48.260 | .105/ 2,67 |                                             |              |         |
| -437                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -438                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -439                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -440                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -441                      | 2x20 | LP                 | 1.900/48.260 | .150/ 3,81 |                                             |              |         |
| -442                      | 2x25 | NO                 | 2.400/60.960 | .105/ 2,67 |                                             |              |         |
| -443                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -444                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -445                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -446                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -447                      | 2x25 | LP                 | 2.400/60.960 | .150/ 3,81 |                                             |              |         |
| -448                      | 2x30 | NO                 | 2.900/73.660 | .105/ 2,67 |                                             |              |         |
| -449                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -450                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -451                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -452                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -453                      | 2x30 | LP                 | 2.900/73.660 | .150/ 3,81 |                                             |              |         |
| -454                      | 2x12 | NO                 | 1.100/27.940 | .105/ 2,67 |                                             |              |         |
| -455                      | 2x12 | STD                |              |            |                                             |              |         |
| -456                      | 2x12 | LP                 |              |            |                                             |              |         |
| -456S                     | 2x12 | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -457                      | 2x12 | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -458                      |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -459                      |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -460                      |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -461                      |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -462                      |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -463                      |      | NO                 |              |            | 120u"-200u"/3.04u-5.08uTIN/LEAD             |              |         |
| -464                      |      | STD                |              |            | 120u"-200u"/3.04u-5.08uTIN/LEAD             |              |         |
| 65863-465                 | 2x12 | LP                 | 1.100/27.940 | .105/ 2,67 | 120u"-200u"/3.04u-5.08uTIN/LEAD             | D            | NONE    |

NOTE 18

NOTE 16,19

NOTE 16,19

NOTE 16,19

[illegible]

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|-----------------|--------------|------------|---------------------------------------------|-------|
| 65863-466                | 2x12 | NO              | 1.100/27.940 | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -467                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -468                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -469                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -470                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -471                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -472                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -473                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -474                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -475                     |      | NO              |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -476                     |      | STD             |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -477                     |      | LP              |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -478                     |      | NO              |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -479                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -480                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -481                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -482                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -483                     |      | LP              |              | .105/2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -484                     |      | NO              |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -485                     |      | STD             |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -486                     |      | LP              |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -487                     |      | NO              |              | .675/17.15 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -488                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -489                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -490                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -491                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -492                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -493                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -494                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -495                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -496                     |      | NO              |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -497                     |      | STD             |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -498                     | 2x12 | LP              | 1.100/27.940 | .675/17.15 | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -499                     | 2x15 | NO              | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-500                | 2x15 | STD             | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

|             |     |                |    |                                |                                       |           |                                  |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
|-------------|-----|----------------|----|--------------------------------|---------------------------------------|-----------|----------------------------------|--|-----------------------------------------------------------------------------------------------------|---------------------------------------------------|---------------------------|-------|--|--|--|--|
| mat'l. code |     |                |    |                                | surface<br>ISO 1302 ✓                 |           | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |                                                   | product family<br>QUICKIE |       |  |  |  |  |
| ltr         | ecn | no             | dr | date                           | tolerances unless otherwise specified |           |                                  |  |                                                                                                     |                                                   |                           | title |  |  |  |  |
| BE          |     |                |    |                                | angles                                | linear    | XXX±.01/XXX±.3                   |  |                                                                                                     | INCH/MM<br><br>scale 1:1                          |                           |       |  |  |  |  |
|             |     |                |    | XXX±.005/XXX±.13               |                                       |           |                                  |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
|             |     |                |    | 0°±2°<br>XXXX±.0020/XXXX±.0051 |                                       |           |                                  |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
|             |     |                |    |                                | dr                                    | M. CORNMN | 8/21/90                          |  |                                                                                                     | dwg no<br><br>sheet16 of23size<br><br>65863<br>A3 |                           |       |  |  |  |  |
|             |     |                |    |                                | enr                                   | M. SMYK   | 8/21/90                          |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
|             |     |                |    |                                | chr                                   | M. SMYK   | 8/21/90                          |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
|             |     |                |    |                                | app                                   | M. SMYK   | 8/21/90                          |  |                                                                                                     |                                                   |                           |       |  |  |  |  |
| sheet index |     | revision sheet |    |                                |                                       |           |                                  |  |                                                                                                     | type Product Customer Drawing                     |                           |       |  |  |  |  |



| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-501                | 2x15 | LP                 | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -502                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -503                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -504                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -505                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -506                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -507                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -508                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -509                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -510                     |      | LP                 |              | .105/2.67  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -511                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -512                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -513                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -514                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -515                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -516                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -517                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -518                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -519                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -520                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -521                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -522                     |      | LP                 |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -523                     |      | NO                 |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -524                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -525                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -526                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -527                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -528                     |      | LP                 |              | .105/2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -529                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -530                     |      | STD                |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -531                     |      | LP                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -532                     |      | NO                 |              | .675/17.15 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -533                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -534                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-535                | 2x15 | NO                 | 1.400/35.560 | .675/17.15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

|             |     |                |    |                       |        |                                       |                               |                                                                                                     |                                                                                       |                                                 |                               |  |                |  |      |  |
|-------------|-----|----------------|----|-----------------------|--------|---------------------------------------|-------------------------------|-----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------|-------------------------------|--|----------------|--|------|--|
| mat'l. code |     |                |    | surface<br>ISO 1302 ✓ |        | tolerance<br>ISO 406<br>ISO 1101      |                               | projection<br> |                                                                                       | product family<br>QUICKIE                       |                               |  |                |  |      |  |
| ltr         | ecn | no             | dr | date                  |        | tolerances unless otherwise specified |                               | <br>INCH/MM    |                                                                                       | title<br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |                               |  |                |  |      |  |
| BE          |     |                |    |                       | angles | linear                                | X.XX ± .01 / X.XX ± .03       |                                                                                                     |                                                                                       |                                                 |                               |  |                |  |      |  |
|             |     |                |    |                       |        |                                       | X.XX ± .005 / X.XX ± .013     |                                                                                                     |                                                                                       |                                                 |                               |  |                |  |      |  |
|             |     |                |    |                       | 0°±2°  |                                       | X.XXX ± .0020 / X.XXX ± .0051 |                                                                                                     |                                                                                       |                                                 |                               |  |                |  |      |  |
|             |     |                |    |                       |        | scale 1:1                             |                               |                                                                                                     |                                                                                       |                                                 |                               |  |                |  |      |  |
|             |     |                |    |                       |        | dr                                    | M. CORNMN                     | 8/21/90                                                                                             |  |                                                 | dwg no                        |  | sheet 17 of 23 |  | size |  |
|             |     |                |    |                       |        | enrg                                  | M. SMYK                       | 8/21/90                                                                                             |                                                                                       |                                                 | 65863                         |  | A3             |  |      |  |
|             |     |                |    |                       |        | chr                                   | M. SMYK                       | 8/21/90                                                                                             |                                                                                       |                                                 |                               |  |                |  |      |  |
|             |     |                |    |                       |        | appd                                  | M. SMYK                       | 8/21/90                                                                                             |                                                                                       |                                                 |                               |  |                |  |      |  |
| sheet index |     | revision sheet |    |                       |        |                                       |                               |                                                                                                     |                                                                                       |                                                 | type Product Customer Drawing |  |                |  |      |  |

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-536                | 2x15 | STD                | 1.400/35.560 | .675/17.15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -537                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -538                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -539                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -540                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -541                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -542                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -543                     | 2x15 | LP                 | 1.400/35.560 | .675/17.15 | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -544                     | 2x22 | NO                 | 2.100/53.340 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -545                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -546                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -547                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -548                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -549                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -550                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -551                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -552                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -553                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -554                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -555                     |      | LP                 |              | .105/2.67  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -556                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -557                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -558                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -559                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -560                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -561                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -562                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -563                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -564                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -565                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -566                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -567                     |      | LP                 |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -568                     |      | NO                 |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -569                     |      | STD                |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-570                | 2x22 | LP                 | 2.100/53.340 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

[illegible]



| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D       | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|-------------|---------------------------------------------|-------|
| 65863-605                | 2X32 | STD                | 3.100/78.740 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -606                     |      | LP                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -607                     |      | NO                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -608                     |      | STD                |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -609                     |      | LP                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -610                     |      | NO                 |              |             | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -611                     |      | STD                |              |             | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -612                     | 2X32 | LP                 | 3.100/78.740 | .105/2.67   | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -613                     | 2x20 | NO                 | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -614                     | 2x20 | STD                | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -615                     | 2x20 | LP                 | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -616                     | 2x25 | NO                 | 2.400/60.960 | .450/ 11.43 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -617                     | 2x17 | NO                 | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -618                     | 2x17 | STD                | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -619                     | 2x17 | LP                 | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -620                     | 2X32 | STD                | 3.100/78.740 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -621                     | 2X32 | NO                 | 3.100/78.740 |             |                                             |       |
| -622                     | 2x15 | STD                | 1.400/35.560 |             |                                             |       |
| -623                     | 2x15 | NO                 | 1.400/35.560 |             |                                             |       |
| -624                     | 2x22 | STD                | 2.100/53.340 |             |                                             |       |
| -625                     | 2x22 | NO                 | 2.100/53.340 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -626                     | 2x25 | NO                 | 2.400/60.960 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -627                     | 2x25 | STD                | 2.400/60.960 |             |                                             |       |
| -628                     | 2x25 | LP                 | 2.400/60.960 |             |                                             |       |
| -629                     | 2x20 | NO                 | 1.900/48.260 |             |                                             |       |
| -630                     | 2x20 | STD                | 1.900/48.260 |             |                                             |       |
| -631                     | 2x20 | LP                 | 1.900/48.260 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -632                     | 2x20 | STD                | 1.900/48.260 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -633                     | 2x8  | STD                | .700/17.78   | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -634                     | 2x7  | NO                 | .600/15.24   | .236/ 5.99  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     |
| -635                     | 2x5  | STD                | .400/10.16   | .520/13.21  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |
| -636                     | 2x8  | NO                 | .700/17.78   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -637                     | 2x8  | STD                | .700/17.78   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -638                     | 2x10 | NO                 | .800/20.32   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-639                | 2x10 | STD                | .800/20.32   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

**CUSTOMER SPECIAL**

A

1

B

1

C

1

D

1

form: A3

1

2

(2)

JS

20

4 PDS: Rev :BE

**STATUS:** Released

Printed: Jun 19, 2014

|                    |  |                |  |  |                                       |  |                           |                                  |         |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |
|--------------------|--|----------------|--|--|---------------------------------------|--|---------------------------|----------------------------------|---------|--|-----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-------------------------------|-----------------------------------------------------|--|----|--|--|--|
| mat'l. code        |  |                |  |  | surface<br>ISO 1302 ✓                 |  |                           | tolerance<br>ISO 406<br>ISO 1101 |         |  | projection<br> |                                                                                       | product family<br>QUICKIE                                                                                     |                               |                                                     |  |    |  |  |  |
| ltr ecn no dr date |  |                |  |  | tolerances unless otherwise specified |  |                           |                                  |         |  |                                                                                                     |                                                                                       | <br>INCH/MM<br>scale 1:1 |                               | title<br><br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |    |  |  |  |
| BE                 |  |                |  |  | angles                                |  | linear                    |                                  |         |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |
|                    |  |                |  |  |                                       |  | $\frac{XXX-01}{XXX-03}$   |                                  |         |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |
|                    |  |                |  |  | $0^{\circ}\pm 2'$                     |  | $\frac{XXX-005}{XXX-013}$ |                                  |         |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |
|                    |  |                |  |  | dr                                    |  | M. CORNMAN                |                                  | 8/21/90 |  |                                                                                                     |  |                                                                                                               | dwg no sheet20 of23size       |                                                     |  |    |  |  |  |
|                    |  |                |  |  | engr                                  |  | M. SMYK                   |                                  | 8/21/90 |  |                                                                                                     |                                                                                       |                                                                                                               | 65863                         |                                                     |  | A3 |  |  |  |
|                    |  |                |  |  | chr                                   |  | M. SMYK                   |                                  | 8/21/90 |  |                                                                                                     |                                                                                       |                                                                                                               | type Product Customer Drawing |                                                     |  |    |  |  |  |
|                    |  |                |  |  | appd                                  |  | M. SMYK                   |                                  | 8/21/90 |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |
| sheet index        |  | revision sheet |  |  |                                       |  |                           |                                  |         |  |                                                                                                     |                                                                                       |                                                                                                               |                               |                                                     |  |    |  |  |  |



EC|connect.com

Copyright FCI

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D     | TERMINAL PLATING                            | STYLE | PIN<br>MISSING |
|--------------------------|------|-----------------|--------------|-----------|---------------------------------------------|-------|----------------|
| 65863-640                | 2x12 | NO              | 1.100/ 27.94 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | NONE           |
| -641                     | 2x12 | STD             | 1.100/ 27.94 |           |                                             |       |                |
| -642                     | 2x15 | NO              | 1.400/ 35.56 |           |                                             |       |                |
| -643                     | 2x15 | STD             | 1.400/ 35.56 |           |                                             |       |                |
| -644                     | 2x30 | NO              | 2.900/ 73.66 |           |                                             |       |                |
| -645                     | 2x30 | STD             | 2.900/ 73.66 |           |                                             |       |                |
| -646                     | 2x25 | STD             | 2.400/ 60.96 |           |                                             | D     |                |
| -647                     | 2x5  | STD             | .400/ 10.16  |           |                                             | A     |                |
| -648                     | 2x7  | STD             | .600/ 15.24  |           |                                             | C     |                |
| -649                     | 2x13 | STD             | 1.120/ 30.48 |           |                                             | D     |                |
| -650                     | 2x17 | STD             | 1.600/ 40.64 |           |                                             | D     |                |
| -651                     | 2x5  | NO              | .400/ 10.16  |           |                                             | A     |                |
| -652                     | 2x7  | NO              | .600/ 15.24  |           |                                             | C     |                |
| -653                     | 2x13 | NO              | 1.120/ 30.48 |           |                                             | D     |                |
| -654                     | 2x17 | NO              | 1.600/ 40.64 | .150/3.81 |                                             | D     |                |
| -655                     | 2x5  | STD             | .400/ 10.16  | .175/4.45 |                                             | A     |                |
| -656                     | 2x7  |                 | .600/ 15.24  |           |                                             | C     |                |
| -657                     | 2x13 |                 | 1.120/ 30.48 |           |                                             | D     |                |
| -658                     | 2x17 | STD             | 1.600/ 40.64 | .175/4.45 |                                             | D     |                |
| -659                     | 2x5  | NO              | .400/ 10.16  | .250/6.35 |                                             | A     |                |
| -660                     | 2x7  | LP              | .600/ 15.24  | .236/5.99 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     | NONE           |
| -715                     | 2x8  | LP              | .700/ 17.78  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3              |
| -716                     | 2x8  | LP              | .700/ 17.78  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 14             |
| -717                     | 2X20 | LP              | 1.900/48.26  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 20             |
| -717S                    | 2X20 | LP              | 1.900/48.26  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 20             |
| -733                     | 2x17 | LP              | 1.600/ 40.14 | .105/2.67 | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 5              |
| -734                     | 2x17 | STD             | 1.600/ 40.64 | .105/2.67 | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 5              |
| -735                     | 2x10 | LP              | .900/ 22.86  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 16             |
| -736                     | 2x10 | LP              | .900/ 22.86  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 19             |
| -737                     | 2x5  | LP              | .400/ 10.16  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     | 10             |
| -738                     | 2X20 | LP              | 1.900/48.26  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 8              |
| -739                     | 2X25 | LP              | 2.400/60.96  |           |                                             | D     | 25             |
| -740                     | 2X12 | LP              | 1.100/ 27.94 |           |                                             | D     | 20             |
| -741                     | 2X17 | LP              | 1.600/ 40.64 |           |                                             | D     | 5              |
| -741S                    | 2X17 | LP              | 1.600/ 40.64 |           |                                             | D     | 5              |
| -742                     | 2X5  | LP              | .400/ 10.16  |           |                                             | A     | 2              |
| 65863-743                | 2X17 | LP              | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3              |

NOTE 18

NOTE 18

|                     |  |                |  |                                       |  |                                                        |  |                |  |                                        |  |        |  |                          |  |      |  |
|---------------------|--|----------------|--|---------------------------------------|--|--------------------------------------------------------|--|----------------|--|----------------------------------------|--|--------|--|--------------------------|--|------|--|
| mat'l. code         |  |                |  | surface<br>ISO 1302 ✓                 |  | tolerance<br>ISO 406<br>ISO 1101                       |  | projection<br> |  | product family<br>QUICKIE              |  |        |  |                          |  |      |  |
| litr ecn no dr date |  |                |  | tolerances unless otherwise specified |  |                                                        |  |                |  |                                        |  | title  |  |                          |  |      |  |
| BE                  |  |                |  | angles                                |  | linear                                                 |  | INCH/MM        |  | HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |        |  |                          |  |      |  |
|                     |  |                |  | 0°±2'                                 |  | 0.004±0.005 / 0.004±0.013<br>0.004±0.002 / 0.004±0.005 |  | scale 1:1      |  |                                        |  |        |  |                          |  |      |  |
|                     |  |                |  | dr                                    |  | M. CORNMAN                                             |  | 8/21/90        |  |                                        |  | dwg no |  | sheet21 of23             |  | size |  |
|                     |  |                |  | enrg                                  |  | M. SMYK                                                |  | 8/21/90        |  |                                        |  | 65863  |  |                          |  | A3   |  |
|                     |  |                |  | chr                                   |  | M. SMYK                                                |  | 8/21/90        |  |                                        |  |        |  |                          |  |      |  |
|                     |  |                |  | appd                                  |  | M. SMYK                                                |  | 8/21/90        |  |                                        |  |        |  |                          |  |      |  |
| sheet index         |  | revision sheet |  |                                       |  |                                                        |  |                |  |                                        |  | type   |  | Product Customer Drawing |  |      |  |

1

2

3

4

5

6

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D     | TERMINAL PLATING                            | STYLE | MISSING<br>PIN |
|--------------------------|------|--------------------|--------------|-----------|---------------------------------------------|-------|----------------|
| 65863-744                | 2x17 | LP                 | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3, 5           |
| 65863-744S               | 2x17 | LP                 | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3, 5           |
| 65863-843                | 2x5  | N/A                | .400/ 10.16  | .120/3.05 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |                |
| -844                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     |                |
| -845                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -846                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -847                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -848                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -849                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| -850                     | 2x30 | N/A                | 2.900/ 73.66 |           |                                             | D     |                |
| -851                     | 2x5  | STD                | .400/ 10.16  |           |                                             | A     |                |
| -852                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     | N/A            |
| -853                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -854                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -855                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -856                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -857                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| -858                     | 2x30 | STD                | 2.900/ 73.66 |           |                                             | D     |                |
| -859                     | 2x5  | L/P                | .400/ 10.16  |           |                                             | A     |                |
| -860                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     |                |
| -861                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -861S                    | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -862                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -863                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -864                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -865                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| 65863-866                | 2x30 | L/P                | 2.900/ 73.66 | .120/3.05 |                                             | D     |                |
| 65863-867S               | 2x12 | L/P                | 1.100/ 27.94 | .105/2.67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 24             |
| 65863-868S               | 2x12 | L/P                | 1.100/ 27.94 | .105/2.67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 24             |

NOTE 18

NOTE 18

NOTE 18

NOTE 18

mat'l. code

surface  
ISO 1302 ✓

tolerance  
ISO 406  
ISO 1101

projection  
INCH/MM

product family  
QUICKIE

ltr  
BE

ecn no

dr

date

tolerances unless otherwise specified

angles  
0°±2°

linear  
XXX±.01/XXX.03  
XXX±.005/XXX.013  
XXXX±.0020/XXXX.0051

scale 1:1

title  
HEADER, QUICKIE  
SEA-HORSE, VERTICAL

dr  
M. CORNMAN 8/21/90

enr  
M. SMYK 8/21/90

chr  
M. SMYK 8/21/90

appd  
M. SMYK 8/21/90

dwg no  
65863

sheet 22 of 23

size  
A3

type  
Product Customer Drawing

sheet index

revision sheet

FCI

Copyright FCI

form: A3

1

2

3

4

5

6

PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-049P               | 2x5  | STD                | .400/10,160  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |
| 65863-055P               | 2x7  | STD                | .600/15,240  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     |
| 65863-061P               | 2x8  | STD                | .700/17,780  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-067P               | 2x10 | STD                | .900/22,860  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-073P               | 2x13 | STD                | 1.200/30,480 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-079P               | 2x17 | STD                | 1.600/40,640 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-085P               | 2x20 | STD                | 1.900/48,260 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-091P               | 2x25 | STD                | 2.400/60,960 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-203P               | 2x20 | LP                 | 1.900/48,260 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-079F               | 2x17 | STD                | 1.600/40,640 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-081F               | 2x17 | STD                | 1.600/40,640 | .150/ 3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

|             |     |          |    |                                                                                                                           |  |                                                                                                     |                                  |                           |                                                                                                  |                                        |  |                |      |
|-------------|-----|----------|----|---------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------|----------------------------------|---------------------------|--------------------------------------------------------------------------------------------------|----------------------------------------|--|----------------|------|
| mat'l. code |     |          |    | surface <input checked="" type="checkbox"/> tolerance<br>ISO 1302 <input checked="" type="checkbox"/> ISO 406<br>ISO 1101 |  | projection<br> |                                  | product family<br>QUICKIE |                                                                                                  |                                        |  |                |      |
| ltr         | ecn | no       | dr | date                                                                                                                      |  | tolerances unless otherwise specified                                                               |                                  |                           | title                                                                                            |                                        |  |                |      |
| BE          |     |          |    |                                                                                                                           |  | angles<br>linear<br>0°±2°                                                                           | $\frac{.001-.01}{.004-.03}$      |                           | INCH/MM<br> | HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |                |      |
|             |     |          |    |                                                                                                                           |  |                                                                                                     | $\frac{.001-.005}{.003-.013}$    |                           |                                                                                                  |                                        |  |                |      |
|             |     |          |    |                                                                                                                           |  |                                                                                                     | $\frac{.0003-.0020}{.003-.0051}$ |                           |                                                                                                  |                                        |  |                |      |
|             |     |          |    |                                                                                                                           |  | dr                                                                                                  | M. CORNMAN                       | 8/21/90                   | FCI<br>     | dwg no                                 |  | sheet 23 of 23 | size |
|             |     |          |    |                                                                                                                           |  | engr                                                                                                | M. SMYK                          | 8/21/90                   |                                                                                                  | 65863                                  |  |                | A3   |
|             |     |          |    |                                                                                                                           |  | chr                                                                                                 | M. SMYK                          | 8/21/90                   |                                                                                                  |                                        |  |                |      |
|             |     |          |    |                                                                                                                           |  | appd                                                                                                | M. SMYK                          | 8/21/90                   |                                                                                                  |                                        |  |                |      |
| sheet index |     | revision |    |                                                                                                                           |  |                                                                                                     |                                  |                           |                                                                                                  |                                        |  |                |      |
| sheet       |     |          |    |                                                                                                                           |  |                                                                                                     |                                  |                           |                                                                                                  |                                        |  |                |      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[65863-741LF](#)