

T&B® Fittings



T&B Catalog Number:

LT950P

UPC Number:

78621045072

Description:

1/2" Non-Metallic liquidtight Bullet; -90°. For use with liquidtight non-metallic Type B conduit or liquidtight non-metallic tubing.

Status:

Active

WEB USE

-T&B Product Line 012

Features

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

Application

- The Bullet; meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

General

-Trade Size (inches) 1/2
-Material Thermoplastic

Dimension Information

-Dimension A (inches) 0.570
-Dimension B (inches) 1.489
-Dimension C (inches) 1.448
-Dimension D-Minimum Throat (inches) 0.550
-E- NPT Thread (inches) 1/2-14
-Dimension F (inches) 1.986
-A (mm) 14.48
-B (mm) 37.82
-C (mm) 36.78
-D (mm) 13.97
-F Approx. (mm) 50.44
-Dimension A (inches) 0.570
-Dimension B (inches) 1.489
-Dimension C (inches) 1.448

Specifications

-3dmodel Available on Website

Packaging

-T&B Inner Pack 10
-Package in Units 50
-T&B Sold in UOM Each
-T&B Weight Per UOM 11.1 lbs. per 100

Application Support

-T&B Instruction Sheets ta00998-tb2

-Guide to Nonmetallic Conduit Applications Available on Website

-XTRAFLEX System Specifications Available on Website

Notes

-*Note Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com