



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

104352



- 1 -A- SHALL BE THE INTERSECTION OF THE POST AND THE HOUSING
- 2 ASSEMBLY TO BE CUT TO SIZE AS REQUIRED
- 3 ASSEMBLY MAY NOT EXCEED THE BOW LIMITATIONS AS STATED IN AMP TEST SPEC NO 102-25044
- 4 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POSTS AND THE HOUSING
- 5 RETENTIVE POSTS PER 115-1166-1 FOR ACTIVE POSITION SIZES OF 6 AND BELOW. (SEE TABLE FOR LOCATIONS)
- 6 RETENTIVE POSTS PER 115-1133-5 FOR ACTIVE POSITION SIZES OF 7 AND ABOVE. (SEE TABLE FOR LOCATIONS)
- 7 .020 (M) FOR KINKED TAILS
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	OBSOLETE		15,16	1,2	32	3-147550-7	104832-1	32	2-104352-1
			39,40	1,2	80	1-104818-4	104832-1	80	2-104352-0
			29,30	1,2	60	1-104818-4	104832-1	60	1-104352-9
			24,25	1,2	50	1-104818-4	104832-1	50	1-104352-8
			19,20	1,2	40	1-104818-4	104832-1	40	1-104352-7
			16,17	1,2	34	1-104818-4	104832-1	34	1-104352-6
	OBSOLETE		14,15	1,2	30	1-104818-4	104832-1	30	1-104352-5
	OBSOLETE		13,14	1,2	28	1-104818-4	104832-1	28	1-104352-4
	SUPERSEDED		12,13	1,2	26	1-104818-4	104832-1	26	1-104352-3
			11,12	1,2	24	1-104818-4	104832-1	24	1-104352-2
	OBSOLETE		10,11	1,2	22	1-104818-4	104832-1	22	1-104352-1
	SUPERSEDED		9,10	1,2	20	1-104818-4	104832-1	20	1-104352-0
	OBSOLETE		8,9	1,2	18	1-104818-4	104832-1	18	1-104352-9
	OBSOLETE		7,8	1,2	16	1-104818-4	104832-1	16	1-104352-8
			6,7	1,2	14	1-104818-4	104832-1	14	104352-7
	OBSOLETE		5,6	1,2	12	1-104818-4	104832-1	12	1-104352-6
			4,5	1,2	10	1-104818-4	104832-1	10	104352-5
			3,4	1,2	8	1-104818-4	104832-1	8	104352-4
	OBSOLETE		ALL	ALL	6	1-104818-4	104832-1	6	1-104352-3
			ALL	ALL	4	1-104818-4	104832-1	4	104352-2
			ALL	ALL	2	1-104818-4	104832-1	2	104352-1
	RETENTION		ROW N	ROW M	QTY	PART NUMBER ②	HOUSING PART NO	NO OF POSN	ASSEMBLY PART NUMBER
	FEATURE		HOLD-DOWN POST CONFIG LOCATIONS		BANDOLIER POST ASSEMBLY		AS REQD ①		

P		LTR	REVISION RECORD	DATE	DWN	APVD	DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN H MOLL		MATERIAL		HEAT TREAT	
N1		REVISED PER ECO-09-020935	28AUG09	KK	AEG		0 PLC ± .005		1 PLC ± .005		2 PLC ± .005		3 PLC ± .005		4 PLC ± .005	
N		REV PER EC OG3C-0495-03	09MAR04	MB	JG		ANGLES ±		SURFACE TEXTURE		R FEIDT		APVD		R FEIDT	
SCALE		4:1	SIZE		A1		DRAWING NO		104352		SHEET		1 OF 1		REV	

LOC AD
DIST 38

AMP 3308-8 REV 23FEB95

8

7

6

5

4

3

2

1