

FUSEHOLDERS


PCB mount

OG


for  5 × 20 / 6,3 × 32 mm

Fuseholder open design Type OG


through hole mounting



0751.0056



0751.0099/0100/0141/0142



- *) • change in footprint/drilling diagram needed for different fuse-link sizes
- **) • impossible to have two fuse-links inserted at the same time
- spec. clip-ends prevent axial fuse-link movement

Technical data

- Rated voltage: 250 V*
- Rated current: 10 A
- Rated power acceptance at ambient air temperature T_a 23 °C: 2,5 W
- Power acceptance at higher T_a : see derating curves
- Take note of the information on pages 215–219
- Allowable ambient air temperatures T_a : -40 °C to +85 °C
- Contact resistance: 5 mΩ*
- Clip-Material: bronze or brass, tin-plated

* between 2 clips


Standards

IEC 60127-6
EN 60127-6
UL 512


Approvals, Patents

 UL 0751.0099/0141 (16 A/500 V¹)
0751.0056 (10 A 500 V¹)

¹ Fuse-links according to the standards only for 250 V
0751.0099/0100/0141/0142:
Patents in U.S. (No. 4,606,590) and in further countries



Derating curve



Order No.		Terminals
0751.0099	Clip, bronze, tin-plated	"kicked"
0751.0100	Clip, brass, tin-plated	"kicked"
0751.0141	Clip, bronze, tin-plated	straight
0751.0142	Clip, brass, tin-plated	straight
0751.0056	Clip, bronze, tin-plated	straight