



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	22.0	± max
T:	5.0	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	5.0	± max
B:	11.50	± nom
C:	4.33	± nom



Electrical Specifications

Resistance:	120. (Ω	± 25 %
Max Steady State Current upto 65°C:	2.00	A
Max Rec. Energy Rating:	80	J
Actual Failure Instantaneous Energy:	170	J
Maximum Capacitance @ 120 VAC:	5,557	µf
Maximum Capacitance @ 240 VAC:	1,389	µf
Resistance @ 100% Max Current:		Ω
Resistance @ 50% Max Current:	3.70	Ω
Body Temperature at 100% Max Current:		°c
Dissipation Constant:	32.4	mw/°c
Thermal Time Constant:	94	Sec.
Material Type (for Beta and Curve):	L	

SL22 12102	
Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a