


Automotive Transient Voltage Suppressors

High Temperature Stability & High Reliability Conditions



FEATURES

- Patented PAR[®] construction
- Available in Unidirectional polarity only
- 600 W peak pulse power capability with a 10/1000 μ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Typical I_D less than 1.0 μ A above 10 V rating
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, automotive, and telecommunication.

MECHANICAL DATA

Case: DO-204AC, molded epoxy over passivated junction

Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

HE3 suffix for high reliability grade (AEC Q101 qualified)

Polarity: Color band denotes cathode end

MAJOR RATINGS AND CHARACTERISTICS	
$V_{(BR)}$	6.8 V to 43 V
P_{PPM}	600 W
P_D	5.0 W
I_{FSM}	75 A
T_J max.	185 °C

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 μ s ⁽¹⁾ (Fig. 1)	P_{PPM}	Minimum 600	W
Pulse pulse current with a 10/1000 μ s waveform ⁽¹⁾ (Fig. 3)	I_{PPM}	see next table	A
Power dissipation on infinite heatsink at $T_L = 75$ °C (Fig. 5)	P_D	5.0	W
Peak forward surge current, 8.3 ms single half sine-wave ⁽²⁾	I_{FSM}	75	A
Maximum instantaneous forward voltage at 50 A ⁽²⁾	V_F	3.5	V
Operating junction and storage temperature range	T_J, T_{STG}	- 65 to + 185	°C

Note:

(1) Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25$ °C per Fig. 2

(2) Measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 per minute maximum

ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DEVICE TYPE	BREAKDOWN VOLTAGE $V_{(BR)}^{(1)}$ AT I_T (V)		TEST CURRENT I_T (A)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA)	$T_J = 150\text{ }^{\circ}\text{C}$ MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA)	PEAK PULSE CURRENT $I_{PPM}^{(2)}$ (A)	MAXIMUM CLAMPING VOLTAGE AT I_{PPM} V_C (V)	MAXIMUM TEMP. COEFFICIENT OF $V_{(BR)}$ ($\%/^{\circ}\text{C}$)
	MIN	MAX							
P6KA6.8	6.12	7.48	10	5.50	500	1000	55.6	10.8	0.057
P6KA6.8A	6.45	7.14	10	5.80	500	1000	57.1	10.5	0.057
P6KA7.5	6.75	8.25	10	6.05	250	500	51.3	11.7	0.061
P6KA7.5A	7.13	7.88	10	6.40	250	500	53.1	11.3	0.061
P6KA8.2	7.38	9.02	10	6.63	100	200	48.0	12.5	0.065
P6KA8.2A	7.79	8.61	10	7.02	100	200	49.6	12.1	0.065
P6KA9.1	8.19	10.0	1.0	7.37	25	50	43.5	13.8	0.068
P6KA9.1A	8.65	9.55	1.0	7.78	25	50	44.8	13.4	0.068
P6KA10	9.00	11.0	1.0	8.10	10	20	40.0	15.0	0.073
P6KA10A	9.50	10.5	1.0	8.55	10	20	41.4	14.5	0.073
P6KA11	9.90	12.1	1.0	8.92	5.0	5.0	37.0	16.2	0.075
P6KA11A	10.5	11.6	1.0	9.40	5.0	5.0	38.5	15.6	0.076
P6KA12	10.8	13.2	1.0	9.72	2.0	5.0	34.7	17.3	0.076
P6KA12A	11.4	12.6	1.0	10.2	2.0	5.0	35.9	16.7	0.078
P6KA13	11.7	14.3	1.0	10.5	2.0	5.0	31.6	19.0	0.081
P6KA13A	12.4	13.7	1.0	11.1	2.0	5.0	33.0	18.2	0.081
P6KA15	13.5	16.3	1.0	12.1	1.0	5.0	27.3	22.0	0.084
P6KA15A	14.3	15.8	1.0	12.8	1.0	5.0	28.3	21.2	0.084
P6KA16	14.4	17.6	1.0	12.9	1.0	5.0	25.5	23.5	0.086
P6KA16A	15.2	16.8	1.0	13.6	1.0	5.0	26.7	22.5	0.080
P6KA18	16.2	19.8	1.0	14.5	1.0	5.0	22.6	26.5	0.088
P6KA18A	17.1	18.9	1.0	15.3	1.0	5.0	23.8	25.2	0.088
P6KA20	18.0	22.0	1.0	16.2	1.0	5.0	20.6	29.1	0.090
P6KA20A	19.0	21.0	1.0	17.1	1.0	5.0	21.7	27.7	0.090
P6KA22	19.8	24.2	1.0	17.8	1.0	5.0	18.8	31.9	0.092
P6KA22A	20.9	23.1	1.0	18.8	1.0	5.0	19.6	30.6	0.092
P6KA24	21.6	26.4	1.0	19.4	1.0	5.0	17.3	34.7	0.094
P6KA24A	22.8	25.2	1.0	20.5	1.0	5.0	18.1	33.6	0.094
P6KA27	24.3	29.7	1.0	21.8	1.0	5.0	15.3	39.1	0.096
P6KA27A	25.7	28.4	1.0	23.1	1.0	5.0	16.0	37.5	0.096
P6KA30	27.0	33.0	1.0	24.3	1.0	5.0	13.8	43.5	0.097
P6KA30A	28.5	31.5	1.0	25.6	1.0	5.0	14.5	41.4	0.097
P6KA33	29.7	36.3	1.0	26.8	1.0	5.0	12.6	47.7	0.098
P6KA33A	31.4	34.7	1.0	28.2	1.0	5.0	13.1	45.7	0.098
P6KA36	32.4	39.6	1.0	29.1	1.0	5.0	11.5	52.0	0.099
P6KA36A	34.2	37.8	1.0	30.8	1.0	5.0	12.0	49.9	0.099
P6KA39	35.1	42.9	1.0	31.6	1.0	5.0	10.6	56.4	0.100
P6KA39A	37.1	41.0	1.0	33.3	1.0	5.0	11.1	53.9	0.100
P6KA43	38.7	47.3	1.0	34.8	1.0	5.0	9.7	61.9	0.101
P6KA43A	40.9	45.2	1.0	36.8	1.0	5.0	10.1	59.3	0.101

Note:(1) Pulse test: $t_p \leq 50\text{ ms}$

(2) Surge current waveform per Fig. 3 and derate per Fig. 2

(3) All terms and symbols are consistent with ANSI/IEEE C62.35



ORDERING INFORMATION

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
P6KA6.8AHE3/54	0.415	54	4000	13" Diameter Paper Tape & Reel

RATINGS AND CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. Peak Pulse Power Rating Curve





Figure 2. Pulse Waveform



Pulse Power or Current vs. Initial Junction Temperature




Figure 3. Typical Junction Capacitance




Figure 4. Power Derating Curve





Figure 5. Maximum Non-Repetitive Forward Surge Current

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-204AC (DO-15)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.