



3A Low Dropout Positive Adjustable Regulator

TO-252
(DPak)




GS1085CE

TO-220AB



GS1085CT

TO-263AB
(D²Pak)



GS1085CM


Pin Definition

1. Adjust/Gnd.
2. V_{out} (tab)
3. V_{in}

Features

- Dropout Voltage 1.3V at 3A Output Current
- Fast Transient Response
- Line Regulation typically at 0.015%
- Load Regulation typically at 0.1%
- Internal thermal and current limiting
- Adjustable Output Voltage or Fixed 1.8V, 2.5V, 3.3V
- Standard 3-Pin Power Packages

Functional Block Diagram



Description

The GS1085 is a low dropout three terminal regulator with 3A output current capability. The output voltage is adjustable with the use of a resistor divider. For fixed output voltage versions, the output voltage is internally set at 1.8V, 2.5V, or 3.3V. Dropout is guaranteed at a maximum of 1.4V at maximum output current. Its low dropout voltage and fast transient response make it ideal for low voltage microprocessor applications. Internal current and thermal limiting provides protection against any overload condition that would create excessive junction temperatures.

Applications

- Post Regulator for Switching Supply
- Microprocessor Power Supplies
- Constant-Current Regulators
- Motherboard I/O Power Supplies

Mechanical Data

Case: TO-220AB, TO-263AB (D²PAK), TO-252 (DPAK)

High temperature soldering guaranteed:
260°C/10 seconds at terminals

Case outlines are on the back page

Maximum Ratings and Thermal Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Vin Pin to ADJ/GND Pin	Vin	7	V
Thermal Resistance – Junction to Case TO-220AB TO-252 TO-263AB	$R_{\theta JC}$	3.0 8.0 3.0	$^\circ\text{C/W}$
Operating Junction Temperature Range	T_J	0 to +125	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-65 to 150	$^\circ\text{C}$

Electrical Characteristics ⁽¹⁾ $T_J = 25^\circ\text{C}$ ⁽²⁾ $V_{IN} = 5\text{V}$, $I_O = 10\text{mA}$ unless otherwise noted.



Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Reference Voltage	VREF	$T_J = 25^\circ\text{C}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$ $2.65\text{V} \leq V_{IN} \leq 7\text{V}$ $10\text{mA} \leq I_O \leq 3\text{A}$	1.238 1.225	1.250 1.250	1.262 1.275	V
Output Voltage	VOUT	GS1085-1.8 $V_{IN} = 5\text{V}$ GS1085-2.5 $V_{IN} = 5\text{V}$ GS1085-3.3 $V_{IN} = 7\text{V}$ GS1085 $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$ $2.65\text{V} \leq V_{IN} \leq 5\text{V}$ $10\text{mA} \leq I_O \leq 3\text{A}$	1.78 2.47 3.26 0.98V _N	1.8 2.5 3.3 V _N	1.82 2.53 3.33 1.02V _N	V
Line Regulation	REG _{line}	$2.65\text{V} \leq V_{IN} \leq 7\text{V}$ $T_J = 25^\circ\text{C}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$		0.015 0.035	0.2 0.2	% V _O
Load Regulation	REG _{load}	$10\text{mA} \leq I_O \leq 3\text{A}$ $T_J = 25^\circ\text{C}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$		0.1 0.2	0.3 0.4	% V _O
Dropout Voltage	V _{DROP}	$0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$ $I_O = 3\text{A}$ $I_O = 2\text{A}$ $I_O = 1\text{A}$		1.3 1.28 1.25	1.4 1.37 1.34	V
Output Current	I _O	$0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	3.0	4.0	—	A
Adjust Pin Current	I _{adj}	$2.65 \leq V_{in} \leq 7\text{V}$ $10\text{mA} \leq I_O \leq 3\text{A}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	—	55	120	μA
Adjust Pin Current Change	ΔI_{adj}	$2.65 \leq V_{in} \leq 7\text{V}$ $10\text{mA} \leq I_O \leq 3\text{A}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	—	0.2	5	μA
Temperature Stability	T _S	$I_O = 0.5\text{A}$ $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	—	0.5	—	%V _O
Minimum Load Current Adjustable Version	I _{LMIN}	$0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	—	5	10	mA

Electrical Characteristics(con't.)⁽¹⁾ $T_J = 25^\circ\text{C}$ ⁽²⁾, $V_{IN} = 5\text{V}$, $I_O = 10\text{mA}$ unless otherwise noted.

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Quiescent Current Fixed Voltage Version	I_Q	$0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$	–	10	14	mA
RMS Output Noise	N	$10\text{Hz} \leq f \leq 10\text{kHz}$	–	0.003	–	% V_O
Ripple Rejection Ratio	RR	$f = 120\text{Hz}$, $C_O = 25\mu\text{F}$ $C_{\text{adj}} = 25\mu\text{F}$	60	68	–	dB
Thermal Regulation	R_{TH}	$T_A = 25^\circ\text{C}$, 30ms Pulse	–	0.02	0.05	%/W
Long Term Stability		$T_A = 125^\circ\text{C}$, 1000 Hrs	–	0.3	–	% V_O

Notes:

- (1) All parameters, except nominal output voltage are specified for the variable voltage version, allowing a wider V_{IN} Range.
The specified limits also apply for the fixed voltage versions over the allowable input voltage range: GS1085-1.8 (3.2V - 7.0V), GS1085-2.5 (3.9V - 7.0V), GS1085-3.3 (4.75V - 7.0V).
- (2) To maintain the specified junction temperatures, low duty cycle pulse testing is required for most parameters.

Typical Application Circuit

Fixed Voltage Regulator

Adjustable Voltage Regulator
Notes:

$$V_{REF} = V_{OUT} - V_{ADJ} = 1.25\text{V (typ.)}$$

$$V_{OUT} = V_{REF} \times (1 + R2/R1) + I_{ADJ} \times R2$$

$$I_{ADJ} = 55\mu\text{A (typ.)}$$

(1) $C1$ needed if device is far away from filter capacitors

(2) $C2$ required for stability

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 – Dropout Voltage vs. Output Current




Fig. 2 – Load Regulation vs. Temperature




Fig. 3 – Minimum Load Current (Adjustable Version)




Fig. 4 – Adjust Pin Current




Fig. 5 – Temperature Stability







Fig. 6 – Ripple Rejection (with $C_{adj} 25\mu\text{F}$)




**Ratings and
Characteristic Curves** ($T_A = 25^\circ\text{C}$ unless otherwise noted)**Fig. 7 – Load Transient Response****Fig. 8 – Line Transient Response****Ordering Information****GS1085Cxx xxx**

Output Voltage
Default: Adj.
1.8: 1.8V
2.5: 2.5V
3.3: 3.3V


Package Type
T: TO-220
M: TO-263
E: TO-252

Case Outlines


TO-252 (DPAK)



TO-220



TO-263



Dimensions in millimeters