


1918472

REV

THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON



Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Number of Fibers: 2
Mode: MM
Jacket Diameter: 2.0 mm
Jacket Color: Aqua
FiberType: XG - 50/125

Connector(s): Pigtail - (1.6 to 2.0mm)
Mode: MM
Housing Color: Pigtail
Geom. Spec: N/A

LC strain relief - 1.6 to 2.0 mm cable
Color: Beige/Beige

Pigtail - 1.6 to 2.0 zipcord
Color: Pigtail

Notes:



- 1 Includes dust caps (not shown on print).
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS AFFILIATES. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/3/2006	-		
P	LTR	REVISION	RECORD	DATE	DIN	APVD	



DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
CHK	Cable Assy Configurator	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Refer to Engineering Change				
NAME	FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1918472
SHEET	1 of 3	REV	A		

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.


THIS DRAWING IS A CONTROLLED DOCUMENT.
DWG NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	LC-Duplex, Beige		Pigtail - (1.6 to 2.0mm), Pigtail	
		IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1918472-1	0.950 - 1.050	0.50	N/A	0.00	N/A
0-1918472-2	1.950 - 2.050	0.50	N/A	0.00	N/A
0-1918472-3	2.950 - 3.050	0.50	N/A	0.00	N/A
0-1918472-4	3.920 - 4.080	0.51	N/A	0.01	N/A
0-1918472-5	4.920 - 5.080	0.51	N/A	0.01	N/A
0-1918472-6	5.920 - 6.080	0.51	N/A	0.01	N/A
0-1918472-7	6.920 - 7.080	0.51	N/A	0.01	N/A
0-1918472-8	7.920 - 8.080	0.51	N/A	0.01	N/A
0-1918472-9	8.850 - 9.150	0.51	N/A	0.01	N/A
1-1918472-0	9.850 - 10.150	0.52	N/A	0.02	N/A
1-1918472-1	10.850 - 11.150	0.52	N/A	0.02	N/A
1-1918472-2	11.850 - 12.150	0.52	N/A	0.02	N/A
1-1918472-3	12.850 - 13.150	0.52	N/A	0.02	N/A
1-1918472-4	13.850 - 14.150	0.52	N/A	0.02	N/A
1-1918472-5	14.850 - 15.150	0.52	N/A	0.02	N/A
1-1918472-6	15.840 - 16.160	0.52	N/A	0.02	N/A
1-1918472-7	16.830 - 17.170	0.53	N/A	0.03	N/A
1-1918472-8	17.820 - 18.180	0.53	N/A	0.03	N/A
1-1918472-9	18.810 - 19.190	0.53	N/A	0.03	N/A
2-1918472-0	19.800 - 20.200	0.53	N/A	0.03	N/A
2-1918472-1	20.790 - 21.210	0.53	N/A	0.03	N/A
2-1918472-2	21.780 - 22.220	0.53	N/A	0.03	N/A
2-1918472-3	22.770 - 23.230	0.53	N/A	0.03	N/A
2-1918472-4	23.760 - 24.240	0.54	N/A	0.04	N/A
2-1918472-5	24.750 - 25.250	0.54	N/A	0.04	N/A
2-1918472-6	25.740 - 26.260	0.54	N/A	0.04	N/A
2-1918472-7	26.730 - 27.270	0.54	N/A	0.04	N/A
2-1918472-8	27.720 - 28.280	0.54	N/A	0.04	N/A
2-1918472-9	28.710 - 29.290	0.54	N/A	0.04	N/A
3-1918472-0	29.700 - 30.300	0.55	N/A	0.05	N/A
3-1918472-1	30.690 - 31.310	0.55	N/A	0.05	N/A
3-1918472-2	31.680 - 32.320	0.55	N/A	0.05	N/A
3-1918472-3	32.670 - 33.330	0.55	N/A	0.05	N/A
3-1918472-4	33.660 - 34.340	0.55	N/A	0.05	N/A
3-1918472-5	34.650 - 35.350	0.55	N/A	0.05	N/A
3-1918472-6	35.640 - 36.360	0.55	N/A	0.05	N/A
3-1918472-7	36.630 - 37.370	0.56	N/A	0.06	N/A
3-1918472-8	37.620 - 38.380	0.56	N/A	0.06	N/A
3-1918472-9	38.610 - 39.390	0.56	N/A	0.06	N/A
4-1918472-0	39.600 - 40.400	0.56	N/A	0.06	N/A
5-1918472-0	49.500 - 50.500	0.58	N/A	0.08	N/A

	A	Rev Per EC#	RELEASE	4/3/2006	-		
P	LTR	REVISION RECORD		DATE	DIN	APVD	



TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Customer Print

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT				
CHK		Cable Assy Configurator		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608					
APVD		Refer to Engineering Change							
NAME							FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)		
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1918472	SHEET	2 of 3	REV	A

8

7

6

5

4

3

2

1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8 7 6 5 4 3 2 1

	A	Rev Per EC#	RELEASE	4/3/2006	-	
P	LTR	REVISION RECORD		DATE	DIN	APVD

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .
1 PLC ± .
2 PLC ± .
3 PLC ± .
4 PLC ± .

Customer Print

DIN Cable Assy Configurator		MATERIAL-	HEAT TREAT-		
OK Cable Assy Configurator					
APVD Refer to Engineering Change					
NAME FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)					
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1918472
SHEET		3 of 3		REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1918538-1](#)