


PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	LOCOMOTIVE CONDUCTOR SIZE	BARREL		OVERALL LENGTH "A"	WIRE STRIP LENGTH	PANDUIT PART NUMBERS
			I.D.	O.D.			CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2920 CT-2940*
							DIE PART NO./ DIE SET COLOR & INDEX NO./ NUMBER OF CRIMPS
SCSF8-L	-----	37/24	0.18	0.27	1.50	11/16	CD-920-8 RED P21 1 CRIMP
SCSF6-L	#6 WELD CLASS K & M	61/24	0.22	0.31	1.75	13/16	CD-920-6 BLUE P24 1 CRIMP
SCSF4-L	#4 WELD CLASS K & M	105/24	0.28	0.38	1.75	13/16	CD-920-4 GREY P29 1 CRIMP
SCSF2-E	#2 WELD CLASS K & M	150/24	0.36	0.47	1.87	7/8	CD-920-2 BROWN P33 1 CRIMP
SCSF1-X	#1 WELD CLASS K & M	225/24	0.39	0.52	1.87	7/8	CD-920-1/0 PINK P42 1 CRIMP
SCSF1/0-X	1/0 WELD CLASS K & M	275/24	0.45	0.58	2.50	1-3/16	CD-920-2/0 BLACK P45 2 CRIMPS
SCSF2/0-X	2/0 WELD CLASS K & M	325/24	0.51	0.64	2.50	1-3/16	CD-920-3/0 ORANGE P50 2 CRIMPS
SCSF3/0-X	3/0 WELD CLASS K & M	450/24	0.57	0.71	2.50	1-3/16	CD-920-4/0 PURPLE P54 2 CRIMPS
SCSF4/0-X	4/0 WELD CLASS K & M	550/24	0.63	0.77	2.50	1-3/16	CD-920-250 YELLOW P62 2 CRIMPS
SCSF250-X	250 WELD CLASS K & M	650/24	0.70	0.88	2.50	1-3/16	CD-920-300 WHITE P66 2 CRIMPS
SCSF300-6	300 WELD CLASS K & M	775/24	0.76	0.95	2.56	1-1/4	CD-920-350 RED P71 2 CRIMPS
SCSF350-6	350 WELD CLASS K & M	925/24	0.84	1.06	2.94	1-1/4	CD-920-400 BLUE P76 2 CRIMPS

*CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER



NOTES:

1. MATERIAL: HIGH CONDUCTIVITY SEAMLESS COPPER TUBING
2. ELECTRO -TIN PLATED
3. BARREL COLOR CODED WITH DIE SET INDEX NUMBER
4. UL LISTED WITH LOCOMOTIVE & WELD CABLE CONDUCTORS FOR APPLICATIONS UP TO 35KV, FILE E52164
5. CONSULT CABLE MANUFACTURER FOR VOLTAGE STRESS RELIEF INSTRUCTIONS WITH APPLICATIONS GREATER THAN 2000 VOLTS
6. CSA CERTIFIED FOR APPLICATIONS UP TO 600V, FILE LR31212
7. FOR USE WITH COPPER CABLES ONLY



								<div>PANDUIT CORP. TINLEY PARK, ILLINOIS</div>			
								SCSF #8 - 350 COPPER SPLICES CUSTOMER DRAWING			
02	6/11	JHNU	RGB	REVISED PART NUMBER: SCSF2-E WAS SCSF2-Q	N41158BA-C41158	RGB	RGB	UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
01	4/01	BDK		ADDED THE LETTER "P" TO THE DIE INDEX NUMBER, COMBINED EXISTING TOOL CHART COLUMNS, RELOCATED DIE ADAPTER NOTE, FILESPEC WAS N41158CB_PCD							
00	6/95	WB	WJB	DRAWING RELEASED	03378	KS	LA	DRAWN BY WJB	MAT'L:	SCALE NONE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	DATE 6/95		DRAWING NO / CAD FILE C41158_02	DWG B SIZE
								CHK'D			