

NPN SILICON EPITAXIAL TRANSISTOR
POWER MINI MOLD

2SC3554 is designed for high Voltage Switching application, especially in Hybrid Integrated Circuits.



- World Standard Miniature Package
- High Voltage : $V_{CEO} = 300\text{ V}$

Maximum Voltages and Current ($T_a = 25^\circ\text{C}$)

Collector to Base Voltage	V_{CBO}	300	V
Collector to Emitter Voltage	V_{CEO}	300	V
Emitter to Base Voltage	V_{EBO}	5	V
Collector Current (DC)	I_C	200	mA

Maximum Power Dissipation

Total Power Dissipation at 25°C Ambient Temperature*	P _T	2.0	W
---	----------------	-----	---

Maximum Temperatures

Junction Temperature	T _j	150	°C
Storage Temperature Range	T _{stg}	−55 to +150	°C

*When mounted on ceramic substrate of 16 cm² x 0.7 mm

ELECTRICAL CHARACTERISTICS ($T_a = 25^\circ\text{C}$)







ELECTRICAL CHARACTERISTICS ($T_a = 25^\circ\text{C}$)						
CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS
Collector Cutoff Current	I_{CBO}			100	nA	$V_{CB} = 200\text{ V}, I_E = 0$
Emitter Cutoff Current	I_{EBO}			100	nA	$V_{EB} = 5.0\text{ V}, I_C = 0$
DC Current Gain	h_{FE}^{**}	60	150	250		$V_{CE} = 10\text{ V}, I_C = 10\text{ mA}$
Collector Saturation Voltage	$V_{CE(sat)}^{**}$		0.15	1.5	V	$I_C = 50\text{ mA}, I_B = 5.0\text{ mA}$
Gain Bandwidth Product	f_T		50		MHz	$V_{CE} = 30\text{ V}, I_E = -10\text{ mA}$
Output Capacitance	C_{ob}		2.8	3.5	pF	$V_{CB} = 30\text{ V}, I_E = 0, f = 1.0\text{ MHz}$


****Pulsed: PW $\leq 350 \mu s$, Duty Cycle $\leq 2 \%$**

h_{FE} Classification

MARKING	SM	SL	SK
hFE	60 to 120	100 to 200	160 to 250

TYPICAL CHARACTERISTICS ($T_a = 25^\circ\text{C}$)





REFERENCE

Document Name	Document No.
NEC semiconductor device reliability/quality control system.	TEI-1202
Quality grade on NEC semiconductor devices.	IEI-1209
Semiconductor device mounting technology manual.	IEI-1207
Semiconductor device package manual.	IEI-1213
Guide to quality assurance for semiconductor devices.	MEI-1202
Semiconductor selection guide.	MF-1134

[MEMO]

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.

The devices listed in this document are not suitable for use in aerospace equipment, submarine cables, nuclear reactor control systems and life support systems. If customers intend to use NEC devices for above applications or they intend to use "Standard" quality grade NEC devices for applications not intended by NEC, please contact our sales people in advance.

Application examples recommended by NEC Corporation

Standard: Computer, Office equipment, Communication equipment, Test and Measurement equipment, Machine tools, Industrial robots, Audio and Visual equipment, Other consumer products, etc.

Special: Automotive and Transportation equipment, Traffic control systems, Antidisaster systems, Anticrime systems, etc.