

2N4401 & 2N4403

General Purpose Switching Transistors




Features:

- NPN/PNP Silicon Planar Epitaxial Transistors.
- General purpose Switching Applications.
- 2N 4401 Type NPN.
- 2N 4403 Type PNP.



2N4401 NPN 2N4403 PNP

TO-92



Dimensions	Minimum	Maximum
A	4.32	5.33
B	4.45	5.20
C	3.18	4.19
D	0.41	0.55
E	0.35	0.50
F	5°	
G	1.14	1.40
H		1.53
K	12.70	-
L	1.982	2.082

Dimensions : Millimetres



Pin Configuration

- 1 = Emitter
- 2 = Base
- 3 = Collector



2N4401 & 2N4403

General Purpose Switching Transistors



Absolute Maximum Ratings

Parameters	Symbol	2N4401	2N4403	Unit
Collector Emitter Voltage	V _{CEO}	40	40	V
Collector Base Voltage	V _{CBO}	60		
Emitter Base Voltage	V _{EBO}	6	5	
Collector Current Continuous	I _C	600		mA
Power Dissipation at T _a = 25°C Derate above 25°C	P _D	625 5.0		mW mW/°C
Power Dissipation at T _C = 25°C Derate above 25°C		1.5 12		W W/°C
Operating and Storage Junction Temperature Range	T _j , T _{stg}	-55 to +150		°C
Thermal Resistance				
Junction to Case	Rth _(j-c)	83.3		°C/W
Junction to Ambient	Rth _(j-a)	200		

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Parameters	Symbol	Test Condition	2N4401	2N4403	Unit
Collector Emitter Voltage	BV_{CEO}^*	$I_C = 1\text{mA}, I_B = 0$	>40	>40	V
Collector Base Voltage	BV_{CBO}	$I_C = 100\mu\text{A}, I_E = 0$	>60		
Emitter Base Voltage	BV_{EBO}	$I_E = 100\mu\text{A}, I_C = 0$	>6	>5	
Base Cut off Current	I_{BEV}	$V_{CE} = 35\text{V}, V_{EB} = 0.4\text{V}$	<0.1	<0.1	μA
Collector Cut off Current	I_{CEX}	$V_{CE} = 35\text{V}, V_{EB} = 0.4\text{V}$			
Collector Emitter Saturation Voltage	$V_{CE(Sat)}^*$	$I_C = 150\text{mA}, I_B = 15\text{mA}$ $I_C = 500\text{mA}, I_B = 50\text{mA}$	<0.4 <0.75	<0.4 <0.75	V
Base Emitter Saturation Voltage	$V_{BE(Sat)}^*$	$I_C = 150\text{mA}, I_B = 15\text{mA}$ $I_C = 500\text{mA}, I_B = 50\text{mA}$	0.75 - 0.95 <1.2	0.75 - 0.95 <1.3	
DC Current Gain	h_{FE}	$I_C = 0.1\text{mA}, V_{CE} = 1\text{V}$ $I_C = 1\text{mA}, V_{CE} = 1\text{V}$ $I_C = 10\text{mA}, V_{CE} = 1\text{V}$ $I_C = 150\text{mA}, V_{CE} = 1\text{V}^*$ $I_C = 150\text{mA}, V_{CE} = 2\text{V}^*$ $I_C = 500\text{mA}, V_{CE} = 2\text{V}^*$	>20 >40 >80 100 - 300 - >40	>30 >60 >100 - 100 - 300 >20	-
Dynamic Characteristics					
Small Signal Current Gain	h_{fe}	$I_C = 1\text{mA}, V_{CE} = 10\text{V}, f = 1\text{kHz}$	40 - 500	60 - 500	-
Input Impedance	h_{ie}	$I_C = 1\text{mA}, V_{CE} = 10\text{V}, f = 1\text{kHz}$	1.0 - 15	1.5 - 15	k Ω

*Pulse Test : Pulse Width: $\leq 300\mu\text{s}$, Duty $\leq 2.0\%$



2N4401 & 2N4403


General Purpose Switching Transistors




Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Parameters	Symbol	Test Condition	2N4401	2N4403	Unit
Voltage Feedback Ratio	h_{re}	$I_C = 1\text{mA}$, $V_{CE} = 10\text{V}$, $f = 1\text{kHz}$	0.1 - 8.0		$\times 10^{-4}$
Output Impedance	h_{oe}	$I_C = 1\text{mA}$, $V_{CE} = 10\text{V}$, $f = 1\text{kHz}$	1.0 - 30	1.0 - 100	$\mu\Omega$
Collector-Base Capacitance	C_{cb}	$V_{CB} = 5\text{V}$, $I_E = 0$, $f = 100\text{kHz}$ $V_{CB} = 10\text{V}$, $I_E = 0$, $f = 140\text{kHz}$	<6.5 -	- <8.5	pF
Emitter-Base Capacitance	C_{eb}	$V_{EB} = 0.5\text{V}$, $I_C = 0$, $f = 100\text{kHz}$ $V_{EB} = 0.5\text{V}$, $I_C = 0$, $f = 140\text{kHz}$	<30 -	- <30	
Transition Frequency	f_T	$I_C = 20\text{mA}$, $V_{CE} = 10\text{V}$, $f = 100\text{MHz}$	>250	>200	MHz
Switching Characteristics					
Delay Time	t_d	$V_{CC} = 30\text{V}$, $V_{EB} = 2\text{V}$ $I_C = 150\text{mA}$, $I_{B1} = 15\text{mA}$	<15		ns
Rise Time	t_r		<20		
Storage time	t_s	$V_{CC} = 30\text{V}$, $I_C = 150\text{mA}$ $I_{B1} = I_{B2} = 15\text{mA}$	<225		
Fall Time	t_f		<30		

DC Current Gain



DC Current Gain




2N4401 & 2N4403


General Purpose Switching Transistors




On Voltages



DC Current Gain



Collector Saturation Region




2N4401 & 2N4403

General Purpose Switching Transistors



On Voltages



Specifications

V_{CEO} maximum (V)	V_{CBO} maximum (V)	I_C (A)	h_{FE} minimum at $I_C = 1\text{mA}$	f_T minimum (MHz)	P_{tot} (mW)	Package and Pin Out	Type	Part Number
40	40	0.6	100	250	625	TO-92	NPN	2N4401
	60			200			PNP	2N4403

2N4401 & 2N4403

General Purpose Switching Transistors



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

