



NO. OF CKTS	DIM B	DIM A
2	2.54 ± 0.05	4.83 ± 0.20
3	5.08 ± 0.13	7.37 ± 0.20
4	7.62 ± 0.13	9.91 ± 0.20
5	10.16 ± 0.13	12.45 ± 0.20
6	12.70 ± 0.15	14.99 ± 0.23
7	15.24 ± 0.15	17.53 ± 0.23
8	17.78 ± 0.15	20.07 ± 0.23
9	20.32 ± 0.18	22.61 ± 0.25
10	22.86 ± 0.18	25.15 ± 0.25
11	25.40 ± 0.18	27.69 ± 0.25
12	27.94 ± 0.20	30.23 ± 0.28
13	30.48 ± 0.20	32.77 ± 0.28
14	33.02 ± 0.20	35.31 ± 0.28
15	35.56 ± 0.20	37.85 ± 0.28
16	38.10 ± 0.20	40.39 ± 0.28



- NOTES:
1. MATERIAL: NYLON, UL 94V-0, COLOR: WHITE
 2. FINISH:
 - (241) SELECT GOLD: 0.00051 MIN.
 - SELECT TIN: 0.00254 MIN.
 - OVERALL NICKEL UNDERPLATE: 0.00127 MIN.
 - (197) OVERALL REFLOWED MATTE TIN: 0.00152 MIN.
 - OVER 0.00127 MIN. NICKEL OVERALL.
 3. PARTS CONFORM TO PRODUCT SPECIFICATION PS-10-07.
 4. PACKAGING INFORMATION: SEE LEGEND.
 5. PINS MUST CONFORM TO SOLDERABILITY SPECIFICATION SMES-152.
 6. PIN PUSHOUT FORCE: 2 LBS. MIN.
 7. PARTS ARE STACKABLE END TO END AND SIDE TO SIDE ON (2.54)/.100 CENTERS.
 8. PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
 9. TEXT ON PART IS FOR REFERENCE ONLY. TEXT AND TEXT LOCATION MAY VARY DEPENDING ON PART NUMBER AND/OR TOOL.
 10. CIRCUIT 1 DESIGNATION IS USED TO DEFINE VOID LOCATION. CIRCUIT 1 MAY OR MAY NOT ALIGN TO CIRCUIT 1 ON THE MATING HOUSING

A - 4 0 9 4 - N * * * - *

NO. OF CKTS.

VERSION

LETTER CHANGES WHEN PIN NO. OR PRESS DIM. CHANGES.

PLATING CODE

SEE NOTE 2

VOID CODE	
BLANK = NO VOIDS	
NO. = CIRCUIT NO. VOIDED	
MULTIPLE VOIDS START WITH 51	
SECONDARY OPERATIONS	
CODE	PACKAGE
BLANK	BULK PER PK-4094-001

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE		CURRENT REV DESC:				molex WAFER ASSY FLAT MINI KK (4030 WITH BENT PINS) 4094 SERIES DRAWING					
MM	NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)												
	MM	INCH										
4 PLACES	±	±	EC NO: 637111				PRODUCT CUSTOMER DRAWING					
3 PLACES	±	±	DRWN: YVENKATESWAR 2020/05/06									
2 PLACES	±	±	CHK'D: YVENKATESWAR 2020/05/07									
1 PLACE	±	±	APPR: ISHWARG 2020/05/07									
0 PLACES	±	±	INITIAL REVISION:									
ANGULAR TOL ± 0.5 °			DRWN: KSS 1984/09/10									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			APPR: FSMITH 2014/08/05									
THIRD ANGLE PROJECTION			DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER					
			C-SIZE	4094	SEE TABLE	GENERAL MARKET	1 OF 3					

DOCUMENT NUMBER

SDA-4094

DOC TYPE

PSD

DOC PART

001

REVISION

AE6

DOCUMENT STATUS	P1	RELEASE DATE	2020/05/07	03:14:39
-----------------	----	--------------	------------	----------

A-4094-NA197		
PART NO.	ENG. NO.	VOID CIRCUIT
22-05-2021	A-4094-2A197	
22-05-2031	A-4094-3A197	
22-05-2041	A-4094-4A197	
22-05-2051	A-4094-5A197	
22-05-2061	A-4094-6A197	
22-05-2071	A-4094-7A197	
22-05-2081	A-4094-8A197	
22-05-2091	A-4094-9A197	
22-05-2101	A-4094-10A197	
22-05-2111	A-4094-11A197	
22-05-2121	A-4094-12A197	
22-05-2131	A-4094-13A197	
22-05-2141	A-4094-14A197	
22-05-2151	A-4094-15A197	
22-05-2161	A-4094-16A197	
22-05-5050	A-4094-5A197-3	3

A-4094-NA241		
PART NO.	ENG. NO.	VOID CIRCUIT
22-12-2021	A-4094-2A241	
22-12-2031	A-4094-3A241	
22-12-2041	A-4094-4A241	
22-12-2051	A-4094-5A241	
22-12-2061	A-4094-6A241	
22-12-2071	A-4094-7A241	
22-12-2081	A-4094-8A241	
22-12-2091	A-4094-9A241	
22-12-2101	A-4094-10A241	
22-12-2111	A-4094-11A241	
22-12-2121	A-4094-12A241	
22-12-2131	A-4094-13A241	
22-12-2141	A-4094-14A241	
22-12-2151	A-4094-15A241	
22-12-2161	A-4094-16A241	
22-19-2054	A-4094-5A241-2	2

A-4094-NAJ197	
PART NO.	ENG. NO.
	A-4094-2AJ197
22-05-3038	A-4094-3AJ197
22-05-3048	A-4094-4AJ197
22-05-3058	A-4094-5AJ197
22-05-3068	A-4094-6AJ197
22-05-3078	A-4094-7AJ197
22-05-3088	A-4094-8AJ197
22-05-3098	A-4094-9AJ197
22-05-3108	A-4094-10AJ197
22-05-3118	A-4094-11AJ197
22-05-3128	A-4094-12AJ197
22-05-3138	A-4094-13AJ197
22-05-3148	A-4094-14AJ197
22-05-3158	A-4094-15AJ197
22-05-3168	A-4094-16AJ197


A-4094-NAP197	
PART NO.	ENG. NO.
22-05-3022	A-4094-2AP197
22-05-3032	A-4094-3AP197
22-05-3042	A-4094-4AP197
22-05-3052	A-4094-5AP197
22-05-3062	A-4094-6AP197
22-05-3072	A-4094-7AP197
22-05-3082	A-4094-8AP197
22-05-3092	A-4094-9AP197
22-05-3102	A-4094-10AP197
22-05-3112	A-4094-11AP197
22-05-3122	A-4094-12AP197
22-05-3132	A-4094-13AP197
22-05-3142	A-4094-14AP197
22-05-3152	A-4094-15AP197
22-05-3162	A-4094-16AP197

A-4094-NBT197	
PART NO.	ENG. NO.
22-05-3020	A-4094-2BT197
22-05-3030	A-4094-3BT197
22-05-3040	A-4094-4BT197
22-05-3050	A-4094-5BT197
22-05-3060	A-4094-6BT197
22-05-3070	A-4094-7BT197
22-05-3080	A-4094-8BT197
22-05-3090	A-4094-9BT197
22-05-3100	A-4094-10BT197
22-05-3110	A-4094-11BT197
22-05-3120	A-4094-12BT197
22-05-3130	A-4094-13BT197
22-05-3140	A-4094-14BT197
22-05-3150	A-4094-15BT197
22-05-3160	A-4094-16BT197

A-4094-NDS197	
PART NO.	ENG. NO.
22-06-3021	A-4094-2DS197
22-06-3031	A-4094-3DS197
22-06-3041	A-4094-4DS197
22-06-3051	A-4094-5DS197
22-06-3061	A-4094-6DS197
22-06-3071	A-4094-7DS197
22-06-3081	A-4094-8DS197
22-06-3091	A-4094-9DS197
22-06-3101	A-4094-10DS197
22-06-3111	A-4094-11DS197
22-06-3121	A-4094-12DS197
22-06-3131	A-4094-13DS197
22-06-3141	A-4094-14DS197
22-06-3151	A-4094-15DS197
22-06-3161	A-4094-16DS197

A-4094-NAA197	
PART NO.	ENG. NO.
	A-4094-2AA197
	A-4094-3AA197
	A-4094-4AA197
	A-4094-5AA197
46999-0606	A-4094-6AA197
46999-0650	A-4094-7AA197
	A-4094-8AA197
	A-4094-9AA197
	A-4094-10AA197
	A-4094-11AA197
	A-4094-12AA197
	A-4094-13AA197
	A-4094-14AA197
	A-4094-15AA197
	A-4094-16AA197

[illegible][illegible]

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex									
INCH		NTS															
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 637111 DRWN: YVENKATESWAR 2020/05/06 CHK'D: YVENKATESWAR 2020/05/07 APPR: ISHWARG 2020/05/07				WAFER ASSY FLAT MINI KK (4030 WITH BENT PINS) 4094 SERIES DRAWING									
		MM												INCH			
4 PLACES		±		±		INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
3 PLACES		±		±													
2 PLACES		±		0.13		±		PRODUCT CUSTOMER DRAWING									
1 PLACE		±		0.25		±											
0 PLACES		±				±		SDA-4094				PSD		001		AE6	
ANGULAR TOL				±		0.5 °											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
						C-SIZE		4094		SEE TABLE		GENERAL MARKET		3 OF 3			

FORMAT: Eng-lega-master-ib-prod-C REVISION: D	12	11	10
--	----	----	----