


F
E
D
C
B
A



RECOMMENDED
CABLE STRIPPING DIM'S

NOTES. FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
3. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK
OVER COPPER STRIKE
4. TEFLON MIL-P-19468
5. JIS H 3250, C 2700

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

						DIMENSIONS ARE IN MILLIMETERS				PART NO.		Amphenol		
5	FERRULE	NOTE 5	NOTE 2	1	FR-39/32X95	UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				FME1121A4-NT3G-5-50				
4	CONTACT PIN	NOTE 1	NOTE 3	1	FME1121A4-4-15/06					APPROVED			DATE	
3	LOCK RING	NOTE 1	NOTE 2	1	FME1121A3-3-B					CHECKED			DATE	
2	INSULATOR	NOTE 4	NATURAL	1	FME1121A4-2T-50									
1	BODY	NOTE 1	NOTE 2	1	FME1121A4-1-27/17					DRAWN		DATE		
										10-11-01'		TITLE		
												FME CRIMP PLUG (FOR RG-174/U,188A/U,316/U)		
												DRAWING NO.	KJ-FME1121A4-NT3G-316U-50	
												ITEM NO.		
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	4/1	ISSUE	A	FILE NO.				