







Horizontal 975H Series	In-line 1550 Series	Vertical 1700 Series
● Block double decker sockets ● 5.0mm pitch ● In-line pins ● Closed ends 	● Plug-in header ● 3.81mm pitch ● Rising clamp mechanism 	● Plug-in header ● 3.81mm pitch ● Rising clamp mechanism 
Part number 20.975H/** Number of poles 2-24 poles **Insert required No. of poles	Part number 21.1550/** Number of poles 2-20 poles **Insert required No. of poles	Part number 21.1700/** Number of poles 2-20 poles **Insert required No. of poles
Ratings		
   UL 1059 CSA 22.2 No.158 DIN VDE 0627 Rated voltage 300 V 300 V 250 V Rated current 15 A 15 A 12 A (T60) Rating impulse voltage/dirt level 4.0 kV/3	   UL 1059 CSA 22.2 No.158 DIN VDE 0627 Rated voltage 300 V 300 V 160 V Rated current 8 A 8 A 9 A (T60) Wire size AWG 28-16 AWG 28-16 1.5mm ² Rating impulse voltage/dirt level 4.0 kV/3 Rated torque/screw size 0.4 Nm/M2	   UL 1059 CSA 22.2 No.158 DIN VDE 0627 Rated voltage 300 V 300 V 160 V Rated current 8 A 8 A 9 A (T60) Wire size AWG 28-16 AWG 28-16 1.5mm ² Rating impulse voltage/dirt level 4.0 kV/3 Rated torque/screw size 0.4 Nm/M2
Maximum rated cross section		
	Single wire (solid) 1.5mm ² Stranded wire (flexible) 1.0mm ² Stranded wire with ferrules 1.0mm ²	Single wire (solid) 1.5mm ² Stranded wire (flexible) 1.0mm ² Stranded wire with ferrules 1.0mm ²
Materials		
Insulating material PA Flammability class UL94 V-0 Temperature range -30°C/+105°C Contact PIN Cu Colour Green RAL 6018	Insulating material PA Flammability class UL94 V-0 Temperature range -30°C/+105°C Terminal block CuZn Contact CuSn Colour Green RAL 6018	Insulating material PA Flammability class UL94 V-0 Temperature range -30°C/+105°C Terminal block CuZn Contact CuSn Colour Green RAL 6018
Dimensions		
Spacing 5.0mm PCB hole diameter 1.4mm 	Spacing 3.81mm (3.5mm) Stripped length 7.0mm 	Spacing 3.81mm Stripped length 7.0mm 
Options:	Options: ● 3.5mm pitch ● Printed terminals ● Coding	Options: ● Printed terminals ● Coding