





LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A		REVISED PER ECO-12-018102	11OCT2012	MGM	CT	
		B		ECO-13-004759	01APR2013	KG	DH	
		C		REVISED PER ECO-14-014385	20NOV14	MGM	CT	



- 1 MATERIAL:
CONTACT - COPPER ALLOY
HOUSING - LCP, COLOR - BLACK
- 2 FINISH:
MATING AREA: 1.27μm MIN GOLD OVER
1.25μm MIN NICKEL
- 3 FINISH:
COMPLIANT PIN AREA: 0.38μm MIN BRIGHT TIN LEAD
OVER 1.27μm MIN NICKEL
- 4 FINISH:
COMPLIANT PIN AREA: 0.38μm MIN MATTE TIN
OVER 1.27μm MIN NICKEL
- 5 --
- 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7 REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATING THRU HOLE DIAMETER AND PLATING THICKNESS.
- 8 RECOMMENDED DIFFERENTIAL PAIR CONFIGURATION SHOWN.
THE CONNECTOR UTILIZES AN OPEN PIN FIELD AND
CAN BE LAID OUT IN A SINGLE-ENDED CONFIGURATION.

2 4	2102093-2
2 3	2102093-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009			DWN D. BELACK 24NOV2010		 TE Connectivity	
DIMENSIONS: mm			CHK A. TSANG			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD M. McALONIS		NAME Fortis Zd. 2-PAIR, 10-COLUMN, VERTICAL, CENTER MODULE ASSEMBLY	
0 PLC ±.013			PRODUCT SPEC 108-2409			
1 PLC ±.013			APPLICATION SPEC 114-13267			
2 PLC ±.013			WEIGHT ~ 2.40 g			
3 PLC ±.013			CUSTOMER DRAWING			
4 PLC ±.013			SCALE 10:1			
ANGLES ±.2°			SHEET 1 OF 1			
FINISH -			REV C			