

Comb busbars, connectors and assembled terminals



14881

Application for Comb busbar C60H

When fed by a single cable per phase the busbar is rated 100A at 40°C.
If two connections (i.e. two cables) are used per phase the rating is increased to 120A. Short circuit rating compatible with the breaking capacity of the MCBs fitted.
Short time ratings: 10kA for 30ms, 1800A for 1 second. Suitable for use with all Merlin Gerin MCBs with 18mm width poles (C60HB/HC/HD).

Technical data

Rated operational voltage 500V. Complies with BS EN 60439-1


- Fully insulated for protection against direct contact
- Supplied with insulated end covers
- Main connection: 16mm² direct 25mm² via connectors part n°. **14885**

Type suitable for C60H and STI	Part N°.
1P 1 row of 12 - 1P MCBs (12)	14881
1 row of 54 - 1P MCBs (54)	14801
2 row of 24 - 1P MCBs (24)	14891
2P 1 row of 6 - 2P MCBs (6)	14882
1 row of 27 - 2P MCBs (27)	14802
2 row of 12 - 2P MCBs (24)	14892
3P 1 row of 4 - 3P MCBs (4)	14883
1 row of 18 - 3P MCBs (18)	14803
2 row of 8 - 3P MCBs (16)	14893
4P 1 row of 3 - 4P MCBs (3)	14884
1 row of 13 - 4P MCBs (13)	14804
2 row of 6 - 4P MCBs (12)	14894
Cable connectors - pack of 4	14885

Type suitable for DPN	Part N°.
1P+N 1 row of 13 MCBs	14880
2 row of 12 - 24 MCBs	14890

Type suitable for C120 NG125	Part N°.
1P 16 MCBs	14811
2P 8 MCBs	14812
3P 5 MCBs	14813
4P 4 MCBs	14814
Set of 20 boots for unused teeth	14818

Accessories	Part N°.
Set of 40 ends caps	
for 1P and 2P combs	14886
for 3P and 4P combs	14887
Set of 40 boots for unused teeth	14888



13514

Stepped terminals 125/140A (40°C) Installation

- Clipping on to Multifix or symmetrical rails
- Screwing on to plain or slotted plates, Multifix rails or asymmetrical rails

Terminals with holes 125A

	Isc (kA rms) 415V	Part N°.
4 x 10 holes (5 x 10 mm ²) + (4 x 16 mm ²) + (1 x 35 mm ²)	3.5kA/1s	13512
4 x 17holes (8 x 10 mm ²) + (8 x 16 mm ²) + (1 x 35 mm ²)	3.5kA/1s	13514
Terminals with clamps	10kA/1s	14949
140A 4 x 12 holes (12 clamps 6 mm ²)		



07105

Distribloc 125 and 160A

4 pole distribution block comprising:

- A fully insulated, one piece distribution system complying with IPXXB (protection against direct contact)
- A modular cover designed for a 45mm panel slot for integration in a row of DIN rail mounted modular products

Technical data

- $U_i = 690V$, $I_{cw} = 4.5kA/1s$ to IEC947-7-1
- **Peak withstand current:** $I_{pk} = 20kA$ to IEC439-1
- **Rated impulse withstand voltage:** $U_{imp} = 8kV$

Type	Part N°.
Distribloc 125	07105
Distribloc 160	07106
35mm ² x 210	07054 4 flexible connections

Cable capacity		
Distribloc 125	Incoming	6 - 35mm ² flexible or 10 - 35mm ² rigid cables
Distribloc 160	Incoming	Flexible cable links fitted to device
Distribloc 125 & 160	Outgoing	Per pole: 2 x 10mm ² 3 x 6mm ² 7 x 4mm ² 1 x 25mm ² (16mm ² multicore)