



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Drawings
 - PDFFiber Optic ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'F5D2-3M1'

Your search criteria matched only one product, shown below

F5D2-3M1Y



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F5D2-3M1Y
RoHS Compliancy Status	Intended for use in fixed installations which are outside the scope of RoHS
Note	F5D2-3M1Y replaces F5D2-3M1
Part Description	ST to SC multimode duplex patch cord, 3mm jacketed cable (two ST connectors on one end and one duplex SC connector on the other end)- 50/125µm.
Product Type	Hybrid Patch Cords
Length (m)	1
Fiber Compatibility	50/125µm
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Connector 1 Type	ST Connector
Connector 2 Type	SC Connector
End Configurations	ST to SC
Fiber Count	2
Flammability Rating	Riser (OFNR)
Pricing Description	PC ST To SC 50µm 1m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.