






**UNCONTROLLED
DOCUMENT**

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	150 Ω	280 Ω	400 Ω
Minimum	- Ω	224 Ω	- Ω




AGILENT E4991A Impedance/Material Analyzer
HP 16082A Test Fixture REF #3188

FERRITE CORE DIMENSIONS (SPEC): mm/inches

A	15.88 [.625]	+	0.30 [.012]
B	7.87 [.310]	+	0.15 [.006]
C	28.58 [1.125]	+	0.76 [.030]

WEIGHT/1000 20.66 kgs [45.55 Lbs]

SCALE DRAWING 1:1



28B0625-100

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. PROJECT/PART NUMBER: 28B0625-100 DATE: 09/24/93 CAD # 28B0625-100-K SCALE: 2 : 1 TOOL # B0625 MATERIAL: Ni Zn Ferrite
K	UPDATE CO. LOGO CHG CHAMFER DESIGN	03/20/09	JRK	
J	UPDATE Z SPEC AND COMPANY LOGO	06/06/07	JRK	
H	UPDATE MIN Z SPEC @100 MHZ	09/26/06	JRK	
G	UPDATE Z SPEC ADD TEST REF#	12/06/04	JRK	
F	REMOVE COATINGS CHANGE P/N UPDATE PRINT FORMAT & Z SPECS	03/26/03	JRK	
E	UPDATE PRINT FORMAT FOR ELECTRONIC DATABASE ADD DETAIL "A", UPDATE Z SPEC FORMAT CORRECTED P/Ns ON CORE DIMENSIONS AND NOTES	02/26/01	TMB	
D	ADD WHITE COATING, UPDATE DIM FORMAT	04/03/00	JAJ	
REV	DESCRIPTION	DATE	INT	

Laird
TECHNOLOGIES