




LOC	DIST	REVISIONS				
AJ	00	P	LTR	DESCRIPTION	DATE	DWN
			B1	REVISED PER ECO-11-005030	11MAR11	RK
				APVD		HMR

D

C

B

A



PCB CONFIGURATION

- 1 ZINC PER ASTM B 86.
- 2 BERYLLIUM COPPER PER ASTM B 196.
- 3 PTFE PER ASTM B 1710.
- 4 NICKEL PLATE PER QQ-N-290, $3.81 \mu\text{m}$ [$.000150$] MINIMUM THICK.
- 5 TIN PLATE PER ASTM B 545, $3.04 \mu\text{m}$ [$.000120$] MINIMUM THICK, OVER NICKEL PLATE PER MIL-C-26074, $7.62 \mu\text{m}$ [$.000300$] MINIMUM THICK.
- 6 GOLD PLATE PER ASTM B 488, $1.27 \mu\text{m}$ [$.000050$] MINIMUM THICK.
- 7. INTERFACE PER MIL-C-39012.
- 8 GOLD PLATE PER ASTM B 488, $0.76 \mu\text{m}$ [$.000030$] MINIMUM THICK.
- 9 POLYMETHYLPENTENE: GENERAL PURPOSE.

	4.34 [.171]			5413558-5
	3.33 [.131]			5413558-3
	4.34 [.171]			5413558-2
	4.34 [.171]			5413558-1
FRONT DIELECTRIC MATERIAL	A	CONTACT FINISH	SHELL FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	22APR2005	TE Connectivity	
		CHK	22APR2005		
		APVD	22APR2005	NAME	
		PRODUCT SPEC	108-12078	JACK, RIGHT ANGLE, PCB, 75 OHM, SERIES BNC	
		APPLICATION SPEC			
		WEIGHT	-	SIZE	RESTRICTED TO
		CUSTOMER DRAWING	A2	CAGE CODE	REV
		SCALE	4:1	SHEET	B1