



Seamless Hubbell System Integration.

Universal Keystone Design fits into all Hubbell Products.


USB 2.0 Performance.

Reversible A and B Interface.


HUBBELL iStation Audio Video Connectors, USB

Low-profile footprint.

Quick and easy connection installation.



Type A-to-A




Type A-to-B

High impact, flame-retardant polymer.

SPECIFICATIONS

- ◆ **Performance:**
 - Type: 2.0
 - Performance: 480 Mbps
 - Mating Cycles: 500+
 - Maximum Distance: 5 Meters
- ◆ **Material:**
 - Housing: Flame Retardant Polymer Rated UL 94V-0.
- ◆ **Cable Type:** standard USB A and B patch cord connections.
- ◆ **Connector Type:** Standard A and B footprint.



WIRING SPECIFICATIONS

USB signals are transmitted on a twisted pair of data cables, labelled D+ and D-. These collectively use half-duplex differential signaling to combat the effects of electromagnetic noise on longer lines. Transmitted signal levels are 0.0-0.3 volts for low and 2.8-3.6 volts for high.

Pin	Function
1	V(USB (4.75-5.25V))
2	D-
3	D+
4	GND
Shell	Shield

Hubbell's USB 2.0 AV Connectors provide a perfect solution for connecting computer peripherals to a computer workstation, requiring just a plug 'n play patch cord connection. Hubbell's USB-connectors install into standard Hubbell keystone products providing a clean, aesthetic look, integrating all applications into one space.

Hubbell's USB 2.0 AV Connectors are reversible in the AB version. Just simply face which connection you desire on the front of the plate and snap it in. Available in three colors: Office White, White and Blue, these connectors flush mount into **iSTATION™** face plates, modules, frames, poke-throughs, raceway, delivery and UDX multimedia panels.

Create a customized multimedia workstation by adding a USB 2.0 Connector along with Hubbell's extensive line of AV connectors, loaded modules and **XCELERATOR™** jacks.

APPLICATIONS SUPPORTED

- ▲ Connecting peripherals to a computer(s):
 - KVM, keyboards, mouse devices, printers, scanners, external storage, and networking components.
 - PDAs, phones, MP3 players, gamepads and joysticks, digital voice recorders, digital cameras and video recorders.

INSTALLATION TIPS

Important: Always allow for clearance behind connection location to ensure for proper bend radius and patch cord connector depth.


NOTE: USB maximum connection length may not exceed 5 meters, non-active. With amplification, follow manufactures specifications.

CONNECTOR TERM



Universal Serial Bus (USB) is a serial bus standard to interface devices. It was originally designed for personal computers, but it has become commonplace on scanners, printers, handheld devices such as portable memory devices, video game consoles, PDAs and portable media players. USB is also used extensively to connect non-networked devices, replacing the parallel ports that had previously been in wide use; USB simplifies connecting several devices to one computer.

iSTATION™ USB 2.0 AV Connectors



Color	Format: A-to-A	Format: A-to-B
Blue	Catalog No. SFUSBAAB	Catalog No. SFUSBABB
Office White	SFUSBAAOW	SFUSBABOW
White	SFUSBAAW	SFUSBABW

CONNECTOR DEPTH CHART**DIMENSIONS**

Type A




Type B

**iSTATION™ COMPATIBLE****Work Station and Cross-Connect Solutions**

- Front and Rear-loading Plates
- Duplex and Decorator Frames
- ISM Surface Mount Boxes
- UDX Multimedia Panels (except 1U-48)
- **netSELECT™**: Residential Network Solution
- **iFRAME™** Vertical Patch Panel

**Hubbell Delivery System**

- Hubbell **SystemOne** Poke-Throughs and Floor Boxes
- Hubbell Surface Raceway, Metal and Non-Metallic
- Multi-Connect™ Wall Boxes/Conference Table Boxes
- Power Poles

**TYPICAL APPLICATION**

Patch Cords
Horizontal Cable



RCA AV module/
connector in a Hubbell
iSTATION™ face plate.

**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
Hubbell Canada Inc.
Hubbell Premise Wiring, Central America
Hubbell Premise Wiring, China
Hubbell Premise Wiring, Europe
Hubbell Premise Wiring, India
Hubbell Int'l. Inc., Korea Branch

852-2836-7131
905-839-1138
506-309-4158
86-21-6374 2660
44-01283 500500
91-80-4022-4089
(82 2) 2607 1363

Fax: 852-2836-7132
Fax: 905-839-9108
Fax: 506-260-1616
Fax: 86-21-6374 2799
Fax: 44-01283 500400
Fax: 91-80-4022-4033
Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America
Hubbell de Mexico, S.A. de C.V.
Hubbell Premise Wiring, Middle East
Hubbell Premise Wiring, Puerto Rico
Hubbell-Taian Co., Ltd., Taiwan
Hubbell Premise Wiring, Venezuela

305-408-4501
(5255) 9151-9999
971-4-393-4192
787-855-1075
886-2-2522-1862
58-212-5156482

Fax: 305-408-8201
Fax: (5255) 9151-9989
Fax: 971-4-393-4194
Fax: 787-855-3265
Fax: 886-2-2522-1872
Fax: 58-212-6627258