



English | 简体中文 | 日本語

Search Entire Site



Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Document Search | Package Search | Parametric Search | Cross Reference Search | Green & RoHS | Calculators | Thermal Data | Reliability & Quality | Military

Home > Products > > 952801 > 952801CFLF

Add to myIDT [?]

You may also like...

## 952801CFLF

### Category:

Generic Part: 952801

Market Group: PC CLOCK

Description: PC MAIN CLOCK

The ICS952801 is a two chip clock solution for desktop designs using SIS 755/760 style chipsets. When used with a zero delay buffer such as the ICS9179-16 for PC133 or the ICS93735 for DDR applications it provides all the necessary clocks signals for such a system. Output Features: â€¢ 2 - Pairs of differential push-pull K8CPU outputs â€¢ 8 - PCICLK @ 3.3V â€¢ 2 - AGPCLK @ 3.3V â€¢ 3 - REF @ 3.3V â€¢ 2 - ZCLK @ 3.3V â€¢ 1 - 24\_48MHz @ 3.3V â€¢ 1 - 48MHz @ 3.3V

Time is money

### Parameters

|                         |                 |
|-------------------------|-----------------|
| Package                 | SSOP 48 (PVG48) |
| Speed                   | NA              |
| Temperature             | C               |
| Voltage                 | 3.3 V           |
| Status                  | Active          |
| Sample                  | Yes             |
| Minimum Order Quantity  | 90              |
| Factory Order Increment | 30              |

### Distributor Inventory

No Pricing information is available from our Distributors at this time.

### Documents

| Type | Title                  | Size  | Revision Date |
|------|------------------------|-------|---------------|
| Misc | PC Clocks Contact Info | 61 KB | 05/29/2007    |

### Package

|                                  |                          |
|----------------------------------|--------------------------|
| Description                      | SSOP 300 MIL, 48LD       |
| Class                            | PLASTIC                  |
| Moisture Sensitivity Level (MSL) | 1                        |
| Category                         | Green                    |
| Moisture Exposure Floor Life     | Unlimited @ <30°C/85% RH |
| Peak Reflow Temperature          | 260°C                    |
| Rebake Conditions                | N/A                      |
| Length                           | 15.9                     |
| Mark                             | PVG                      |
| Width                            | 7.5                      |
| Pitch                            | 0.64                     |
| Thickness                        | 2.3                      |
| Status                           | Active                   |

Home | Site Map | Legal | Careers | Contact Us | Quality | **RSS** What is this?

Use of this website signifies your agreement to the acceptable use and privacy policy. Copyright © 1997-2008 Integrated Device Technology, Inc. All Rights Reserved.