

RF Power MOSFET Transistor 5W, 500-1000MHz, 28V

M/A-COM Products
Released; RoHS Compliant

Features

- N-Channel enhancement mode device
- DMOS structure
- Lower capacitances for broadband operation
- Common source configuration
- Lower noise floor
- Applications
 - Broadband linear operation
 - 500 MHz to 1400 MHz

ABSOLUTE MAXIMUM RATINGS AT 25° C

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	65	V
Gate-Source Voltage	V_{GS}	20	V
Drain-Source Current	I_{DS}	1.4	A
Power Dissipation	P_D	14.4	W
Junction Temperature	T_J	200	°C
Storage Temperature	T_{STG}	-65 to +150	°C
Thermal Resistance	θ_{JC}	12.1	°C/W

TYPICAL DEVICE IMPEDANCE

F (MHz)	Z_{IN} (Ω)	Z_{LOAD} (Ω)
500	4.3 - j29.0	27.3 + j28.6
1000	2.2 - j2.75	8.0 + j16.0
1400	2.8 - j3.0	9.4 + j10.6

$V_{DD} = 28V$, $I_{DQ} = 50$ mA, $P_{OUT} = 5.0$ W


Z_{IN} is the series equivalent input impedance of the device from gate to source.

Z_{LOAD} is the optimum series equivalent load impedance as measured from drain to ground.

ELECTRICAL CHARACTERISTICS AT 25°C

Parameter	Symbol	Min	Max	Units	Test Conditions
Drain-Source Breakdown Voltage	BV_{DSS}	65	-	V	$V_{GS} = 0.0$ V, $I_{DS} = 2.0$ mA
Drain-Source Leakage Current	I_{DSS}	-	1.0	mA	$V_{GS} = 28.0$ V, $V_{DS} = 0.0$ V
Gate-Source Leakage Current	I_{GSS}	-	1.0	μ A	$V_{GS} = 20.0$ V, $V_{DS} = 0.0$ V
Gate Threshold Voltage	$V_{GS(TH)}$	2.0	6.0	V	$V_{DS} = 10.0$ V, $I_{DS} = 10.0$ mA
Forward Transconductance	G_M	80	-	mS	$V_{DS} = 10.0$ V, $I_{DS} = 100.0$ mA, $\Delta V_{GS} = 1.0V$, 80 μ s Pulse
Input Capacitance	C_{ISS}	-	7	pF	$V_{DS} = 28.0$ V, $F = 1.0$ MHz
Output Capacitance	C_{OSS}	-	5	pF	$V_{DS} = 28.0$ V, $F = 1.0$ MHz
Reverse Capacitance	C_{RSS}	-	2.4	pF	$V_{DS} = 28.0$ V, $F = 1.0$ MHz
Power Gain	G_P	10	-	dB	$V_{DD} = 28.0$ V, $I_{DQ} = 50$ mA, $P_{OUT} = 5.0$ W, $F = 1.0$ GHz
Drain Efficiency	η_D	50	-	%	$V_{DD} = 28.0$ V, $I_{DQ} = 50$ mA, $P_{OUT} = 5.0$ W, $F = 1.0$ GHz
Load Mismatch Tolerance	VSWR-T	-	20:1	-	$V_{DD} = 28.0$ V, $I_{DQ} = 50$ mA, $P_{OUT} = 5.0$ W, $F = 1.0$ GHz






Package Outline



UNLESS OTHERWISE NOTED, TOLERANCES ARE INCHES $\pm .005$ " [MILLIMETERS ± 0.13 mm]

LETTER DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	20.70	20.96	.815	.825
B	14.35	14.61	.565	.575
C	13.72	14.22	.540	.560
D	6.27	6.53	.247	.257
E	6.22	6.48	.245	.255
F	6.22	6.48	.245	.255
G	1.14	1.40	.045	.055
H	2.92	3.18	.115	.125
J	1.40	1.65	.055	.065
K	1.96	2.46	.077	.097
L	3.61	4.37	.142	.172
M	.08	.15	.003	.006

Typical Broadband Performance Curves




RF Power MOSFET Transistor

5W, 500-1000MHz, 28V

M/A-COM Products
Released; RoHS Compliant

TEST FIXTURE CIRCUIT DIMENSIONS



TEST FIXTURE ASSEMBLY

