







LEADFREE CONVERS. EC NO: UCP2013-1898 2012/11/12 DROWNPOFF 2012/11/12 CHKD:MWLF 2012/12/21 APPR:SMILLER	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
				mm	INCH	DRAWN BY JLAURX	DATE 2/21/05	TITLE I-TRAC BACKPLANE HEADER GUIDE RIGHT ASSEMBLY SALES DRAWING							
			4 PLACES	± ---	± ---	CHECKED BY BPISZCZOR	DATE 6/02/06								
			3 PLACES	± ---	± ---	APPROVED BY CBIXLER	DATE 6/02/06								
			2 PLACES	± 0.13	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
			1 PLACE	± 0.25	± ---	SEE TABLE						SD-75705-004		1 OF 4	
			0 PLACE	±	±										
						ANGULAR ±1/2°									
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
						SIZE C			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

75705-****

MODULE TYPE -- TAIL PLATING TYPE

GUIDE RIGHT -- TIN ONLY = 4 (PREVIOUSLY TIN/LEAD)

GUIDE RIGHT -- TIN ONLY = 5

GUIDE RIGHT W/END -- TIN ONLY = 8 (PREVIOUSLY TIN/LEAD)

GUIDE RIGHT W/END -- TIN ONLY = 9

OF COLUMNS

5 = 5 COL

6 = 6 COL

8 = 8 COL

1 = 10 COL

KEY ORIENTATION

0 = NO KEY

1 = A

2 = B

3 = C

4 = D

5 = E

6 = F

7 = G

8 = H

PIN LENGTH (P)

2 = 3.90 - 30 GOLD

3 = 4.70 - 30 GOLD

4 = 5.70 - 30 GOLD

5 = 4.70 & 5.70 - 30 GOLD

STAGGERED

6 = 3.90 - 10 GOLD

7 = 4.70 - 10 GOLD

8 = 5.70 - 10 GOLD


9 = 4.70 & 5.70 - 10 GOLD

STAGGERED


MATERIAL NUMBER	# OF COLUMNS	DIM "A"	DIM "B"
75705-#5**	5	24.8	14.80
75705-#6**	6	28.5	18.50
75705-#8**	8	35.9	25.90
75705-#1**	10	43.3	33.30

MATERIAL NUMBER	# OF COLUMNS	DIM "A"	DIM "B"
75705-#5**	5	26.1	14.80
75705-#6**	6	29.8	18.50
75705-#8**	8	37.2	25.90
75705-#1**	10	44.6	33.30

GUIDE RIGHT STYLE




GUIDE RIGHT W/END STYLE



NOTES:


- MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP)
GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
- FINISH: 10 MICROINCH MINIMUM GOLD OR 30 MICROINCH MINIMUM GOLD
IN CONTACT AREA. SELECTIVE MATTE TIN ON PCB TAILS,
NICKEL OVERALL.
- REFER TO MOLEX PRODUCT SPECIFICATION PS-75710-999
FOR PERFORMANCE SPECIFICATIONS.
- FOR MIXED CONTACT MATING LENGTHS, CONSULT MOLEX
FOR AVAILABILITY.
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
MOLEX COSMETIC SPEC PS-45499-002.
- PACKAGE PER: PK-70873-587.
- GUIDED PARTS TO BE SHIPPED WITH 2-56 UNC B SCREW P/N 73774-1000.
- FOR GROUNDED GUIDE PINS USE DIA 3.56+/-0.08 (PTH)
DIA 3.66 (DRILL), AND DIA 6.5 (PAD).
- REFER TO PCB ROUTING GUIDE FOR ANTIPAD AND ROUTING RECOMMENDATIONS.

SEE SHEET 1 EC NO: UCP2013-1898 2012/11/12 DRWN:MP0FF CHKD:MMOLFE 2012/11/12 APPR:SMILLER 2012/12/21	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE I-TRAC BACKPLANE HEADER GUIDE RIGHT ASSEMBLY SALES DRAWING molex	DOCUMENT NO. SD-75705-004	SHEET NO. 2 OF 4				
			F=0	F=0	F=0	mm		INCH						DRAWN BY JLAURX		DATE 2/21/05	
						4 PLACES ± --- ± ---		3 PLACES ± --- ± ---						CHECKED BY BPISZCZOR		DATE 6/02/06	
						3 PLACES ± 0.13 ± ---		2 PLACES ± 0.25 ± ---						APPROVED BY CBIXLER		DATE 6/02/06	
						2 PLACES ± 0.13 ± ---		0 PLACES ± ±						MATERIAL NO.			
						1 PLACE ± 0.25 ± ---		ANGULAR ± 1/2°									
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE												
SIZE C			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														



I-TRAC 11 ROW BOARD RELATIONSHIPS

SCALE 2:1



SEE SHEET 1	EC NO: UCP2013-1898 2012/11/12 DRWN:MP0FF CHKD:MMOLFE APPR:SMILLER 2012/11/12 2012/12/21				DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		TITLE I-TRAC BACKPLANE HEADER GUIDE RIGHT ASSEMBLY SALES DRAWING molex	
	mm		INCH				DRAWN BY JLAURX		DATE 2/21/05		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-75705-004		SHEET NO. 3 OF 4		
	4 PLACES ± ---		± ---				CHECKED BY BPISZCZOR		DATE 6/02/06								
	3 PLACES ± ---		± ---				APPROVED BY		DATE 6/02/06								
	2 PLACES ± 0.13		± ---				CBIXLER		6/02/06								
	1 PLACE ± 0.25		± ---														
	0 PLACE ±		±														
		ANGULAR ±1/2°															
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															

