

# MC74AC652, MC74ACT652

## Octal Transceiver/Register with 3-State Outputs (Non-Inverting)

The MC74AC/ACT652 consists of registered bus transceiver circuits, with outputs, D-type flip-flops and control circuitry providing multiplexed transmission of data directly from the input bus or from the internal storage registers. Data on the A or B bus will be loaded into the respective registers on the LOW-to-HIGH transition of the appropriate clock pin (CAB or CBA). The four fundamental data handling functions available are illustrated in Figures 1 to 4.

- Independent Registers for A and B Buses
- Multiplexed Real-Time and Stored Data Transfers
- Choice of True and Inverting Data Paths
- 3-State Outputs
- 300 mil Slim Dual-in-Line Package
- Outputs Source/Sink 24 mA
- 'ACT652 Has TTL Compatible Inputs
- **These devices are available in Pb-free package(s). Specifications herein apply to both standard and Pb-free devices. Please see our website at [www.onsemi.com](http://www.onsemi.com) for specific Pb-free orderable part numbers, or contact your local ON Semiconductor sales office or representative.**




Figure 1.




Figure 2.




Figure 3.





Figure 4.




ON Semiconductor™

<http://onsemi.com>




PDIP-24  
N SUFFIX  
CASE 724




SO-24  
DW SUFFIX  
CASE 751E

### MARKING DIAGRAMS

#### PDIP-24



#### SO-24




A = Assembly  
Location  
L, WL = Wafer Lot  
Y, YY = Year  
W, WW = Work Week

### ORDERING INFORMATION

| Device         | Package | Shipping         |
|----------------|---------|------------------|
| MC74AC652N     | PDIP-24 | 15 Units/Rail    |
| MC74ACT652N    | PDIP-24 | 15 Units/Rail    |
| MC74AC652DW    | SOIC-24 | 30 Units/Rail    |
| MC74AC652DWR   | SOIC-24 | 1000 Tape & Reel |
| MC74ACT652DW   | SOIC-24 | 30 Units/Rail    |
| MC74ACT652DWR2 | SOIC-24 | 1000 Tape & Reel |


# MC74AC652, MC74ACT652




## PIN ASSIGNMENT

| PIN                            | FUNCTION                                          |
|--------------------------------|---------------------------------------------------|
| A <sub>0</sub> –A <sub>7</sub> | Data Register A Inputs<br>Data Register A Outputs |
| B <sub>0</sub> –B <sub>7</sub> | Data Register B Inputs<br>Data Register B Outputs |
| CAB, CBA                       | Clock Pulse Inputs                                |
| SAB, SBA                       | Transmit/Receive Inputs                           |
| GAB, GBA                       | Output Enable Inputs                              |

**Figure 5. Pinout: 24-Lead Plastic Package (Top View)**



**Figure 6. Logic Symbol**



NOTE: This diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

**Figure 7. Logic Diagram**

# MC74AC652, MC74ACT652

## FUNCTION TABLE

| Inputs |        |             |             |          |          | Data I/O*                       |                                 | Operation or Function                                |
|--------|--------|-------------|-------------|----------|----------|---------------------------------|---------------------------------|------------------------------------------------------|
| GAB    | GBA    | CAB         | CBA         | SAB      | SBA      | A <sub>0</sub> – A <sub>7</sub> | B <sub>0</sub> – B <sub>7</sub> |                                                      |
| L<br>L | H<br>H | H or L<br>↑ | H or L<br>↑ | X<br>X   | X<br>X   | Input                           | Input                           | Isolation<br>Store A and B Data                      |
| X<br>H | H<br>H | ↑<br>↑      | H or L<br>↑ | X<br>X** | X<br>X   | Input<br>Input                  | Unspecified*<br>Output          | Store A, Hold B<br>Store A in Both Registers         |
| L<br>L | X<br>L | H or L<br>↑ | ↑<br>↑      | X<br>X   | X<br>X** | Unspecified*<br>Output          | Input<br>Input                  | Hold A, Store B<br>Store B in Both Registers         |
| L<br>L | L<br>L | X<br>X      | X<br>H or L | X<br>X   | L<br>H   | Output                          | Input                           | Real-Time B Data to A Bus<br>Stored B Data to A Bus  |
| H<br>H | H<br>H | X<br>H or L | X<br>X      | L<br>H   | X<br>X   | Input                           | Output                          | Real-Time A Data to B Bus<br>Stored A Data to B Bus  |
| H      | L      | H or L      | H or L      | H        | H        | Output                          | Output                          | Stored A Data to B Bus and<br>Stored B Data to A Bus |

\*The data output functions may be enabled or disabled by various signals at the GBA and GAB inputs. Data input functions are always enabled; i.e., data at the bus pins will be stored on every LOW-to-HIGH transition of the appropriate clock inputs.

\*\*Select control = L: clocks can occur simultaneously.

H = HIGH Voltage Level; L = LOW Voltage Level; X = Immaterial; ↑ = LOW-to-HIGH Transition

## MAXIMUM RATINGS\*

| Symbol           | Parameter                                        | Value                         | Unit |
|------------------|--------------------------------------------------|-------------------------------|------|
| V <sub>CC</sub>  | DC Supply Voltage (Referenced to GND)            | –0.5 to +7.0                  | V    |
| V <sub>in</sub>  | DC Input Voltage (Referenced to GND)             | –0.5 to V <sub>CC</sub> + 0.5 | V    |
| V <sub>out</sub> | DC Output Voltage (Referenced to GND)            | –0.5 to V <sub>CC</sub> + 0.5 | V    |
| I <sub>in</sub>  | DC Input Current, per Pin                        | ±20                           | mA   |
| I <sub>out</sub> | DC Output Sink/Source Current, per Pin           | ±50                           | mA   |
| I <sub>CC</sub>  | DC V <sub>CC</sub> or GND Current per Output Pin | ±50                           | mA   |
| T <sub>stg</sub> | Storage Temperature                              | –65 to +150                   | °C   |

\*Maximum Ratings are those values beyond which damage to the device may occur. Functional operation should be restricted to the Recommended Operating Conditions.

## RECOMMENDED OPERATING CONDITIONS

| Symbol                             | Parameter                                                               |                         | Min | Typ | Max             | Unit |
|------------------------------------|-------------------------------------------------------------------------|-------------------------|-----|-----|-----------------|------|
| V <sub>CC</sub>                    | Supply Voltage                                                          | 'AC                     | 2.0 | 5.0 | 6.0             | V    |
|                                    |                                                                         | 'ACT                    | 4.5 | 5.0 | 5.5             |      |
| V <sub>in</sub> , V <sub>out</sub> | DC Input Voltage, Output Voltage (Ref. to GND)                          |                         | 0   | –   | V <sub>CC</sub> | V    |
| t <sub>r</sub> , t <sub>f</sub>    | Input Rise and Fall Time (Note 1)<br>'AC Devices except Schmitt Inputs  | V <sub>CC</sub> @ 3.0 V | –   | 150 | –               | ns/V |
|                                    |                                                                         | V <sub>CC</sub> @ 4.5 V | –   | 40  | –               |      |
|                                    |                                                                         | V <sub>CC</sub> @ 5.5 V | –   | 25  | –               |      |
| t <sub>r</sub> , t <sub>f</sub>    | Input Rise and Fall Time (Note 2)<br>'ACT Devices except Schmitt Inputs | V <sub>CC</sub> @ 4.5 V | –   | 10  | –               | ns/V |
|                                    |                                                                         | V <sub>CC</sub> @ 5.5 V | –   | 8.0 | –               |      |
| T <sub>J</sub>                     | Junction Temperature (PDIP)                                             |                         | –   | –   | 140             | °C   |
| T <sub>A</sub>                     | Operating Ambient Temperature Range                                     |                         | –40 | 25  | 85              | °C   |
| I <sub>OH</sub>                    | Output Current — HIGH                                                   |                         | –   | –   | –24             | mA   |
| I <sub>OL</sub>                    | Output Current — LOW                                                    |                         | –   | –   | 24              | mA   |

1. V<sub>in</sub> from 30% to 70% V<sub>CC</sub>; see individual Data Sheets for devices that differ from the typical input rise and fall times.

2. V<sub>in</sub> from 0.8 V to 2.0 V; see individual Data Sheets for devices that differ from the typical input rise and fall times.

# MC74AC652, MC74ACT652

## DC CHARACTERISTICS

| Symbol           | Parameter                            | V <sub>CC</sub><br>(V) | 74AC                   |                   | 74AC                                  | Unit | Conditions                                                                                                                                  |
|------------------|--------------------------------------|------------------------|------------------------|-------------------|---------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------------------------|
|                  |                                      |                        | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> =<br>–40°C to<br>+85°C |      |                                                                                                                                             |
|                  |                                      |                        | Typ                    | Guaranteed Limits |                                       |      |                                                                                                                                             |
| V <sub>IH</sub>  | Minimum High Level<br>Input Voltage  | 3.0                    | 1.5                    | 2.1               | 2.1                                   | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
|                  |                                      | 4.5                    | 2.25                   | 3.15              | 3.15                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 2.75                   | 3.85              | 3.85                                  |      |                                                                                                                                             |
| V <sub>IL</sub>  | Maximum Low Level<br>Input Voltage   | 3.0                    | 1.5                    | 0.9               | 0.9                                   | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
|                  |                                      | 4.5                    | 2.25                   | 1.35              | 1.35                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 2.75                   | 1.65              | 1.65                                  |      |                                                                                                                                             |
| V <sub>OH</sub>  | Minimum High Level<br>Output Voltage | 3.0                    | 2.99                   | 2.9               | 2.9                                   | V    | I <sub>OUT</sub> = – 50 μA                                                                                                                  |
|                  |                                      | 4.5                    | 4.49                   | 4.4               | 4.4                                   |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 5.49                   | 5.4               | 5.4                                   |      |                                                                                                                                             |
|                  |                                      | 3.0                    | –                      | 2.56              | 2.46                                  | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>– 12 mA<br>I <sub>OH</sub> – 24 mA<br>– 24 mA                                      |
|                  |                                      | 4.5                    | –                      | 3.86              | 3.76                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | –                      | 4.86              | 4.76                                  |      |                                                                                                                                             |
| V <sub>OL</sub>  | Minimum Low Level<br>Output Voltage  | 3.0                    | 0.002                  | 0.1               | 0.1                                   | V    | I <sub>OUT</sub> = 50 μA                                                                                                                    |
|                  |                                      | 4.5                    | 0.001                  | 0.1               | 0.1                                   |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 0.001                  | 0.1               | 0.1                                   |      |                                                                                                                                             |
|                  |                                      | 3.0                    | –                      | 0.36              | 0.44                                  | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>12 mA<br>I <sub>OL</sub> 24 mA<br>24 mA                                            |
|                  |                                      | 4.5                    | –                      | 0.36              | 0.44                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | –                      | 0.36              | 0.44                                  |      |                                                                                                                                             |
| I <sub>IN</sub>  | Maximum Input<br>Leakage Current     | 5.5                    | –                      | ±0.1              | ±1.0                                  | μA   | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                      |
| I <sub>OZT</sub> | Maximum<br>3-State<br>Current        | 5.5                    | –                      | ±0.6              | ±6.0                                  | μA   | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub><br>V <sub>I</sub> = V <sub>CC</sub> , GND<br>V <sub>O</sub> = V <sub>CC</sub> , GND |
| I <sub>OLD</sub> | †Minimum Dynamic<br>Output Current   | 5.5                    | –                      | –                 | 75                                    | mA   | V <sub>OLD</sub> = 1.65 V Max                                                                                                               |
| I <sub>OHD</sub> |                                      | 5.5                    | –                      | –                 | –75                                   | mA   | V <sub>OHD</sub> = 3.85 V Min                                                                                                               |
| I <sub>CC</sub>  | Maximum Quiescent<br>Supply Current  | 5.5                    | –                      | 8.0               | 80                                    | μA   | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                    |

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one input loaded at a time.

NOTE: I<sub>IN</sub> and I<sub>CC</sub> @ 3.0 V are guaranteed to be less than or equal to the respective limit @ 5.5 V.

# MC74AC652, MC74ACT652

## AC CHARACTERISTICS

| Symbol           | Parameter                                                             | V <sub>CC</sub> *<br>(V) | 74AC                                             |              | 74AC                                                         |              | Unit |
|------------------|-----------------------------------------------------------------------|--------------------------|--------------------------------------------------|--------------|--------------------------------------------------------------|--------------|------|
|                  |                                                                       |                          | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |              | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |              |      |
|                  |                                                                       |                          | Min                                              | Max          | Min                                                          | Max          |      |
| t <sub>PLH</sub> | Propagation Delay<br>CPBA or CPAB to A <sub>n</sub> or B <sub>n</sub> | 3.0<br>5.0               | 4.0<br>2.5                                       | 17.0<br>12.0 | 3.0<br>2.0                                                   | 19.0<br>14.0 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>CPBA or CPAB to A <sub>n</sub> or B <sub>n</sub> | 3.0<br>5.0               | 3.0<br>2.0                                       | 14.5<br>10.5 | 2.5<br>1.5                                                   | 16.5<br>12.0 | ns   |
| t <sub>PLH</sub> | Propagation Delay<br>A or B to B <sub>n</sub> or A <sub>n</sub>       | 3.0<br>5.0               | 3.0<br>2.0                                       | 14.0<br>9.5  | 2.5<br>1.5                                                   | 16.0<br>11.0 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>A or B to B <sub>n</sub> or A <sub>n</sub>       | 3.0<br>5.0               | 2.5<br>1.5                                       | 13.0<br>9.0  | 2.0<br>1.0                                                   | 15.0<br>10.5 | ns   |
| t <sub>PLH</sub> | Propagation Delay<br>SBA or SAB to A <sub>n</sub> or B <sub>n</sub>   | 3.0<br>5.0               | 3.0<br>2.5                                       | 14.0<br>10.0 | 2.5<br>2.0                                                   | 16.0<br>11.5 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>SBA or SAB to A <sub>n</sub> or B <sub>n</sub>   | 3.0<br>5.0               | 2.5<br>2.0                                       | 13.5<br>10.0 | 2.0<br>1.5                                                   | 15.5<br>11.5 | ns   |
| t <sub>PZH</sub> | Output Enable Time<br>OEBA to A <sub>n</sub>                          | 3.0<br>5.0               | 2.5<br>1.5                                       | 12.0<br>9.0  | 2.0<br>1.0                                                   | 13.5<br>10.0 | ns   |
| t <sub>PZL</sub> | Output Enable Time<br>OEBA to A <sub>n</sub>                          | 3.0<br>5.0               | 2.5<br>1.5                                       | 12.0<br>9.0  | 2.0<br>1.0                                                   | 14.0<br>10.5 | ns   |
| t <sub>PHZ</sub> | Output Disable Time<br>OEBA to A <sub>n</sub>                         | 3.0<br>5.0               | 3.0<br>2.0                                       | 13.0<br>11.0 | 2.5<br>1.5                                                   | 14.0<br>12.0 | ns   |
| t <sub>PLZ</sub> | Output Disable Time<br>OEBA to A <sub>n</sub>                         | 3.0<br>5.0               | 2.5<br>2.0                                       | 12.5<br>10.5 | 2.0<br>1.5                                                   | 14.0<br>12.0 | ns   |

\*Voltage Range 3.3 V is 3.3 V ±0.3 V.  
Voltage Range 5.0 V is 5.0 V ±0.5 V.

# MC74AC652, MC74ACT652

## DC CHARACTERISTICS

| Symbol            | Parameter                              | V <sub>CC</sub><br>(V) | 74ACT                  |                   | 74ACT                                 |    | Unit                                                                                                                                        | Conditions |
|-------------------|----------------------------------------|------------------------|------------------------|-------------------|---------------------------------------|----|---------------------------------------------------------------------------------------------------------------------------------------------|------------|
|                   |                                        |                        | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> =<br>–40°C to<br>+85°C |    |                                                                                                                                             |            |
|                   |                                        |                        | Typ                    | Guaranteed Limits |                                       |    |                                                                                                                                             |            |
| V <sub>IH</sub>   | Minimum High Level<br>Input Voltage    | 4.5<br>5.5             | 1.5<br>1.5             | 2.0<br>2.0        | 2.0<br>2.0                            | V  | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |            |
| V <sub>IL</sub>   | Maximum Low Level<br>Input Voltage     | 4.5<br>5.5             | 1.5<br>1.5             | 0.8<br>0.8        | 0.8<br>0.8                            | V  | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |            |
| V <sub>OH</sub>   | Minimum High Level<br>Output Voltage   | 4.5<br>5.5             | 4.49<br>5.49           | 4.4<br>5.4        | 4.4<br>5.4                            | V  | I <sub>OUT</sub> = – 50 µA                                                                                                                  |            |
|                   |                                        | 4.5<br>5.5             | –<br>–                 | 3.86<br>4.86      | 3.76<br>4.76                          | V  | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>– 24 mA<br>I <sub>OH</sub> – 24 mA                                                 |            |
| V <sub>OL</sub>   | Minimum Low Level<br>Output Voltage    | 4.5<br>5.5             | 0.001<br>0.001         | 0.1<br>0.1        | 0.1<br>0.1                            | V  | I <sub>OUT</sub> = – 50 µA                                                                                                                  |            |
|                   |                                        | 4.5<br>5.5             | –<br>–                 | 0.36<br>0.36      | 0.44<br>0.44                          | V  | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>– 24 mA<br>I <sub>OH</sub> – 24 mA                                                 |            |
| I <sub>IN</sub>   | Maximum Input<br>Leakage Current       | 5.5                    | –                      | ±0.1              | ±1.0                                  | µA | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                      |            |
| ΔI <sub>CCT</sub> | Additional Max. I <sub>CC</sub> /Input | 5.5                    | 0.6                    | –                 | 1.5                                   | mA | V <sub>I</sub> = V <sub>CC</sub> – 2.1 V                                                                                                    |            |
| I <sub>OZT</sub>  | Maximum<br>3-State<br>Current          | 5.5                    | –                      | ±0.6              | ±6.0                                  | µA | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub><br>V <sub>I</sub> = V <sub>CC</sub> , GND<br>V <sub>O</sub> = V <sub>CC</sub> , GND |            |
| I <sub>OLD</sub>  | †Minimum Dynamic<br>Output Current     | 5.5                    | –                      | –                 | 75                                    | mA | V <sub>OLD</sub> = 1.65 V Max                                                                                                               |            |
| I <sub>OHD</sub>  |                                        | 5.5                    | –                      | –                 | –75                                   | mA | V <sub>OHD</sub> = 3.85 V Min                                                                                                               |            |
| I <sub>CC</sub>   | Maximum Quiescent<br>Supply Current    | 5.5                    | –                      | 8.0               | 80                                    | µA | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                    |            |

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one input loaded at a time.

# MC74AC652, MC74ACT652

## AC CHARACTERISTICS

| Symbol           | Parameter                                                                   | V <sub>CC</sub> *<br>(V) | 74ACT                                            |      | 74ACT                                                        |      | Unit |
|------------------|-----------------------------------------------------------------------------|--------------------------|--------------------------------------------------|------|--------------------------------------------------------------|------|------|
|                  |                                                                             |                          | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |      | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |      |      |
|                  |                                                                             |                          | Min                                              | Max  | Min                                                          | Max  |      |
| t <sub>PLH</sub> | Propagation Delay<br>CPBA or CPAB to A <sub>n</sub> or B <sub>n</sub>       | 5.0                      | 4.0                                              | 14.5 | 3.5                                                          | 16.5 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>CPBA or CPAB to A <sub>n</sub> or B <sub>n</sub>       | 5.0                      | 3.5                                              | 14.5 | 3.0                                                          | 16.5 | ns   |
| t <sub>PLH</sub> | Propagation Delay<br>A or B to B <sub>n</sub> or A <sub>n</sub>             | 5.0                      | 2.5                                              | 11.5 | 2.0                                                          | 13.0 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>A or B to B <sub>n</sub> or A <sub>n</sub>             | 5.0                      | 2.5                                              | 11.5 | 2.0                                                          | 13.0 | ns   |
| t <sub>PLH</sub> | Propagation Delay<br>SBA or SAB to A <sub>n</sub> or B <sub>n</sub>         | 5.0                      | 2.5                                              | 12.0 | 2.0                                                          | 13.5 | ns   |
| t <sub>PHL</sub> | Propagation Delay<br>SBA or SAB to A <sub>n</sub> or B <sub>n</sub>         | 5.0                      | 3.0                                              | 12.0 | 2.5                                                          | 13.5 | ns   |
| t <sub>PZH</sub> | Output Enable Time<br>OEBA to A <sub>n</sub>                                | 5.0                      | 2.0                                              | 11.5 | 1.5                                                          | 13.0 | ns   |
| t <sub>PZL</sub> | Output Enable Time<br>OEBA to A <sub>n</sub>                                | 5.0                      | 2.5                                              | 11.5 | 2.0                                                          | 13.0 | ns   |
| t <sub>PHZ</sub> | Output Disable Time<br>OEBA to A <sub>n</sub>                               | 5.0                      | 3.0                                              | 13.0 | 2.5                                                          | 14.0 | ns   |
| t <sub>PLZ</sub> | Output Disable Time<br>OEBA to A <sub>n</sub>                               | 5.0                      | 2.5                                              | 12.5 | 2.0                                                          | 14.0 | ns   |
| t <sub>PZH</sub> | Output Enable time<br>OEAB to B <sub>n</sub>                                | 5.0                      | 2.5                                              | 12.0 | 2.0                                                          | 13.5 | ns   |
| t <sub>PZL</sub> | Output Enable Time<br>OEAB to B <sub>n</sub>                                | 5.0                      | 2.5                                              | 12.0 | 2.0                                                          | 13.5 | ns   |
| t <sub>PHZ</sub> | Output Enable Time<br>OEAB to B <sub>n</sub>                                | 5.0                      | 3.5                                              | 13.5 | 3.0                                                          | 14.5 | ns   |
| t <sub>PLZ</sub> | Output Enable Time<br>OEAB to B <sub>n</sub>                                | 5.0                      | 3.0                                              | 13.5 | 2.5                                                          | 15.0 | ns   |
| t <sub>s</sub>   | Setup Time, HIGH or LOW<br>A <sub>n</sub> or B <sub>n</sub> to CPBA or CPAB | 5.0                      | 7.0                                              | –    | 8.0                                                          | –    | ns   |
| t <sub>h</sub>   | Hold Time, HIGH or LOW<br>A <sub>n</sub> or B <sub>n</sub> to CPBA or CPAB  | 5.0                      | 2.5                                              | –    | 2.5                                                          | –    | ns   |
| t <sub>w</sub>   | CPAB, CPBA Pulse Width<br>HIGH or LOW                                       | 5.0                      | 6.0                                              | –    | 7.0                                                          | –    | ns   |

\*Voltage Range 3.3 V is 3.3 V ±0.3 V.  
Voltage Range 5.0 V is 5.0 V ±0.5 V.


## CAPACITANCE

| Symbol           | Parameter                     | 74ACT<br>Typ | Unit | Test Conditions         |
|------------------|-------------------------------|--------------|------|-------------------------|
| C <sub>IN</sub>  | Input Capacitance             | 4.5          | pF   | V <sub>CC</sub> = 5.0 V |
| C <sub>I/O</sub> | Input/Output Capacitance      | 15           | pF   | V <sub>CC</sub> = 5.0 V |
| C <sub>PD</sub>  | Power Dissipation Capacitance | 60.0         | pF   | V <sub>CC</sub> = 5.0 V |

# MC74AC652, MC74ACT652

## PACKAGE DIMENSIONS

### PDIP-24 N SUFFIX 24 PIN PLASTIC DIP PACKAGE CASE 724-03 ISSUE D




#### NOTES:

1. CHAMFERED CONTOUR OPTIONAL.
2. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
3. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
4. CONTROLLING DIMENSION: INCH.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 1.230     | 1.265 | 31.25       | 32.13 |
| B   | 0.250     | 0.270 | 6.35        | 6.85  |
| C   | 0.145     | 0.175 | 3.69        | 4.44  |
| D   | 0.015     | 0.020 | 0.38        | 0.51  |
| E   | 0.050 BSC |       | 1.27 BSC    |       |
| F   | 0.040     | 0.060 | 1.02        | 1.52  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| J   | 0.007     | 0.012 | 0.18        | 0.30  |
| K   | 0.110     | 0.140 | 2.80        | 3.55  |
| L   | 0.300 BSC |       | 7.62 BSC    |       |
| M   | 0°        | 15°   | 0°          | 15°   |
| N   | 0.020     | 0.040 | 0.51        | 1.01  |

### SO-24 DW SUFFIX 24 PIN PLASTIC SOIC PACKAGE CASE 751E-04 ISSUE E



#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.13 (0.005) TOTAL IN EXCESS OF D DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |       | INCHES    |       |
|-----|-------------|-------|-----------|-------|
|     | MIN         | MAX   | MIN       | MAX   |
| A   | 15.25       | 15.54 | 0.601     | 0.612 |
| B   | 7.40        | 7.60  | 0.292     | 0.299 |
| C   | 2.35        | 2.65  | 0.093     | 0.104 |
| D   | 0.35        | 0.49  | 0.014     | 0.019 |
| F   | 0.41        | 0.90  | 0.016     | 0.035 |
| G   | 1.27 BSC    |       | 0.050 BSC |       |
| J   | 0.23        | 0.32  | 0.009     | 0.013 |
| K   | 0.13        | 0.29  | 0.005     | 0.011 |
| M   | 0°          | 8°    | 0°        | 8°    |
| P   | 10.05       | 10.55 | 0.395     | 0.415 |
| R   | 0.25        | 0.75  | 0.010     | 0.029 |

## **Notes**

## **Notes**

## Notes

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

### PUBLICATION ORDERING INFORMATION

**LITERATURE FULFILLMENT:**

Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA  
**Phone:** 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Japan:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

**Order Literature:** <http://www.onsemi.com/litorder>

For additional information, please contact your  
local Sales Representative.