




REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	8/19/97
A	WIRE DIAGRAM CHNGS	10/31/00
B	CONVERT TO CAD	6/6/01
C	ADD HOLE DIA.	3/15/02



CHARACTERISTICS	MIN	TYP	MAX
INPUT VOLTAGE: (vdc)	4.5	5.0	5.5
INPUT CURRENT: (mA)	200	250	300
OUTPUT VOLTAGE: (Vrms)	600	650	700
OUTPUT CURRENT (maRms)	4.0	4.5	5.0
OUTPUT FREQUENCY: (kHz)	70	80	90
OPERATING TEMP: (CELSIUS)	0	25	50

BOARD PIN #	INPUT
1	+V (V in)
2	V (GND)
3	OUT GND
4	V OUT

TOLERANCE		
L < 20	±0.2	
20 ≤ L < 50	±0.3	
50 ≤ L < 100	±0.4	
100 ≤ L	±0.5	



METRIC	DIMENSIONS ARE IN MILLIMETERS	TITLE			
THIRD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED	JKL COMPONENTS CORPORATION			
1 PL +/- 0.2	2 PL +/- 0				
ANGLE +/- 0		5 V CCFL POWER SUPPLY			
DRAWN BY L. WENGSTROM	APP'D BY	DATE	SIZE A	FSC# NO. 55335	DRAWING NO. BXA-502
- CAD DRAWING -		SCALE NONE	RELEASED DATE 8/19/97	REVISION DATE 3/15/02	REV. NO. C
MANUAL REVISIONS NOT PERMITTED					SHEET OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BXA-502](#)