

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

©

COPYRIGHT

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD







Y2

REVISED PER ECO-11-005301

14APR11

RK

HMR



Angeschlagener Leiter: FLK-Leitung
Leiter: F-Crimp
Isolation: F-Crimp


Leitungsquerschnitt in mm²
CROSS-SECTION IN mm²

	SINGLE CONNECTION Einzelanschlag	0.50	0.75	1.00	1.50	2.00	2.50	3.00	4.00	6.00
0.50	x	x	x	x	x					
0.75	x	x	x	x						
1.00	x	x	x	x						
1.50	x	x								
2.00										
2.50										
3.00										
4.00										
6.00										

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

OBSOLETE	925660-7	925715-7	CuZn 30	blank
	925660-6	925715-6	CuSn 4	Gold üb. Ni.
	925660-5	925715-5	St4K50	vorverzinnt
	925660-4	925715-4	CuSn 4	blank
	925660-3	925715-3	CuSn 4	versilber
	925660-2	925715-2	CuSn 4	vorverzinnt
	925660-1	925715-1	CuZn 30	vorverzinnt
Bestell.-Nr. für Einzelausführung Crimp vorgeformt	BESTELL-NR.	WERSTOFF	OBERFLÄCHE	

DIMENSIONS:
mm



MATERIAL SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±0.2
1 PLC	±0.2
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±°
FINISH	SEE TABLE

DWN 22JUL2005

CHK J.SKODA

R.VLCEK 19AUG2005

APVD 26AUG2005

M.BLIFCHER

PRODUCT SPEC

108-1032

APPLICATION SPEC

114-1007

WEIGHT

-

CUSTOMER DRAWING / KUNDENZEICHNUNG



TE Connectivity

NAME

ø 3.5 PIN

ø 3.5 Stift

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=925715

SCALE 5:1 SHEET 1 OF 1 REV Y2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[925715-2](#) [925715-2 \(CUT STRIP\)](#) [925715-2 \(MOUSER REEL\)](#)