HD

D-Sub connectors - Stamped and Formed Contacts



RIGHT ANGLE
HIGH DENSITY CONNECTORS

MAIN CHARACTERISTICS

Specifications
- **Connectors according to: MIL C24308**
- **UL File:** E149426

Materials and Platings	
Shells	Steel, tin over nickel plating
Insulator	Glass-filled thermoplastic, UL 94V- 0
Contacts	Brass, selected gold in mating area; 2.54µm (100 µ") min.tin on termination area over 1.27µm (50µ") min.nickel
Rear insert	Brass, 2.54µm (100µ") min.nickel plated
Boardlock	Phosphor bronze or Brass, 2.54µm (100µ") min.nickel plated
Screwlock	Brass, 2.54µm (100µ") min.nickel plated

Electrical Data	
Current rating	3A
Voltage rating	250V AC/ rms 50Hz
Withstanding voltage	1000V AC/rms 50Hz for one minute
Insulation resistance	5000MΩ at 500V DC
Contact resistance	10mΩ max

Climatic Data	
Operating temperature	-55°C to +125°C
Salt spray	24 hours

Mechanical Data

Single contact insertion force 0.34kg (0.75lb) max.
Single contact withdrawal force 0.02kg (0.044lb) min.

Mating and unmating force
Unit: kg (lb)

No. of Cts	Mate (max)	Unmate (min)
15	3.81 (8.42)	0.52 (1.14)
26	5.95 (13.16)	1.05 (2.32)
44	9.26 (20.46)	1.37 (3.02)
62	13.48 (29.78)	1.76 (3.88)

Standard plating thickness
- Gold flash
- 0.4µm (15µ") Gold
- 0.76 µm (30µ") Gold

DESCRIPTION

Amphenol's high density D-Sub connectors complement Amphenol's extensive D-Sub connector line. This line offers many superior features, high performance level and low installation cost.

The decreased contact spacing accommodates greater signal density in comparison to conventional D-Sub connectors.

Economical right angle PCB mount connectors

APPLICATIONS

- Industrial
- Telecom
- Any industry standard I / O connections

HD / E19

Amphenol RoHS Compliant EU 2002/95/EC

Amphenol

Shell size dimensions

Plug



Socket



Nb OF CONTACTS	DIMENSIONS mm (inch)				
	A	B	C	C'	D
15	30.84 (1.214)	24.99 (.984)	16.92 (.661)	16.26 (.640)	2.29 (.090)
26	39.24 (1.545)	33.32 (1.312)	25.25 (.994)	24.56 (.967)	2.29 (.090)
44	53.04 (2.088)	47.04 (1.852)	38.96 (1.534)	38.30 (1.508)	2.29 (.090)
62	69.34 (2.730)	63.50 (2.500)	55.42 (2.182)	54.76 (2.156)	2.41 (.095)

P.C.B. Layout



15 PIN



62 PIN



26 PIN



44 PIN

PCB layout for socket connector, top view

Panel mounting option



Front female screwlock

4F / 3F



Threaded rear insert

4R / 3R

How to order

L ... HD C309

RoHS Compliant

Gold flash	**77**: tinned shell for receptable **717**: tinned shell + dimples for plug
0.4µm (15µ")	**177**: tinned shell for receptable **777**: tinned shell + dimples for plug

Series
High density

Configuration
E15, A26, B44, C62

Contact type
P = Plug
S = Socket

Plating option
valid only for 0.76µm (30µ") part numbers to be written as follow:
or 77.....**C309**
717.....**C309**

Front mounting option
Blank = 3.05mm (.120") rivet
4R = 4-40 rear insert
4F = 4-40 front screwlock
3R = M3 rear insert
3F = M3 front screwlock

Grounding option
CO = Grounding bracket
CH = Grounding bracket + PCB boardlock
C4 = Grounding bracket + PCB 4-40 insert
C3 = Grounding bracket + PCB M3 insert

Footprint option
D0 = 1.5mm (.059")
D1 = 8.89mm (.350")
D2 = 5.08mm (.200")
D3 = 2.50mm (.098")

Examples: L 717 HD E15 P D1 CH 4R C309
L 177 HD A26 S D0 CO 3F

For special request, please consult factory

Do not hesitate to contact us for further information

Amphenol IT & Communication Products
Block A3/A4, The 4th Industrial District of
Industrial Headquarters, Dong Keng Road
Gong Ming Town, Shen Zhen China
Fax:+86(0)755 2754 9955

Technical Support
Tel:+86(0)755 2717 7945
Info-dsub@amphenol.com.cn
http://www.dsubconnector.com

The information given in this document are as a guideline only. We reserve the right to modify our products in any way we deem necessary. Any duplication is prohibited, unless approved in writing.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

L177HDA26S L177HDA26SD1CH3F L177HDA26SD1CH3R L177HDA26SD1CH4F L177HDA26SD1CH4R L177HDA26SOL2 L177HDA26SVF L177HDA26SVFM L177HDAG26S L177HDAG26SOL2 L177HDAG26SOL2RM5 L177HDAG26SOL2RM8 L177HDAH26S L177HDAH26SOL2 L177HDAH26SOL2RM5 L177HDAH26SOL2RM8 L177HDB44S L177HDB44SD1CH3F L177HDB44SD1CH3R L177HDB44SD1CH4F L177HDB44SD1CH4R L177HDB44SOL2 L177HDB44SVF L177HDB44SVFM L177HDBG44S L177HDBG44SOL2 L177HDBG44SOL2RM5 L177HDBG44SOL2RM8 L177HDBH44S L177HDBH44SOL2 L177HDBH44SOL2RM5 L177HDBH44SOL2RM8 L177HDC62S L177HDC62SD1CH3F L177HDC62SD1CH3R L177HDC62SD1CH4F L177HDC62SD1CH4R L177HDC62SOL2 L177HDC62SVF L177HDC62SVFM L177HDCG62S L177HDCG62SOL2 L177HDCG62SOL2RM5 L177HDCG62SOL2RM8 L177HDCH62S L177HDCH62SOL2 L177HDCH62SOL2RM5 L177HDCH62SOL2RM8 L177HDD78S L177HDD78SOL2 L177HDD78SVF L177HDD78SVFM L177HDDG78S L177HDDG78SOL2 L177HDDG78SOL2RM5 L177HDDG78SOL2RM8 L177HDDH78S L177HDDH78SOL2 L177HDDH78SOL2RM8 L177HDE15S L177HDE15SD1CH3F L177HDE15SD1CH3R L177HDE15SD1CH4F L177HDE15SD1CH4R L177HDE15SOL2 L177HDE15SVF L177HDE15SVFM L177HDEG15S L177HDEG15SOL2 L177HDEG15SOL2RM5 L177HDEG15SOL2RM8 L177HDEH15S L177HDEH15SOL2 L177HDEH15SOL2RM5 L177HDEH15SOL2RM8 L717HDA26P L717HDA26PC309 L717HDA26PD1CH3F L717HDA26PD1CH3FC309 L717HDA26PD1CH3R L717HDA26PD1CH3RC309 L717HDA26PD1CH4F L717HDA26PD1CH4FC309 L717HDA26PD1CH4R L717HDA26PD1CH4RC309 L717HDA26POL2 L717HDA26POL2C309 L717HDA26PVFC309 L717HDA26PVFM L717HDA26PVFMC309 L717HDAG26P L717HDAG26PC309 L717HDAG26POL2 L717HDAG26POL2C309 L717HDAG26POL2RM5 L717HDAG26POL2RM5C309 L717HDAG26POL2RM8 L717HDAG26POL2RM8C309 L717HDAH26P L717HDAH26PC309