

# Ethernet Switch

## 10/100 Mbps



### HUB-905M and HUB-908M:



### HUB-916M and HUB-924M:



### Features:

- Complies with IEEE802.3, IEEE 802.3u standards.
- Supports IEEE 802.3x flow control for full duplex and half duplex modes.
- Expandable by cascading more hubs together.

#### HUB-905M and HUB-908M:

- 5 or 8, 10/100Mbps auto-negotiation RJ45 uplink ports supporting auto-MDI/MDI-X.
- Supports MAC address auto-learning and auto-aging.
- LED indicators for monitoring power, link, activity.
- Plastic case, desktop or wall-mounting design.
- External power adapter supplied.

#### HUB-916M and HUB-924M:

- 16 or 24 10/100Mbps auto-negotiation RJ45 ports supporting auto-MDI/MDI-X.
- Supports MAC address auto-learning and auto-aging.
- LED indicators for monitoring power, link, activity, 100Mbps.
- Standard 19-inch rack-mountable steel case
- Internal universal power supply.

### Specifications:

Standards	: IEEE802.3 10Base-T, IEEE802.3u 100Base-TX.	
Protocol	: CSMA/CD.	
Data transfer rate	Ethernet	: 10Mbps (half duplex), 20Mbps (full duplex)
	Fast Ethernet	: 100Mbps (half duplex), 200Mbps (full duplex).
Network media (cable)	10Base-T	: UTP category 3, 4, 5 cable (maximum 100m)
		EIA/TIA-568 100U STP (maximum 100m)
	100Base-Tx	: UTP category 5, 5e cable (maximum 100m)
		EIA/TIA-568 100U STP (maximum 100m).
MAC address learning	: Automatically learning, automatically update.	

#### HUB-905M and HUB-908M:


Power supply output	: 12V, 50 to 60Hz, 0.35A to 5 port
	: 9V, 50 to 60Hz, 0.8A to 8 port.

#### HUB-916M and HUB-924M:

Number of ports	: 16 or 24 10/100Mbps auto-negotiation ports.
-----------------	---

# Ethernet Switch

10/100 Mbps



## Specification Table

Description	Dimensions			Part Number
	A	B	C	
Ethernet Switch, 10/100, 5 Port	30	140	85	HUB-905M
Ethernet Switch, 10/100, 8 Port				HUB-908M
Ethernet Switch, 10/100, 16 Port	44	440	180	HUB-916M
Ethernet Switch, 10/100, 24 Port				HUB-924M

Dimensions : Millimetres

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2009.

<http://www.farnell.com>  
<http://www.newark.com>  
<http://www.cpc.co.uk>

