

1.5KE Series Protection Diodes


Transient Voltage Suppressors



Features:

- Glass passivated chip junction in Molded Plastic package.
- 1500W surge capability at 1ms.
- Low zener impedance.
- Excellent clamping capability.
- Fast response time : Typically less than 1.0ps from 0 volts to BV minimum.
- Typical I_R less than $1\mu A$ above 10V.
- High temperature soldering. : $260^\circ C/10$ seconds /.375", (9.5mm) lead length/5lbs. (2.3kg) tension.
- Low clamping voltages.
- Wide voltage range.
- High transient power dissipation.
- No wear-out limitation.
- Small physical size.

1.5KE Series



Dimensions : Inches (Millimetres)

Mechanical Data

Case	: JEDEC DO-201AE molded plastic.
Terminals	: Axial leads, solderable per MIL-STD-202, Method 208.
Polarity	: Colour band denoted cathode except Bipolar.
Mounting Position	: Any.
Weight	: 0.045 ounce, 1.2 grams.



1.5KE Series Protection Diodes

Transient Voltage Suppressors



Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Ratings	Symbol	Value	Units
		1.5KE Series	
Peak Power Dissipation at $T_A = 25^\circ\text{C}$, $T_P = 1\text{ms}$ (Note 1)	P_{PK}	Minimum 1500	Watts
Steady State Power Dissipation at $T_L = 75^\circ\text{C}$ Lead Lengths 5.8 to 7.6, 7.2 to 9.5 (Note 2)	PD	5.0	
Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method) (Note 3)	I_{FSM}	200	Amps
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +175	$^\circ\text{C}$

Notes

1. Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25^\circ\text{C}$ per Fig. 2.
2. Mounted on Copper Leaf area of 0.79in^2 (20mm^2).
3. 8.3ms single half sine-wave, duty cycle = 4 pulses per minutes maximum.

RATING AND CHARACTERISTIC CURVES

1.5KE SERIES




Fig. 1-PEAK PULSE POWER RATING CURVE




Fig. 2-PULSE DERATING CURVE

1.5KE Series Protection Diodes

Transient Voltage Suppressors




Fig. 3-PULSE WAVEFORM




Fig. 4-TYPICAL JUNCTION CAPACITANCE UNIDIRECTIONAL




Fig. 5-STEADY STATE POWER DERATING CURVE




Fig. 6-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT UNIDIRECTIONAL

1.5KE Series Protection Diodes

Transient Voltage Suppressors



Uni-Directional 1500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} @ $T_L=75^\circ C$ (W)	Uni-Directional Part Number	JEDEC Part Number
5.5	6.45	7.14	10	10.5	143.0	5	1.5KE6.8A	1N6267A
9.4	10.5	11.6	1	15.6	96.0		1.5KE11A	1N6272A
13.6	15.2	16.8		22.5	67.0		1.5KE16A	1N6276A
15.3	17.1	18.9		25.2	59.5		1.5KE18A	1N6277A
18.8	20.9	23.1		30.6	49.0		1.5KE22A	1N6279A
23.1	25.7	28.4		37.5	40.0		1.5KE27A	1N6281A
25.6	28.5	31.5		41.4	36.0		1.5KE30A	1N6282A
28.2	31.4	34.7		45.7	33.0		1.5KE33A	1N6283A
30.8	34.2	37.8		49.9	30.0		1.5KE36A	1N6284A
40.2	44.7	49.4		64.8	23.2		1.5KE47A	1N6287A
136.0	152.0	162.0		219.0	6.8		1.5KE160A	1N6300A
342.0	380.0	420.0		548.0	4.0		1.5KE400A	—

Bi-Directional 1500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} @ $T_L=75^\circ C$ (W)	Bi-Directional Part Number	JEDEC Part Number
5.8	6.45	7.14	10	10.5	143.0	5	1.5KE6.8CA	1N6267CA
9.4	10.5	11.6	1	15.6	96.0		1.5KE11CA	1N6272CA
13.6	15.2	16.8		22.5	67.0		1.5KE16CA	1N6276CA
15.3	17.1	18.9		25.2	59.5		1.5KE18CA	1N6277CA
18.8	20.9	23.1		30.6	49.0		1.5KE22CA	1N6279CA
23.1	25.7	28.4		37.5	40.0		1.5KE27CA	1N6281CA
25.6	28.5	31.5		41.4	36.0		1.5KE30CA	1N6282CA
28.2	31.4	34.7		45.7	33.0		1.5KE33CA	1N6283CA
30.8	34.2	37.8		49.9	30.0		1.5KE36CA	1N6284CA
40.2	44.7	49.4		64.8	23.2		1.5KE47CA	1N6287CA
136.0	152.0	168.0		219.0	6.8		1.5KE160CA	1N6300CA
342.0	380.0	420.0		548.0	4.0		1.5KE400CA	—



1.5KE Series Protection Diodes

Transient Voltage Suppressors



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

