


B45194R, Tantalum, MnO2 Tantalum, 150 uF, 20%, 6.3 V, SMD, Molded, Low Profile, Low ESR, Surge Robust, 150 mOhms, 7343, Height Max = 2mm



Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2mm MAX
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
K	1.7mm TYP

Packaging Specifications

Packaging:	T&R, 178mm
Packaging Quantity:	1000

General Information

Supplier:	KEMET
Series:	B45194R
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, Molded, Low Profile, Low ESR, Surge Robust
Features:	Low Profile, Low ESR, Surge Robust
RoHS:	Yes
Termination:	Tin
Notes:	Obsolete. Old Part Number [Obsolete] Was B45194R1157M409

Specifications

Capacitance:	150 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	8%
Failure Rate:	N/A
Resistance:	0.15 Ohms (100kHz)
Current:	910 mAmps (25C), 819 mAmps (85C), 364 mAmps (125C)
Leakage Current:	9.5 uA