



RECOMMENDED P.C. BOARD HOLE LAYOUT



SECTION J-J



	DIM. 'A'	DIM. 'B'	DIM. 'C'	DIM. 'D'	DIM. 'E'						
06	(1.68) .066	(8.43) .332	(5.08) .200	(1.68) .066							
08	(1.68) .066	(10.97) .432	(7.62) .300	(1.68) .066							
10	(1.68) .066	(13.51) .532	(10.16) .400	(4.22) .166							
12	(1.68) .066	(16.05) .632	(12.70) .500	(4.22) .166							
14	(1.68) .066	(18.59) .732	(15.24) .600	(6.76) .266							
16	(1.68) .066	(21.13) .832	(17.78) .700	(6.76) .266							
18	(1.68) .066	(23.67) .932	(20.32) .800	(9.30) .366							
20	(1.68) .066	(26.21) 1.032	(22.86) .900	(1.68) .066	(19.46) .766						
22	(1.68) .066	(28.75) 1.132	(25.40) 1.000	(1.68) .066	(22.00) .866						
24	(1.68) .066	(31.29) 1.232	(27.94) 1.100	(1.68) .066	(24.54) .966						
CKT.	(1.68) .066	(33.83) 1.332	(30.48) 1.200	(1.68) .066	(27.08) 1.066						
26	(1.68) .066	(36.37) 1.432	(33.02) 1.300	(1.68) .066	(29.62) 1.166						
30	(1.68) .066	(38.91) 1.532	(35.56) 1.400	(1.68) .066	(32.16) 1.266						
32	(1.68) .066	(41.45) 1.632	(38.10) 1.500	(1.68) .066	(34.70) 1.366						
34	(1.68) .066	(43.99) 1.732	(40.64) 1.600	(1.68) .066	(37.24) 1.466						
36	(1.68) .066	(46.53) 1.832	(43.18) 1.700	(1.68) .066	(39.78) 1.566						
38	(1.68) .066	(49.07) 1.932	(45.72) 1.800	(1.68) .066	(42.32) 1.666						
40	(1.68) .066	(51.61) 2.032	(48.26) 1.900	(1.68) .066	(44.86) 1.766						
42	(1.68) .066	(54.15) 2.132	(50.80) 2.000	(1.68) .066	(47.40) 1.866						
44	(1.68) .066	(56.69) 2.232	(53.34) 2.100	(1.68) .066	(49.94) 1.966						
46	(1.68) .066	(59.23) 2.332	(55.88) 2.200	(1.68) .066	(52.48) 2.066						
48	(1.68) .066	(61.77) 2.432	(58.42) 2.300	(1.68) .066	(55.02) 2.166						
50	(1.68) .066	(64.31) 2.532	(60.96) 2.400	(1.68) .066	(57.56) 2.266						
52	(1.68) .066	(66.85) 2.632	(63.50) 2.500	(1.68) .066	(60.10) 2.366						
54	(1.68) .066	(69.39) 2.732	(66.04) 2.600	(1.68) .066	(62.64) 2.466						
56	(1.68) .066	(71.93) 2.832	(68.58) 2.700	(1.68) .066	(65.18) 2.566						
58	(1.68) .066	(74.47) 2.932	(71.12) 2.800	(1.68) .066	(67.72) 2.666						
60	(1.68) .066	(77.01) 3.032	(73.66) 2.900	(1.68) .066	(70.26) 2.766						
62	(1.68) .066	(79.55) 3.132	(76.20) 3.000	(1.68) .066	(72.80) 2.866						
64	(1.68) .066	(82.09) 3.232	(78.74) 3.100	(1.68) .066	(75.34) 2.966						
66	(1.68) .066	(84.63) 3.332	(81.28) 3.200	(1.68) .066	(77.88) 3.066						
68	(1.68) .066	(87.17) 3.432	(83.82) 3.300	(1.68) .066	(80.42) 3.166						U ADD -3003 OPT LSP3004-2508 DMORGAN 04/05/20
70	(1.68) .066	(89.71) 3.532	(86.36) 3.400	(1.68) .066	(82.96) 3.266						T LEAD FREE LSP3004-1170 RL WHITE 04/04/26
72	(1.68) .066	(92.25) 3.632	(88.90) 3.500	(1.68) .066	(85.50) 3.366						S ADD -8002 OPT LSP3004-1250 DMORGAN 04/07/12

MATERIAL:

SHROUDED WAFER: GLASS FILLED POLYESTER, 94V-0; COLOR: BLACK.
PINS: PHOSPHOR BRONZE,
SEE SHEET 2 FOR FINISHES.

ASSEMBLY STYLE "A" AND "B"

DIMENSIONS SHOWN METRIC INCH		MFG. QTY. REV. I.T.R.		REVISIONS	
1. REUSE ONLY ON CAD SYSTEM 2.		TITLE			
3.		SALES ASSEMBLY			
4.		WAFER - STRAIGHT MT. FULLY SO. PINS .000 GRID-FOG W/ .006 END WALLS WITH .006 END WALLS			
5.		MOLEX INCORPORATED		SHEET NO.	DATE
6.		LIBRARY: 69532		1 OF 7	92/07/17
7.		PART		DRAWING	
8.		SEE CHART		SDA-8723-73	
9.		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			
10.		DRAWN BY: 58273AK1		DATE:	SIZE:
11.		APPROVED BY: RB		DATE:	SIZE:
12.		SCALE: 4:1			

