




FEATURES

- Max. propagation delay of 750ps
- IEE min. of -25mA
- Industry standard 100K ECL levels
- Extended supply voltage option:
VEE = -4.2V to -5.5V
- Voltage and temperature compensation for improved noise immunity
- 20% faster than Fairchild 300K at lower power
- Internal 75KΩ input pull-down resistors
- Function and pinout compatible with Fairchild F100K
- Available in 24-pin CERPACK and 28-pin PLCC packages



BLOCK DIAGRAM



DESCRIPTION

The SY100S301 is an ultra-fast triple 5-input OR/NOR gate designed for use in high-performance ECL systems. The inputs on this device have 75KΩ pull-down resistors.

PIN CONFIGURATIONS



PIN NAMES

Pin	Function
Dna, Dnb, Dnc	Data Inputs (n-1...5)
Oa, Ob, Oc	Data Outputs
Oa, Ob, Oc	Complementary Data Outputs
VEE	VEE Substrate
VCCA	Vcco for ECL Outputs

LOGIC EQUATION

$$O_a = D_{1a} + D_{2a} + D_{3a} + D_{4a} + D_{5a}$$

$$O_b = D_{1b} + D_{2b} + D_{3b} + D_{4a} + D_{5b}$$

$$O_c = D_{1c} + D_{2c} + D_{3c} + D_{4c} + D_{5c}$$

GUARANTEED OPERATING CONDITIONS

Symbol	Parameter	Min.	Typ.	Max.	Unit
VEE	Input HIGH Current	-5.5	-4.5	-4.2	V
TA	Power Supply Current	0	25	85	°C

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

Symbol	Rating	Value	Unit
VEE	Power Supply	-0.5 to +7.0	V
VIN	Input Voltage	-0.5 to VEE	V
IOU	DC Output Current	-50	mA
TC	Temperature Under Bias	-55 to +125	°C
TJ	Junction Temperature	+150	°C
Tstore	Storage Temperature	-65 to +150	°C

NOTE:

1. Permanent device damage may occur if ABSOLUTE MAXIMUM RATINGS are exceeded. This is a stress rating only and functional operation is not implied at conditions other than those detailed in the operational sections of this data book. Exposure to ABSOLUTE MAXIMUM RATING conditions for extended periods may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

VEE = -4.2V to -5.5V unless otherwise specified, VCC = VCCA = GND

Symbol	Parameter	Min.	Typ.	Max.	Unit	Condition
I _{IH}	Input HIGH Current	—	—	200	μA	—
I _{EE}	Power Supply Current	-25	-17	-11	mA	Inputs Open

AC ELECTRICAL CHARACTERISTICS**CERPACK**

VEE = -4.2V to -5.5V unless otherwise specified, VCC = VCCA = GND


Symbol	Parameter	TA = 0°C		TA = +25°C		TA = +85°C		Unit	Condition
		Min.	Max.	Min.	Max.	Min.	Max.		
t _{PLH} t _{PHL}	Propagation Delay Data to Output	300	800	300	800	300	800	ps	
t _{TLH} t _{THL}	Transition Time 20% to 80%, 80% to 20%	300	900	300	900	300	900	ps	

PLCC

VEE = -4.2V to -5.5V unless otherwise specified, VCC = VCCA = GND

Symbol	Parameter	TA = 0°C		TA = +25°C		TA = +85°C		Unit	Condition
		Min.	Max.	Min.	Max.	Min.	Max.		
t _{PLH} t _{PHL}	Propagation Delay Data to Output	300	750	300	750	300	750	ps	
t _{TLH} t _{THL}	Transition Time 20% to 80%, 80% to 20%	300	900	300	900	300	900	ps	

TIMING DIAGRAM




Propagation Delay and Transition Times

PRODUCT ORDERING CODE


Ordering Code	Package Type	Operating Range
SY100S301FC	F24-1	Commercial
SY100S301JC	J28-1	Commercial
SY100S301JCTR	J28-1	Commercial

24 LEAD CERPACK (F24-1)



Rev. 03

28 LEAD PLCC (J28-1)



Rev. 03

MICREL-SYNERGY 3250 SCOTT BOULEVARD SANTA CLARA CA 95054 USA

TEL + 1 (408) 980-9191 FAX + 1 (408) 914-7878 WEB <http://www.micrel.com>

This information is believed to be accurate and reliable, however no responsibility is assumed by Micrel for its use nor for any infringement of patents or other rights of third parties resulting from its use. No license is granted by implication or otherwise under any patent or patent right of Micrel Inc.

© 2000 Micrel Incorporated