








THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION
 AUG, 2004.
 (C) COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J		A	REVISED	ECR-05-007904	29JUL05	C.Z	S.Y
ITEM	MATERIAL	FINISH					
①	COPPER ALLOY	NICKEL UNDER PLATE ALL OVER CONTACT AREA ; Au(0.0003) SOLDER TINE AREA ; TIN PLATE					
②	ZINC	NICKEL PLATING					
③	STEEL t0.25	NICKEL PLATE OVER COPPER UNDERPLATE					
④	THERMO-PLASTIC	COLOR; BLACK					
⑤							
⑥	COPPER ALLOY	TIN PLATE OVER NICKEL UNDERPLATE					



RECOMMENDED PC BOARD
 MOUNTING DIMENSION
 COMPONENT SIDE



RECOMMENDED PANEL CUTOUT
 THK, 2mm MAX

- △ RECOMMENDED SCREW SIZE ; M2.6 PANHEAD SCREW(L=5)
 2 RECOMMENDED P.C BOARD THICKNESS ; 0.6~1.0 (REF)
 3 INSERTION FORCE OF RETENTION LEG TO P.C.B; 21.56N(2.2kgf) MAX/CONNECTOR.
 4 RETENTIVITY OF RETENTION LEG TO P.C.B; 4.9N(0.5kgf) MIN/CONNECTOR.

LEAD FREE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN COREL WANG	31AUG04	Tyco Electronics AMP K.K. Kawasaki, Japan	
		CHK STEVEN YAO	31AUG04		
		APVD JENOMOTO	31AUG04		
DIMENSIONS: mm		PRODUCT SPEC 108-60043		NAME RECEPTACLE HDR ASSY (2.2mm) RETENTION LEG TYPE STANDARD CHAMP.050 SERIES (II)	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± °		APPLICATION SPEC		SIZE A2	
MATERIAL SEE TABLE		FINISH SEE TABLE		CAGE CODE 00779	
		WEIGHT		DRAWING NO 5178240	
		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 2:1		SHEET 1 of 1	
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5178240-2](#)