




## Dimensions: mm (in.)



## Circuit Diagram



## PCB Layout



## Electrical Specifications:

- Rating: 0.5A/50V DC
- Contact Resistance: 30mΩ max.
- Insulation Resistance: 100MΩ min.
- Dielectric Strength: 500VAC/minute
- Life Test: 10,000 Cycles, 15-18 Cycles/Min

## Mechanical Specifications:

- Timing: Non-shorting
- Type: SPDT
- Operating Force: 250gf ± 100gf

## Note:

- RoHS Compliant

**Slide Switch**  
103-1256-EV

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-1256-EV](#)