

Technical drawing of a probe with dimensions and tolerances:

- H REF.** NOMINAL HOLE DIAMETER $+0.010(.25)/-0.005(.13)$
- E**
- B** $\pm 0.01(.25)$
- J REF.** $\pm 0.030(.76)$
- G REF.**
- C REF.**
- F REF.**
- D REF.**
- A** $\pm 0.01(.25)$

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)													
PLWP1SA	.06 (1.5)	1.0 (25.4)	.052 (1.32)	.190 (4.8)	.230 (5.8)	.370 (9.4)	.320 (8.1)	5.1 (130)	.240 (6.1)	.187 (4.7)	.74 (18.8)	.093 (2.4)	50 (222)	STANDARD	.29 (132)
PLWP1.5SA	.06 (1.5)	1.5 (38.1)	.052 (1.32)	.190 (4.8)	.230 (5.8)	.370 (9.4)	.320 (8.1)	6.7 (170)	.240 (6.1)	.187 (4.7)	.74 (18.8)	.093 (2.4)	50 (222)	STANDARD	.34 (154)
PLWP2SA	.06 (1.5)	1.75 (44.5)	.052 (1.32)	.190 (4.8)	.230 (5.8)	.370 (9.4)	.320 (8.1)	7.7 (196)	.240 (6.1)	.187 (4.7)	.74 (18.8)	.093 (2.4)	50 (222)	STANDARD	.37 (168)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

										PANDUIT	CORP.	TINLEY PARK, ILLINOIS
										LOCKING WING PUSH MOUNT TIE		
										PLWP1SA, 1.5SA, 2SA		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX)± .020(.51) (.XX)± .02(.5) ANGLES± -----	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
									DRAWN BY KJL	MAT'L;	SCALE NONE	
6	1/21/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS	23525	6			DATE 11/22/88	SEE NOTE	DRAWING NO. SS-23525	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	CHK'D JML			SIZE