



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE1042

Integrated Circuit

3 Stage FM IF Amplifier

Absolute Maximum Ratings:

Supply Voltage, V_{CC} 20V
Input Voltage, V_{IN} $\pm 3V$
Power Dissipation, P_D 300mW
Operating Temperature Range, T_{opr} -20° to $+70^{\circ}C$
Storage Temperature Range, T_{stg} -55° to $+125^{\circ}C$

Electrical Characteristics: ($V_{CC} = 7.5V$, $T_A = +25^{\circ}C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Total Power	P_T	$f = 10.7MHz$	80	–	175	mA
Input Resistance	R_i		–	3.7	–	$k\Omega$
Input Capacitance	C_i		–	9.2	–	pF
Output Resistance	R_o		–	31.5	–	$k\Omega$
Output Capacitance	C_o		–	4.2	–	pF
Voltage Gain	G_v		55	61	–	dB
Input Limit Voltage	$V_{i(Lim)}$	$V_{CC} = 10V$, $f = 10.7MHz$	–	300	450	μV

Pin Connection Diagram

