




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R1	REVISED PER ECO-11-004917	11MAR11	RK	HMR
	R2	REVISED PER ECO-16-006924	28APR2017	RS	JO

- 1

PLATED WITH 0.00076[.000030] GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER, OVER 0.00127[.000050] NICKEL.
- 2

PLATED WITH 0.00127[.000050] GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER, OVER 0.00127[.000050] NICKEL.
- 3

PLATED WITH 0.00254[.000100] BRIGHT TIN-LEAD OVER 0.00127[.000050] NICKEL - ENTIRE CONTACT.
- 4

PLATED WITH 0.00127[.000050] GOLD OVER 0.00127[.000050] NICKEL - ENTIRE CONTACT.
- 5

SPRING MATERIAL: STAINLESS STEEL
- 6

BODY MATERIAL: PHOS BRONZE
FINISH: SEE TABLE
- 7

PLATED WITH 0.00254[.000100] BRIGHT TIN OVER 0.00127[.000050] NICKEL - ENTIRE CONTACT.

OBSOLETE	1	9-87124-1	9-87165-1
	7	87124-2	5-87165-2
	4	87124-4	87165-4
	2	87124-3	87165-3
	3	87124-2	87165-2
	1	87124-1	87165-1
	BODY FINISH	STRIP PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG 23NOV94	TE TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK S. SHUEY 23NOV94			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± -		APVD D. DUPLER 23NOV94		
	1 PLC ± -		PRODUCT SPEC		
	2 PLC ± -		108-36028		
MATERIAL AS NOTED	3 PLC ± -		APPLICATION SPEC		
	4 PLC ± -		114-25006		
	ANGLES ± -		WEIGHT -		
	FINISH SEE TABLE		CUSTOMER DRAWING		
		SIZE A2		CAGE CODE 00779	DRAWING NO C=87165
		SCALE 10:1		SHEET 1 of 1	REV R2