


REVISIONS						
P	LTR	DESCRIPTION		DATE	DWN	APVD
	C	REVISED	PER	OG3B-0197-05	4/25/05	SS GS
	C1	REVISED	PER	ECO-09-020689	25AUG09	KK AEG
	C2	REVISED	PER	ECO-17-005912	22JUL2017	RS MZ



RECOMMENDED PC BOARD LAYOUT

- △

0.76um[.000030] MIN GOLD FOR A LENGTH OF 5.08[.200] MIN FROM MATIING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 2.16 [.085] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL ON ENTIRE CONTACT.
- △

0.76um[.000030] MIN GOLD OVER 1.27um [.000050] MIN NICKEL.
- △

0.76um[.000030] MIN GOLD FOR A LENGTH OF 5.08[.200] MIN FROM MATIING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 2.16 [.085] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL ON ENTIRE CONTACT.
- △

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	OBSOLETE	2	3	POSITIONS 10 AND 21	POSITIONS 18 AND 20	POSITIONS 1 THRU 9, 11 THRU 17,19,22,23	213768-6
	OBSOLETE	2	3	POSITION 23	NONE	POSITIONS 1 THRU 22	213768-5
		2	3	NONE	NONE	ALL POSITIONS	213768-4
4 4	OBSOLETE	2	1	POSITIONS 10 AND 21	POSITIONS 18 AND 20	POSITIONS 1 THRU 9, 11 THRU 17,19,22,23	213768-3
	OBSOLETE	2	1	POSITION 23	NONE	POSITIONS 1 THRU 22	213768-2
	OBSOLETE	2	1	NONE	NONE	ALL POSITIONS	213768-1
	GROUND CONTACT FINISH		SIGNAL CONTACT FINISH	EMPTY CIRCUITS	GROUND CONTACTS	SIGNAL CONTACTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.LENKER CHK J.McCLINTON	11/02/92 11-16-92	TE Connectivity		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC	± -	PRODUCT SPEC		
		1 PLC	± -	APPLICATION SPEC		
		2 PLC	± 0.13 [.005]	SIZE		
		3 PLC	± -	CAGE CODE		
MATERIAL HOUSING: POLYESTER, UL94V-0 BLACK		4 PLC	± -	DRAWING NO		
CONTACTS: BRASS PER QQ-B-626		ANGLES	± -	RESTRICTED TO		
		FINISH	-	A100779C=213768		
CUSTOMER DRAWING				SCALE 2:1 SHEET 1 OF 1 REV C2		