

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 20M (65-ft.)

MODEL NUMBER: **N320-20M-RD**



### Description

Tripp Lite's Red, 20-meter multimode duplex micron fiber optic LC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC connectors on each end, a PVC jacket, and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications. Ideal for color coding the cable plant.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 20 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI)and OFNR rated

## Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)
Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	LC/LC

### Highlights

- Manufactured from 62.5/125 duplex (zipcord) fiber with Red jacket
- Length: 20 meter Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical)

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

### Package Includes

- 20M Duplex MMF Cable LC/LC 62.5/125 Micron Fiber Red Jacket

Network Speed	1Gbps
<b>INPUT</b>	
Cable Length (m)	20
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332130815
<b>PHYSICAL</b>	
Color	Red
Style	Fiber Optic
<b>CONNECTIONS</b>	
Connector A	LC
Connector B	LC
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.