





Tous droits réservés. Toute réimpression ou utilisation non autorisée sans la permission écrite de la FCI est formellement interdite.
All rights strictly reserved. Reproduction or unauthorized use without the written authority of FCI is hereby expressly prohibited.
Copyright © 2005 FCI

PRODUCT NUMBER
77320-YXX

TOP VIEW




RECOMMENDED HOLE PATTERN



NOTES:

- 1 - PIN MATERIAL : COPPER ALLOY.
- 2 - MATERIAL BODY : POLAMID 30% GLASS-FILLED , FLAME RETARDANT PER UL-V0 COLOR BLACK.
- 3 - PIN PUSH OUT FORCE : 6N MIN.

PART NUMBER DEFINITION




mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI ELECTRONICS		
ltr	ecr no	dr	date	linear	angles		www.fciconnect.com		
L	F70654	OMA	97.10.23	linear	angles	projection	title		
M	F70815	OMA	97.12.23			mm	HEADER RA,DR, WIDE BODY, POL, DUPX		
N	F80121	JMC	98.01.29	linear	angles	mm	product family		
P	F90196	LMU	99.03.29			mm	BSTIK		
R	F03-0201	LMU	03.04.23	linear	angles	mm	size		
K	F70629	JMC	97.09.25			mm	dwg no		
sheet	revision	R	G	E	M	B	scale		
index	sheet	1	2	3	4	5	5:1		
							A3		
							77320		
							1 of 5		

Tous droits réservés. Toute réimpression ou utilisation non autorisée sans la permission écrite de la société FCI Electronics S.A. est formellement interdite.




All rights reserved. Any reprinting or unauthorized use without the written permission of FCI Electronics S.A. is expressly prohibited.



PRODUCT NUMBER	PRODUCT DEFINITION						
	POS	"A" ±0.2	"B" ±0.35	"C" REF	"J" REF	"M" REF	"N" REF
77320-X02	2X2	5.84	2.83	1.52	12.44	5.08	2.54
77320-X03	2X3	5.84	2.83	1.52	12.44	7.62	5.08
77320-X04	2X4	5.84	2.83	1.52	12.44	10.16	7.62
77320-X05	2X5	5.84	2.83	1.52	12.44	12.7	10.16
77320-X06	2X6	5.84	2.83	1.52	12.44	15.24	12.7
77320-X07	2X7	5.84	2.83	1.52	12.44	17.78	15.24
77320-X08	2X8	5.84	2.83	1.52	12.44	20.32	17.78
77320-X09	2X9	5.84	2.83	1.52	12.44	22.86	20.32
77320-X10	2X10	5.84	2.83	1.52	12.44	25.4	22.86
77320-X11	2X11	5.84	2.83	1.52	12.44	27.94	25.4
77320-X12	2X12	5.84	2.83	1.52	12.44	30.48	27.94
77320-X13	2X13	5.84	2.83	1.52	12.44	33.02	30.48
77320-X14	2X14	5.84	2.83	1.52	12.44	35.56	33.02




77320-9XX	0.2µm Au	4µm SnPb
77320-8XX	0.38µm Au	4µm SnPb
77320-4XX	4µm Sn Pb	
77320-2XX	1.27µm Au	4µm SnPb
77320-1XX	0.76µm Au	4µm SnPb
PLATING CODE	CONTACT AREA	REMAINDER
	PLATING THICKNESS OVER 1.27µm Ni	




mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 ELECTRONICS www.fciconnect.com	
ltr	ecn no	dr	date	linear			projection 	title		
D	F20566	JMC	92.10.19					HEADER,DR,RA, WIDE BODY,POL, DUPX		
E	F60279	OMA	96.04.09	angles				product family		
F	F60884	OMA	96.12.05					BSTIK		
G	F03-020	LMU	03.04.23	dr O.	MATHEVON	96.04.09	scale	size		
				engr	COMPAGNON J	96.04.09		dwg no		
				chr	COMPAGNON J	96.04.09	N/A	A3		
				appd	JMC	96.04.09		77320		
sheet index		revision sheet								
			</							

Tous droits strictement réservés. Reproduction ou communication des titres illustrés sans autorisation écrite du propriétaire.
All rights strictly reserved. Reproduction or communication of titles in any form without written authority from the proprietor.
Copyright © Bessone S. A.



PRODUCT NUMBER	PRODUCT DEFINITION						
	POS	"A" ±0.2	"B" ±0.35	"C" REF	"J" REF	"M" REF	"N" REF
77320-X15	2X15	5.84	2.83	1.52	12.44	38.1	35.56
77320-X16	2X16	5.84	2.83	1.52	12.44	40.64	38.1
77320-X17	2X17	5.84	2.83	1.52	12.44	43.18	40.64
77320-X18	2X18	5.84	2.83	1.52	12.44	45.72	43.18
77320-X19	2X19	5.84	2.83	1.52	12.44	48.26	45.72
77320-X20	2X20	5.84	2.83	1.52	12.44	50.8	48.26
77320-X21	2X21	5.84	2.83	1.52	12.44	53.34	50.8
77320-X22	2X22	5.84	2.83	1.52	12.44	55.88	53.34
77320-X23	2X23	5.84	2.83	1.52	12.44	58.42	55.88
77320-X24	2X24	5.84	2.83	1.52	12.44	62.96	58.42
77320-X25	2X25	5.84	2.83	1.52	12.44	63.5	62.96
77320-X26	2X26	5.84	2.83	1.52	12.44	66.04	63.5
77320-X27	2X27	5.84	2.83	1.52	12.44	68.58	66.04
77320-X28	2X28	5.84	2.83	1.52	12.44	71.12	68.58
77320-X29	2X29	5.84	2.83	1.52	12.44	73.66	71.12




mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 ELECTRONICS www.fciconnect.com			
ltr	ecn no	dr	date	linear			projection 	title HEADER,DR,RA, WIDE BODY,POL, DUPX			
D	F20566	JMC	92.10.19								
E	F60279	OMA	96.04.09	angles				product family		BSTIK	code
				dr O.	MATHEVON	96.04.09		size		dwg no	213
				engr	COMPAGNON J	96.04.09	scale N/A	A3		77320	sheet
				chr	COMPAGNON J	96.04.09					3 of
				app	JMC	96.04.09					
sheet	revision										
index	sheet										


Tous droits strictement réservés. Reproduction ou communication des titres, notices, plans, schémas ou autres documents sans autorisation écrite du propriétaire.
All rights strictly reserved. Reproduction or communication of titles, notices, drawings, schematics or other documents without written authority from the proprietor.
Copyright © Bessone S. A.





PRODUCT NUMBER	PRODUCT DEFINITION						
	POS	"A" ±0.2	"B" ±0.35	"C" REF	"J" REF	"M" REF	"N" REF
77320-X30	2X30	5.84	2.83	1.52	12.44	76.2	73.66
77320-X31	2X31	5.84	2.83	1.52	12.44	78.74	76.2
77320-X32	2X32	5.84	2.83	1.52	12.44	81.28	78.74
77320-X33	2X33	5.84	2.83	1.52	12.44	83.82	81.28
77320-X34	2X34	5.84	2.83	1.52	12.44	86.36	83.82
77320-X35	2X35	5.84	2.83	1.52	12.44	88.9	86.36
77320-X36	2X36	5.84	2.83	1.52	12.44	91.44	88.9
77320-X37	2X13	8.08	2.83	1.52	12.44	33.02	30.48
77320-X38	2X10	8.08	2.83	1.52	12.44	25.4	22.86
77320-X39	2X17	8.08	2.83	1.52	14.68	43.18	40.64
77320-X40	2X11	8.08	2.83	1.52	14.68	27.94	25.4
77320-X41	2X09	8.08	2.83	1.52	14.68	22.86	20.32
77320-X42	2X11	10.9	2.9	1.52	17.5	27.94	25.4
77320-X43	2X14	10.9	2.9	1.52	17.5	35.56	33.02
77320-X44	2X14	5.84	2.83	1.52	12.44	50.8	48.26



VIEW OF MISSING PINS POSITION
FROM TOP VIEW







mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 ELECTRONICS www.fciconnect.com		
litr	ecn no	dr	date	linear				projection 	title HEADER,DR,RA, WIDE BODY,POL, DUPX			
L	F70815	OMA	97.12.23									
M	F80121	JMC	98.01.29									
				angles								
G	F60666	JMC	96.09.24	dr O.	MATHEVON		96.04.09	mm ↔	product family		BSTIK	code
H	F60726	JMC	96.10.18	engr	COMPAGNON J		96.04.09		size		dwg no	213
J	F70629	JMC	97.09.25	chr	COMPAGNON J		96.04.09	scale N/A	A3		77320	
K	F70654	OMA	97.10.23	appd	JMC		96.04.09					
sheet	revision											
index	sheet											

Tous droits réservés. Reproduction ou utilisation sans autorisation écrite du propriétaire.
All rights reserved. Reproduction or use without written authority from the proprietor.
Copyright © Bessone S. A.

All rights reserved. Reproduction or use without written authority from the proprietor.
All rights reserved. Reproduction or use without written authority from the proprietor.
Copyright © Bessone S. A.

PRODUCT NUMBER	PRODUCT DEFINITION						
	POS	"A" ±0.2	"B" ±0.35	"C" REF	"J" REF	"M" REF	"N" REF
77320-X45	2X06	5.08	3.05	1.52	11.68	15.24	12.7
77320-X46	2X29	5.84	3.05	1.52	12.44	73.66	71.12
77320-X47	2X36	5.84	3.05	1.52	12.44	91.44	88.9



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 ELECTRONICS www.fciconnect.com		
ltr	ecn no	dr	date	linear		projection 	title HEADER,DR,RA, WIDE BODY,POL, DUPX		
A	F90196	LMU	99.03.29						
B	F03-0201	LMU	03.04.23	angles		mm 	product family size dwg no		
				dr	MULIN L	99.03.29	code 213		
				engr	COMPAGNON J	99.03.29			
				chr	COMPAGNON J	99.03.29	sheet 5 of -		
				app	JMC	99.03.29			
sheet index	revision sheet						A3	77320	