



Silicon Planar Voltage Regulator Diode

Feature:

Low voltage general purpose voltage regulator diode.



Absolute Maximum Ratings ($T_a = 25^{\circ}\text{C}$)

Description	Symbol	Value	Unit
Working Voltage Tolerance		± 5	%
Repetitive Peak Forward Current	I_{FRM}	250	mA
Repetitive Peak Working Current	I_{ZRM}		
Power Dissipation upto $T_a = 25^{\circ}\text{C}$	$*P_D$	300	mW
Power Dissipation upto $T_c = 25^{\circ}\text{C}$	$**P_D$	250	
Junction Temperature	T_j	150	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	- 65 to + 150	

Thermal Resistance

Junction to Ambient	$*R_{th(j-a)}$	420	K/W
---------------------	----------------	-----	-----

* Device mounted on a ceramic alumna.

** Device mounted on an FR5 printed circuit board.

Forward Voltage at $V_F < 0.9\text{V}$ at 10mA and $< 1.5\text{V}$ at 200mA.

Electrical Characteristics (Ta=25°C unless specified otherwise)

Working Voltage ***V _Z (± 5%) (V) at I _Z test = 5mA		Differential Resistance rdiff (Ω) at I _Z test = 5mA	Temperature Coefficient S _Z (mV/K) at I _Z test = 5mA		Differential Resistance rdiff (Ω) at I _Z test = 1mA	I _R at V _R μA		Marking	Part Numbers
min	max	max	min	max	Max	max	(V)		
9.40	10.60	20	4.5	8.0	150	0.2	7.0	Z9	BZX84C10
10.40	11.60	20	5.4	9.0	150	0.1	8	Y1	BZX84C11
11.40	12.70	25	6.0	10	150	0.1	8	Y2	BZX84C12
12.40	14.10	30	7.0	11	170	0.1	8	Y3	BZX84C13
13.80	15.60	30	9.2	13	200	0.05	10.5	Y4	BZX84C15
15.30	17.10	40	10.4	14	200	0.05	11.2	Y5	BZX84C16
16.80	19.10	45	12.4	16	225	0.05	12.6	Y6	BZX84C18
18.80	21.20	55	14.4	18	225	0.05	14.0	Y7	BZX84C20
20.80	23.30	55	16.4	20	250	0.05	15.4	Y8	BZX84C22
22.80	25.60	70	18.4	22	250	0.05	16.8	Y9	BZX84C24
at I _Z test = 2mA		at I _Z test = 2mA	at I _Z test = 2mA		at I _Z test = 0.5mA				
25.10	28.90	80	21.4	25.3	300	0.05	18.9	Y10	BZX84C27
28.00	32.00	80	24.4	29.4	300	0.05	21.0	Y11	BZX84C30
31.00	35.00	80	27.4	33.4	325	0.05	23.1	Y12	BZX84C33
34.00	38.00	90	30.4	37.4	350	0.05	25.2	Y13	BZX84C36
37.00	41.00	130	33.4	41.2	350	0.05	27.3	Y14	BZX84C39
40.00	46.00	150	37.6	46.6	375	0.05	30.1	Y15	BZX84C43
44.00	50.00	170	42.0	51.8	375	0.05	32.9	Y16	BZX84C47
4.40	5.00	80	- 3.5	0.2	500	3.0	2.0	Z1	BZX84C4V7
48.00	54.00	180	46.6	57.2	400	0.05	35.7	Y17	BZX84C51
4.80	5.40	60	- 2.7	1.2	480	2.0	2.0	Z2	BZX84C5V1
5.20	6.00	40	- 2.0	2.5	400	1.0	2.0	Z3	BZX84C5V6
5.80	6.60	10	0.4	3.7	150	3.0	4.0	Z4	BZX84C6V2
7.00	7.90	15	2.5	5.3	80	1.0	5.0	Z6	BZX84C7V5
7.70	8.70	15	3.2	6.2	80	0.7	5.0	Z7	BZX84C8V2
8.50	9.60	15	3.8	7.0	100	0.5	6.0	Z8	BZX84C9V1

*** Pulse Test 20ms ≤tp ≤50ms

Notes:

International Sales Offices:

	AUSTRALIA – Farnell Tel No: ++61 1300 361 005 Fax No: ++61 1300 361 225		FINLAND – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ITALY – Farnell Tel No: ++ 39 02 93 995 200 Fax No: ++ 39 02 93 995 300		SPAIN – Farnell Tel No: 901 20 20 80 Fax No: 901 20 20 90
	AUSTRIA – Farnell Tel No: ++ 43 662 2180 680 Fax No: ++ 43 662 2180 670		FRANCE – Farnell Tel No: ++ 33 474 68 99 99 Fax No: ++ 33 474 68 99 90		MALAYSIA – Farnell-Newark Tel No: ++ 60 3 7873 8000 Fax No: ++ 60 3 7873 7000		SWEDEN – Farnell Tel No: ++ 46 8 730 50 00 Fax No: ++ 46 8 83 52 62
	BELGIUM – Farnell Tel No: ++ 32 3 475 2810 Fax No: ++ 32 3 227 3648		GERMANY – Farnell Tel No: ++ 49 89 61 39 39 39 Fax No: ++ 49 89 613 59 01		NETHERLANDS – Farnell Tel No: ++ 31 30 241 7373 Fax No: ++ 31 30 241 7333		SWITZERLAND – Farnell Tel No: ++ 44 204 64 64 Fax No: ++ 44 204 64 54
	BRAZIL – Farnell-Newark Tel No: ++ 55 11 4066 9400 Fax No: ++ 55 11 4066 9410		HONG KONG – Farnell-Newark Tel No: ++ 852 2268 9888 Fax No: ++ 852 2268 9899		NEW ZEALAND – Farnell Tel No: 0800 90 80 80 Fax No: 0800 90 80 81		UK – Farnell Tel No: ++ 44 8701 200 200 Fax No: ++ 44 8701 200 201
	CHINA – Farnell-Newark Tel No: ++86 10 6238 5152 Fax No: ++86 10 6238 5022		HUNGARY – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		NORWAY – Farnell Tel No: 800 146 70 Fax No: 800 146 76		UK – CPC ++ 44 8701 202 530 ++ 44 8701 202 531
	CZECH REPUBLIC – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		INDIA – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		PORTUGAL – Farnell Tel No: ++ 34 93 475 8804 Fax No: ++ 34 93 474 5288		USA – Newark Tel No: 800 463 9275
	DENMARK – Farnell Tel No: ++ 45 44 53 66 44 Fax No: ++ 45 44 53 66 06		IRELAND – Farnell Tel No: ++ 353 1 830 9277 Fax No: ++ 353 1 830 9016		RUSSIA – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 EXPORT – Farnell Tel No: ++ 44 8701 200 208 Fax No: ++ 44 8701 200 209 For enquiries from all other markets	
	ESTONIA – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ISRAEL – Farnell Tel No: ++ 180 937 0015 Fax No: ++ 180 937 0014		SINGAPORE – Farnell-Newark Tel No: ++ 65 6788 0200 Fax No: ++ 65 6788 0300		

<http://www.farnell.com>
<http://www.newark.com>
<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.