


**Part Number: 68114-1562**

High Density D-Subminiature Shielded I/O PCB Female Receptacle, Right Angle, 15 Circuits, Hexagon Nut, Lead-Free



Series image - Reference only

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	Contact Molex
<b>Series:</b>	68114
<b>Category:</b>	I/O Connectors

**Product Environmental Compliance**EU RoHS: ELV and RoHS CompliantChina RoHS: REACH SVHC:Low-Halogen Status: Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	I/O Connectors
Series	<a href="#">68114</a>
Application	Wire-to-Board
Component Type	Plug
Product Name	D-Sub
Type	N/A

**Physical**

Boot Color	N/A
Circuits (Loaded)	15
Circuits (maximum)	15
Durability (mating cycles max)	500
Gender	Receptacle
Keying to Mating Part	None
Lock to Mating Part	No
Material - Plating Mating	Gold
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.29mm
Pitch - Termination Interface	2.29mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	3A
Grounding to Panel	Yes
Shield Type	Full Shield
Shielded	Yes

Voltage - Maximum: 350V AC (RMS)/DC

**Material Info****Reference - Drawing Numbers**

Product Specification	PS-68114-002
Sales Drawing	SD-68114-002

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)