

International **IR** Rectifier

INSULATED GATE BIPOLAR TRANSISTOR

Features

- Standard: optimized for minimum saturation voltage and low operating frequencies (< 1kHz)
- Lead-Free, RoHS Compliant
- Automotive Qualified *

Benefits

- Typical Applications: PTC Heater, Discharge Switch & Relay Replacements


AUTOMOTIVE GRADE

PD - 96340

AUIRG4BC30S-S

AUIRG4BC30S-SL

Standard Speed IGBT



Absolute Maximum Ratings

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other condition beyond those indicated in the specifications is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions. Ambient temperature (T_A) is 25°C, unless otherwise specified

	Parameter	Max.	Units
G	C	E	
Gate	Collector	Emitter	
V_{CES}	Collector-to-Emitter Breakdown Voltage	600	V
I_C @ $T_C = 25^\circ\text{C}$	Continuous Collector Current	34	A
I_C @ $T_C = 100^\circ\text{C}$	Continuous Collector Current	18	
I_{CM}	Pulsed Collector Current ①	68	
I_{LM}	Clamped Inductive Load Current ②	68	
V_{GE}	Gate-to-Emitter Voltage	±20	V
E_{ARV}	Reverse Voltage Avalanche Energy ③	10	mJ
P_D @ $T_C = 25^\circ\text{C}$	Maximum Power Dissipation	100	W
P_D @ $T_C = 100^\circ\text{C}$	Maximum Power Dissipation	42	
T_J	Operating Junction and	-55 to +150	
T_{STG}	Storage Temperature Range		°C
	Soldering Temperature, for 10 seconds	300 (0.063 in. (1.6mm) from case)	

Thermal Resistance

	Parameter	Typ.	Max.	Units
R_{eJC}	Junction-to-Case	—	1.2	°C/W
R_{eCS}	Case-to-Sink, Flat, Greased Surface	0.50	—	
R_{eJA}	Junction-to-Ambient, typical socket mount	—	40	
Wt	Weight	1.44	—	g (oz)

* When mounted on 1" square PCB (FR-4 or G-10 Material). For recommended footprint and soldering techniques refer to application note #AN-994.

AUIRG4BC30S-S/SL

International
IR Rectifier

Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(\text{BR})\text{CES}}$	Collector-to-Emitter Breakdown Voltage	600	—	—	V	$V_{\text{GE}} = 0\text{V}$, $I_C = 250\mu\text{A}$
$V_{(\text{BR})\text{ECS}}$	Emitter-to-Collector Breakdown Voltage ④	18	—	—	V	$V_{\text{GE}} = 0\text{V}$, $I_C = 1.0\text{A}$
$\Delta V_{(\text{BR})\text{CES}/\Delta T_J}$	Temperature Coeff. of Breakdown Voltage	—	0.75	—	$^\circ\text{C}$	$V_{\text{GE}} = 0\text{V}$, $I_C = 1.0\text{mA}$
$V_{\text{CE}(\text{ON})}$	Collector-to-Emitter Saturation Voltage	—	1.40	1.6	V	$I_C = 18\text{A}$ $V_{\text{GE}} = 15\text{V}$
		—	1.84	—		$I_C = 34\text{A}$ See Fig. 2, 5
		—	1.45	—		$I_C = 18\text{A}$, $T_J = 150^\circ\text{C}$
		3.0	—	6.0		$V_{\text{CE}} = V_{\text{GE}}$, $I_C = 250\mu\text{A}$
$\Delta V_{\text{GE}(\text{th})/\Delta T_J}$	Temperature Coeff. of Threshold Voltage	—	-11	—	$\text{mV}/^\circ\text{C}$	$V_{\text{CE}} = V_{\text{GE}}$, $I_C = 250\mu\text{A}$
g_{fe}	Forward Transconductance ⑤	6.0	11	—	S	$V_{\text{CE}} = 100\text{V}$, $I_C = 18\text{A}$
I_{CES}	Zero Gate Voltage Collector Current	—	—	250	μA	$V_{\text{GE}} = 0\text{V}$, $V_{\text{CE}} = 600\text{V}$
		—	—	2.0		$V_{\text{GE}} = 0\text{V}$, $V_{\text{CE}} = 10\text{V}$, $T_J = 25^\circ\text{C}$
		—	—	1000		$V_{\text{GE}} = 0\text{V}$, $V_{\text{CE}} = 600\text{V}$, $T_J = 150^\circ\text{C}$
I_{GES}	Gate-to-Emitter Leakage Current	—	—	± 100	nA	$V_{\text{GE}} = \pm 20\text{V}$

Switching Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
Q_g	Total Gate Charge (turn-on)	—	50	75	nC	$I_C = 18\text{A}$
Q_{ge}	Gate - Emitter Charge (turn-on)	—	7.3	11		$V_{\text{CC}} = 400\text{V}$ See Fig. 8
Q_{gc}	Gate - Collector Charge (turn-on)	—	17	26		$V_{\text{GE}} = 15\text{V}$
$t_{\text{d}(\text{on})}$	Turn-On Delay Time	—	22	—	ns	$T_J = 25^\circ\text{C}$ $I_C = 18\text{A}$, $V_{\text{CC}} = 480\text{V}$ $V_{\text{GE}} = 15\text{V}$, $R_G = 23\Omega$
t_r	Rise Time	—	18	—		
$t_{\text{d}(\text{off})}$	Turn-Off Delay Time	—	540	810		
t_f	Fall Time	—	390	590		
E_{on}	Turn-On Switching Loss	—	0.26	—	mJ	Energy losses include "tail" See Fig. 9, 10, 14
E_{off}	Turn-Off Switching Loss	—	3.45	—		
E_{ts}	Total Switching Loss	—	3.71	5.6		
$t_{\text{d}(\text{on})}$	Turn-On Delay Time	—	21	—	ns	$T_J = 150^\circ\text{C}$, $I_C = 18\text{A}$, $V_{\text{CC}} = 480\text{V}$ $V_{\text{GE}} = 15\text{V}$, $R_G = 23\Omega$
t_r	Rise Time	—	19	—		
$t_{\text{d}(\text{off})}$	Turn-Off Delay Time	—	790	—		
t_f	Fall Time	—	760	—		
E_{ts}	Total Switching Loss	—	6.55	—	mJ	Energy losses include "tail" See Fig. 11, 14
L_E	Internal Emitter Inductance	—	7.5	—	nH	Measured 5mm from package
C_{ies}	Input Capacitance	—	1100	—	pF	$V_{\text{GE}} = 0\text{V}$ $V_{\text{CC}} = 30\text{V}$ See Fig. 7 $f = 1.0\text{MHz}$
C_{oes}	Output Capacitance	—	72	—		
C_{res}	Reverse Transfer Capacitance	—	13	—		

Notes:

- ① Repetitive rating; $V_{\text{GE}} = 20\text{V}$, pulse width limited by max. junction temperature (See fig. 13b).
- ② $V_{\text{CC}} = 80\%(V_{\text{CES}})$, $V_{\text{GE}} = 20\text{V}$, $L = 10\mu\text{H}$, $R_G = 23\Omega$, (See fig. 13a).
- ③ Repetitive rating; pulse width limited by maximum junction temperature.
- ④ Pulse width $\leq 80\mu\text{s}$; duty factor $\leq 0.1\%$.
- ⑤ Pulse width $5.0\mu\text{s}$, single shot.

Qualification Information[†]

Qualification Level		Automotive (per AEC-Q101) ^{††}	
		Comments: This part number(s) passed Automotive qualification. IR's Industrial and Consumer qualification level is granted by extension of the higher Automotive level.	
Moisture Sensitivity Level		D ² PAK	MSL1 ^{†††} (per IPC/JEDEC J-STD-020)
		TO-262	N/A
ESD	Machine Model	Class M4 (400V) AEC-Q101-002	
	Human Body Model	Class H1C (2000V) AEC-Q101-001	
	Charged Device Model	Class C5 (1000V) AEC-Q101-005	
RoHS Compliant		Yes	

[†] Qualification standards can be found at International Rectifier's web site: <http://www.irf.com>

^{††} Exceptions to AEC-Q101 requirements are noted in the qualification report.

AUIRG4BC30S-S/SL

International
IR Rectifier




Fig. 1 - Typical Load Current vs. Frequency
(Load Current = I_{RMS} of fundamental)




Fig. 2 - Typical Output Characteristics

4




Fig. 3 - Typical Transfer Characteristics

www.irf.com




Fig. 4 - Maximum Collector Current vs. Case Temperature




Fig. 5 - Typical Collector-to-Emitter Voltage vs. Junction Temperature




Fig. 6 - Maximum Effective Transient Thermal Impedance, Junction-to-Case

AUIRG4BC30S-S/SL

International
IR Rectifier




Fig. 7 - Typical Capacitance vs. Collector-to-Emitter Voltage




Fig. 8 - Typical Gate Charge vs. Gate-to-Emitter Voltage




Fig. 9 - Typical Switching Losses vs. Gate Resistance




Fig. 10 - Typical Switching Losses vs. Junction Temperature

AUIG4BC30S-S/SL




Fig. 11 - Typical Switching Losses vs.
 Collector-to-Emitter Current





Fig. 12 - Turn-Off SOA


AUIRG4BC30S-S/SL

International
IR Rectifier



* Driver same type as D.U.T.; $V_c = 80\%$ of $V_{ce(max)}$
* Note: Due to the 50V power supply, pulse width and inductor will increase to obtain rated I_d .

Fig. 13a - Clamped Inductive Load Test Circuit



Pulsed Collector Current Test Circuit

Fig. 13b - Pulsed Collector Current Test Circuit




Fig. 14a - Switching Loss Test Circuit

* Driver same type as D.U.T., $V_C = 480V$





Fig. 14b - Switching Loss Waveforms

International
IR Rectifier

D²Pak (TO-263AB) Package Outline

Dimensions are shown in millimeters (inches)



AUIG4BC30S-S/SL

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES]
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY AT DATUM H.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. DATUM A & B TO BE DETERMINED AT DATUM PLANE H.
7. CONTROLLING DIMENSION: INCH.
8. OUTLINE CONFORMS TO JEDEC OUTLINE TO-263AB.

SY M B O L	DIMENSIONS		NOT E S
	MILLIMETERS	INCHES	
	MIN.	MAX.	
A	4.06	4.83	.160 .190
A1	0.00	0.254	.000 .010
b	0.51	0.99	.020 .039
b1	0.51	0.89	.020 .035
b2	1.14	1.78	.045 .070
b3	1.14	1.73	.045 .068
c	0.38	0.74	.015 .029
c1	0.38	0.58	.015 .023
c2	1.14	1.65	.045 .065
D	8.38	9.65	.330 .380
D1	6.86	—	.270
E	9.65	10.67	.380 .420
E1	6.22	—	.245
e	2.54	BSC	.100 BSC
H	14.61	15.88	.575 .625
L	1.78	2.79	.070 .110
L1	—	1.65	— .066
L2	1.27	1.78	— .070
L3	0.25	BSC	.010 BSC
L4	4.78	5.28	.188 .208

LEAD ASSIGNMENTS

HEXFET

1. GATE
- 2, 4. DRAIN
3. SOURCE

IGBTs, CoPACK


1. GATE
- 2, 4. COLLECTOR
3. Emitter

DIODES

1. ANODE *
- 2, 4. CATHODE
3. ANODE

* PART DEPENDENT.

D²Pak (TO-263AB) Part Marking Information




Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>
www.irf.com

AUIRG4BC30S-S/SL

International
IR Rectifier

TO-262 Package Outline

Dimensions are shown in millimeters (inches)



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES]
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION: INCH.
7. OUTLINE CONFORM TO JEDEC TO-262 EXCEPT A1(max.), b(min.) AND D1(min.) WHERE DIMENSIONS DERIVED THE ACTUAL PACKAGE OUTLINE.

SYMBOL	DIMENSIONS		NOTES
	MILLIMETERS	INCHES	
	MIN.	MAX.	
A	4.06	4.83	.160 .190
A1	2.03	3.02	.080 .119
b	0.51	0.99	.020 .039
b1	0.51	0.89	.020 .035
b2	1.14	1.78	.045 .070
b3	1.14	1.73	.045 .068
c	0.38	0.74	.015 .029
c1	0.38	0.58	.015 .023
c2	1.14	1.65	.045 .065
D	8.38	9.65	.330 .380
D1	6.86	—	.270 —
E	9.65	10.67	.380 .420
E1	6.22	—	.245 —
e	2.54	BSC	.100 BSC
L	13.46	14.10	.530 .555
L1	—	1.65	— .065
L2	3.56	3.71	.140 .146

LEAD ASSIGNMENTS

HEXFET

1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

IGBTs, CoPACK

1. GATE
2. COLLECTOR
3. Emitter
4. COLLECTOR

TO-262 Part Marking Information

Part Number

AUG4BC30S-SL

Date Code

Y= Year

WW= Work Week

A= Automotive, Lead Free

IR Logo

IR YWWA


XX ● XX

Lot Code

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>

D²Pak Tape & Reel Information

Dimensions are shown in millimeters (inches)



AUIRG4BC30S-S/SL

International
IR Rectifier

Ordering Information

Base part number	Package	Standard Pack		Complete Part Number
		Form	Quantity	
AUIRG4BC30S-SL	TO-262	Tube	50	AUIRG4BC30S-SL
AUIRG4BC30S-S	D2Pak	Tube	50	AUIRG4BC30S-S
		Tape and Reel Left	800	AUIRG4BC30SSTRL
		Tape and Reel Right	800	AUIRG4BC30SSTRR

AU^{RG4BC30S-S/SL}

IMPORTANT NOTICE

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

IR products are neither designed nor intended for use in military/aerospace applications or environments unless the IR products are specifically designated by IR as military-grade or "enhanced plastic." Only products designated by IR as military-grade meet military specifications. Buyers acknowledge and agree that any such use of IR products which IR has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

IR products are neither designed nor intended for use in automotive applications or environments unless the specific IR products are designated by IR as compliant with ISO/TS 16949 requirements and bear a part number including the designation "AU". Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, IR will not be responsible for any failure to meet such requirements.

For technical support, please contact IR's Technical Assistance Center

<http://www.irf.com/technical-info/>

WORLD HEADQUARTERS:

233 Kansas St., El Segundo, California 90245

Tel: (310) 252-7105