

SPECIFICATION CONTROL DRAWING

55FB1551


TITLE

FIVE CONDUCTOR CABLE, SHIELDED, JACKETED, FILTER LINE - ELECTROLOSS

Date 8-13-10

Revision E

This specification sheet forms a part of the latest issue of Raychem Specification 55F.



PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	CABLE CONSTRUCTION DETAILS				MAXIMUM WEIGHT (lbs/1000 ft.)	JACKET FLEXURE ENDURANCE MANDREL DIAMETER (in.) (± 3%)		
			JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)					
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM				
55FB1551-22-*	22	38	.0060	.008	.170	.199	31.8	.325		
55FB1551-20-*	20	38	.0060	.008	.191	.223	42.6	.325		
55FB1551-18-*	18	38	.0070	.009	.223	.258	60.1	.325		
55FB1551-16-*	16	38	.0070	.009	.245	.285	74.6	.500		
55FB1551-14-*	14	38	.0070	.009	.291	.336	103.	.500		
55FB1551-12-*	12	38	.0080	.010	.339	.392	147.	1.00		
55FB1551-10-*	10	36	.0080	.010	.408	.471	223.	1.00		

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

BLOCKING: 200 ± 3°C for 6 hours

CROSSLINKING PROOF TEST: 300 ± 3°C for 7 hours

FLAMMABILITY: 3 seconds (maximum); 3 in. (maximum);
no flaming of facial tissue

FLUORIDE EXTRACTION:

70 ± 2°C for 168 hours, 250 ppm (maximum)

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

JACKET COLOR: Black

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 3500 lbf/in² (minimum)

JACKET FLAWS: Not Applicable

JACKET FLEXURE ENDURANCE: 10 cycles, no cracking

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND (DIELECTRIC):

Conductor to conductor and shield, 1500 volts (rms), 60 Hz

VOLTAGE WITHSTAND (Post Environmental): Not Applicable

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Violet shall be light violet and the designator shall be 7L. Colors shown do not necessarily reflect the sequence of manufacturing.

Example: AWG 22, light violet, light violet with a red stripe, light violet with an orange stripe, light violet with a green stripe and light violet with a blue stripe component wires, black jacket:

55FB1551-22-7L/7L2/7L3/7L5/7L6-0

NOTE: Nominal values are for information only.

Nominal values are not requirements.

This product meets or exceeds all requirements of SAE AS85485/12 for 22-14 AWG, less identification.

Internal wire sizes 22-10 AWG meet or exceed all requirements of SAE AS85485/9, less identification.

All other AWG sizes meet or exceed all requirements of SAE AS85485, less identification.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1	The TE logo, Tyco Electronics, Electroloss and Raychem are trademarks.		 Tyco Electronics Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297	
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL			
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.			